

1987152-1 AS SHOWN

DUST COVER
FOR FIBER PORT
1 x ENCLOSED

STAUBSCHUTZKAPPE
FÜR FASER-
OPTISCHEN EINGANG
1 x BEILIEGEND

DUST COVER
FOR RJ45 PORT
1 x ENCLOSED


STAUBSCHUTZKAPPE
FÜR RJ45-EINGANG
1 x BEILIEGEND

WALL MOUNTING KIT
ENCLOSED


W ANDMONTAGE-BAUSATZ
BEILIEGEND

HARDWARE SPECIFICATION		
1	ETHERNET STANDARD COMPLIANCE	IEEE 802.3 - 10BASE-T IEEE 802.3u - 100BASE-TX AND 100BASE-FX IEEE 802.3x - FLOW CONTROL AND BACK PRESSURE
2	SWITCH ARCHITECTURE	STORE-AND-FORWARD SWITCHING ARCHITECTURE LINK LOSS FORWARD (LLF) AND LINK FAULT PASS-THROUGH (LFP)
3	DIP SWITCH	1: ON: PORT/POWER ALARM ENABLED OFF: PORT/POWER ALARM DISABLED 2: ON: LLF AND LFP ENABLED OFF: LLF AND LFP DISABLED 3: ON: 100BASE-FX HALF MODE OFF: 100BASE-FX FULL MODE 4: ON: MEDIA MODE OFF: SWITCHING MODE
4	ETHERNET PORTS	10/100TX RJ-45 WITH AUTO MDI/MDI-X SUPPORT 100FX SC CONNECTOR FOR MULTI-MODE (MM), WAVE LENGTH 1310nm MULTI-MODE FIBER: 50/125 μ m-62.5/125 μ m, MAX. DISTANCE 2km
5	LED	PER UNIT: POWER 1 (GREEN), POWER 2 (GREEN), FAULT (RED) FIBER PORT: LINK/ACTIVITY (GREEN), HALF/FULL DUPLEX (YELLOW) RJ-45 PORT: LINK/ACTIVITY (GREEN), 10/100Mbps (YELLOW)
6	POWER SUPPLY	WIDE RANGE SUPPLY: 12 TO 48 V DC REVERSE POLARITY PROTECTED OVERLOAD CURRENT PROTECTED (RE-SETTABLE FUSE)
7	POWER CONSUMPTION	2.74 WATTS


FRONT PANEL 1987152-1



FRONT PANEL 1987152-2



1987/152-2	1987/152-1	TYCO ELECTRONICS ORDER NO. BESTELL-NR.	
1	-	2	10/100TX to 100FX MM MEDIA CONVERTER TEC-100-MM-XE WIDE OPERATING TEMPERATURE RANGE -40 °C TO 75 °C
-	1	1	10/100TX to 100FX MM MEDIA CONVERTER TEC-100-MM-X STANDARD OPERATING TEMPERATURE RANGE -10 °C TO 60 °C
QUANTITY STUECK	ITEM NO. POS.	DESCRIPTION BENENNUNG	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR THIS ELECTRONIC COMPONENT THIS DRAWING IS THE PROPERTY OF TYCO ELECTRONICS GMBH. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS GMBH.		DWN 12SEP2007 S.STOLZ		Tyco Electronics Tyco Electronics AMP GmbH 64625 Bensheim (Germany)	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR THIS ELECTRONIC COMPONENT THIS DRAWING IS THE PROPERTY OF TYCO ELECTRONICS GMBH. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS GMBH.		CHN 12SEP2007 B.BERGERER		APVD 12SEP2007 R.KRAEMER	
DIMENSIONS: MASSTEN (MM)		TOL. EXCEPT UNLESS OTHERWISE SPECIFIED: ALIGNMENT TOLERANZEN		NAME INDUSTRIAL ETHERNET MEDIA CONVERTER TEC-100-MM-X(IE) 10/100TX TO 100FX (MM)	
		0 P L C ±0.1 1 P L C ±0.1 2 P L C ±0.1 3 P L C ±0.1 4 P L C ±0.1 ANGLES ON LINE ±0.2°		PRODUCT SPEC 108-94083 APPLICATION SPEC VERBAUTUNGSANLEITUNG - WEIGHT 425 g	
MATERIAL -		FINISH: OBERFLÄCHE: ±0.7		SIZE CASE CODE DRAWING NO. A 00779 C=1987152 RESTRICTED TO NUR FÜR - -	
CUSTOMER DRAWING		KUNDENZEICHNUNG		SCALE MASSTAB 2:1 SHEET BLATT 1 OF 1 REV A2	