

6367254 MOTOROLA SC (XSTRS/R F)

89D 79017 DT-33-15

MOTOROLA **SEMICONDUCTOR** **TECHNICAL DATA**

The RF Line

NPN SILICON RF POWER TRANSISTORS

... designed for power amplifier applications in industrial, commercial and amateur radio equipment to 30 MHz.

- Specified 12.5 Volt, 30 MHz Characteristics —
 Output Power = 80 Watts
 Minimum Gain = 12 dB
 Efficiency = 50%

MAXIMUM RATINGS


Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	25	Vdc
Collector-Base Voltage	V_{CBO}	45	Vdc
Emitter-Base Voltage	V_{EBO}	4.0	Vdc
Collector Current — Continuous	I_C	20	Adc
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	250 1.43	Watts W/ $^\circ\text{C}$
Storage Temperature Range	T_{stg}	-65 to +150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.7	$^\circ\text{C/W}$

MRF454 **MRF454A**


80 W — 30 MHz
RF POWER TRANSISTORS
 NPN SILICON



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	24.63	24.89	0.970	0.980
B	11.81	12.35	0.465	0.510
C	6.82	6.98	0.270	0.275
D	5.46	5.97	0.215	0.235
E	2.13	2.79	0.084	0.110
F	0.08	0.16	0.003	0.007
G	19.29	19.54	0.760	0.770
H	11.05	—	0.435	—
I	6.22	6.48	0.245	0.255
J	45° NOM	—	45° NOM	—
K	3.65	4.52	0.144	0.178
L	2.92	3.30	0.115	0.130

MRF454

CASE 211-11



NOTE
 1 145A-10, USE 10-32NF 2A STUD

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	12.45	12.55	0.490	0.510
B	13.54	15.80	0.415	0.425
C	19.69	22.73	0.775	0.895
D	5.46	5.97	0.215	0.235
E	1.93	—	0.075	—
J	0.06	0.18	0.003	0.007
K	12.45	—	0.490	—
L	1.06	1.50	0.042	0.059
M	45° NOM	—	45° NOM	—
P	—	1.27	—	0.050
R	9.73	10.06	0.383	0.396
S	3.84	4.50	0.151	0.177
T	2.11	2.54	0.083	0.100
U	2.43	3.25	0.096	0.127

MRF454A

CASE 145A-10

3

6367254 MOTOROLA SC (XSTRS/R F)
MRF454, MRF454A

89D 79018 DT-33-15

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted.)

Characteristic	Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS					
Collector-Emitter Breakdown Voltage ($I_C = 100\text{ mA}$, $I_B = 0$)	$V_{(BR)CEO}$	18	—	—	Vdc
Collector-Emitter Breakdown Voltage ($I_C = 50\text{ mA}$, $V_{BE} = 0$)	$V_{(BR)CES}$	36	—	—	Vdc
Emitter-Base Breakdown Voltage ($I_E = 10\text{ mA}$, $I_C = 0$)	$V_{(BR)EBO}$	4.0	—	—	Vdc
ON CHARACTERISTICS					
DC Current Gain ($I_C = 5.0\text{ A}$, $V_{CE} = 5.0\text{ Vdc}$)	h_{FE}	10	—	150	—
DYNAMIC CHARACTERISTICS					
Output Capacitance ($V_{CB} = 15\text{ Vdc}$, $I_E = 0$, $f = 1.0\text{ MHz}$)	C_{ob}	—	—	250	pF
FUNCTIONAL TESTS (Figure 1)					
Common-Emitter Amplifier Power Gain ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	G_{pe}	12	—	—	dB
Collector Efficiency ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	η	50	—	—	%
Series Equivalent Input Impedance ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	Z_{in}	—	$.938 - j.341$	—	Ohms
Series Equivalent Output Impedance ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	Z_{out}	—	$1.16 - j.201$	—	Ohms
Parallel Equivalent Input Impedance ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	—	—	$1.06\ \Omega$ 1817 pF	—	—
Parallel Equivalent Output Impedance ($V_{CC} = 12.5\text{ Vdc}$, $P_{out} = 80\text{ W}$, $f = 30\text{ MHz}$)	—	—	$1.19\ \Omega$ 777 pF	—	—

3

FIGURE 1 — 30 MHz TEST CIRCUIT SCHEMATIC




FIGURE 2 — OUTPUT POWER versus INPUT POWER




FIGURE 3 — OUTPUT POWER versus SUPPLY VOLTAGE

