

Home > Products > By Type > Relays > Product Feature Selector > Product Details

TM013012 Product Details



TM013012

TE Internal Number: 1-1393155-6

stop

Obsolete

[Contact Product Information Center](#)

Industrial Relays (General Purpose)

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- TM Series
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 10 Amps.
- Monostable Coil Magnetic System
- Without Coil Suppression Diode

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = Printed Circuit Terminals

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 10
- [Coil Resistance \(Ω\)](#) = 160
- [Coil Power, Nominal \(mW\)](#) = 900
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 12

Body Related Features:

- [Series](#) = TM
- Polarized = No

Contact Related Features:

- [Mounting Options](#) = PC Board
- [Enclosure](#) = Dust Cover
- FCC Part 68 Isolation = No
- Relay Type = Power
- [Contact Base Material](#) = Silver Cadmium Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 27.50 x 21.60 x 35.20 [1.083 x .851 x 1.386]
- Wiring Diagram = 2 Form C
- Approved Standards = UL Recognized, CSA Certified

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Other:

- Brand = Schrack