



REV.	DATE	ECR NO.	DESCRIPTION
NC	10/28/01	—	INITIAL RELEASE
A	02/15/09	—	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	GRS	02/15/09							
7						CHECKED									
6						ISSUED				PART DESCRIPTION TNC PANEL JACK – 50 Ohms					
5						SHEET	1 OF 1								
4	CONTACT PIN	PHOS. BRONZE	GOLD	1		PART NO.					122248				
3	INSULATOR	PTFE	NATURAL	1											
2	HOUSING	BRASS	NICKEL	1		DWG. NO.					122248.DWG				
1	BODY	BRASS	NICKEL	1		REV. A					SIZE A		SCALE NA		
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/122/122248.DWG									