

Accessories

Type ADAPT 1605, Coding Adaptor

Dupline®
Fieldbus Installationbus



- Coding Adaptor between GAP 1605 and Dupline® modules without standard connection plug (e.g. G 8910 1101 and G 8911 1010)

Product Description

Coding Adaptor between GAP 1605 and Dupline® modules without standard 6-pole connection plug. ADAPT 1605 has 4 clip-on terminals for Dupline® modules which are program-

med through wires (e.g. G 8910 1101) and it has a M12-connector for modules like G 8911 1010. ADAPT 1605 has a standard 6-pole connector for the GAP 1605 connection.

Type Selection

Ordering no.

ADAPT 1605

Product Specifications

Input Connection	From GAP 1605 6/6 modular socket
Output connections	4 clip-on terminals M12 connector

Ordering Key

Type no. _____

ADAPT 1605

General Specifications

Environment	
Degree of protection	IP 20
Pollution degree	3 (IEC 60664)
Operating temperature	0° to +50°C (+32° to +122°F)
Storage temperature	-20° to +60°C (-4° to +140°F)
Humidity (non-condensing)	20 to 80% RH
Mechanical resistance	
Shock	15 G (11 ms)
Vibration	2 G (6 to 55 Hz)
Material	ABS, grey
Weight	100 g