

SMP SERIES

50Ω SMP JACKS/PLUGS & ADAPTOR

SMP-PF, SMP-PL, SMP-PS, SMP-PC
Mate with:
SMP-B Bullet Adaptor

Cable Mates:
RF405, BE25S, RF25S

SPECIFICATIONS

For complete specifications see
www.samtec.com?SMP-TH,
www.samtec.com?SMP-EM,
www.samtec.com?SMP-B or
www.samtec.com?SMP-CA

Shell Material:

Au plated Brass (-TH2, -EM3)
Au plated BeCu (-J-B, -J-C)

Contact Material:

Brass (-TH2, -EM3)
BeCu (-CA)

Insulator Material:

PTFE

Impedance:

50Ω

Frequency Range:

DC to 40 GHz,
DC to 20 GHz (25 AWG)

V.S.W.R. (Interface):

1.15: 1 max to 26.5 GHz,
1.5: 1 max to 40 GHz

Working Voltage:

335 Vrms min

Dielectric Withstanding:

500 Vrms min

Contact Resistance:

Center Contact: 6mΩ max

Outer Contact: 2mΩ max

Insulator Resistance:

5000 MΩ min

Engagement Force:

-PF: 15 lbs. max

-PL: 10 lbs. max

-PS & -PC: 2 lbs. max

Disengagement Force:

-PF: 2 lbs. min

-PL: 2 lbs. min

-PS & -PC: 0.5 lbs. min

Operating Temperature:

-65°C to +165°C

RoHS Compliant: Yes

Processing:

Lead-Free Solderable:

Yes

ALTERNATIVE SOLUTIONS

- The SMP Series is an alternative to the Corning Gilbert GPO Series. A mini SMP Series, available as an ASO, is an alternative to the Corning Gilbert GPPO Series.

Note: While optimized for 50Ω applications, this connector can also perform well in certain 75Ω applications. Contact RFGroup@samtec.com for further information.

SMP-J-B-GF-ST-1450

SMP-PF-P-HH-ST-EM3

SMP-J-C-GF-RA-CA7

SMP-PF-P-GF-ST-TH2

SMP-J-C-GF-ST-CA5

SMP

GENDER

TYPE

PLATING

ORIENTATION

TERMINATION

-PF

= Plug, Full Detent

-PL

= Plug, Limited Detent


-PS

= Plug, Smooth Bore


-PC

= Plug, Catcher's Mitt


-P
= PCB
Mount-GF
= 10μ" (0,25 μm)
Gold center
contact, Gold
Flash outer
contact
(-TH2 only)-HH
= 30μ" (0,76 μm)
Gold center
and outer
contact
(-EM3 only)-ST
= Straight-TH2
= Through-hole

-EM3
= Drop-in
Edge Mount
(N/A with -PC)

-PF/-PL/-PS-TH2




-PC-TH2



-EM3

APPLICATION

LENGTH	BOARD SPACE
-0645	(9,05) .356
-1450	(17,10) .673



ALSO AVAILABLE (MOQ Required)

- Other lengths
- Contact Samtec.

SMP

J

TYPE

PLATING

ORIENTATION

BULLET LENGTH


CABLE END

-B


= Bullet Adaptor

-C


= Cable End

-GF
= 10μ" (0,25 μm)
Gold center
contact, Gold
Flash outer
contact-ST
= Straight-RA
= Right Angle
(N/A with -B)Leave blank
for cable end-0645
= 6,45 mm
(.254")-1450
= 14,50 mm
(.571")Leave blank
for bullet type-CA7
= RG 405
(.086" DIA)
Semi-flexible
Cable-CA5
= CCA-25M
Cable-CS5
= MWC-2550-01
25 AWG
Microwave
Cable


-0645



-1450



-ST-CXX



-RA-CXX

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685