

CABLE END-SLEEVES

for short circuit resistant conductors (NSGAFÖU)


Material: copper

Surface: tin plated

Temperature: 120 °C max.; continuously rated for: 105 °C

Insulated, free of halide

Synthetic material: Polypropylene



Conductor mm ²	Part No.	Colour	Dimensions mm					Tools	1000 pcs ~ kg	pcs
			d ₁	d ₃	l ₁	l ₂	s ₁			
1.5	432/8	black	1.8	7.6	17.5	8	0.15	Chart Page 6.09 – 6.10	0.220	100
	432/10				19.5	10	0.15		0.270	
2.5	433/8	blue	2.3	8.5	17.5	8	0.15		0.240	100
	433/12				21.5	12	0.15		0.360	
4	434/10	grey	2.9	8.5	19.5	10	0.2		0.360	100
6	435/12	yellow	3.6	9.3	23	12	0.2		0.490	100
10	436/12	red	4.6	10.8	24	12	0.2		0.650	100
16	437/12	blue	6	13.1	25.5	12	0.2		0.930	100




TWIN-CABLE END-SLEEVES

Material: copper

Surface: tin plated

Insulated, free of halide

Synthetic material: Polypropylene



Conductor mm ²	Part No.	Colour	Dimensions mm						Tools	pcs
			d ₁	d ₃	l ₁	l ₂	s ₁	s ₂		
2 x 0.5	869/8	white	1.5	2.5 / 4.7	15	8	0.15	0.25	Chart Page 6.09 – 6.10	1000
2 x 0.75	870/8	grey	1.8	2.8 / 5	15	8	0.15	0.25		1000
	870/10				17	10				
2 x 1	871/8	red	2.05	3.4 / 5.4	15	8	0.15	0.3		1000
	871/10				17	10				
2 x 1.5	872/8	black	2.3	3.6 / 6.6	16	8	0.15	0.3		1000
	872/12				20	12				
2 x 2.5	873/10	blue	2.9	4.2 / 7.8	18.5	10	0.2	0.3		1000
	873/13				21.5	13				
2 x 4	874/12	grey	3.8	4.9 / 8.8	23	12	0.2	0.3		100
2 x 6	875/14	yellow	4.9	6.9 / 10	26	14	0.2	0.4		100
2 x 10	876/14	red	6.5	7.2 / 13	26	14	0.2	0.4		100
2 x 16	877/14	blue	8.3	9.6 / 18.4	30	14	0.2	0.4		100

