






PRODUCT NUMBER
SEE SHEET 2



mat'l. code SEE NOTE 1				surface ☒ tolerance		projection 		product family PV TERMINAL			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1		title C.T.W. MALE PIN			
M	V41701	LSS	1994-12-22	angles	lead XX *.01/X*.3 XXX *.005/XX*.13 XXXX *.0020/XXX*.051			dwg no			
N	V04-0056	VS	2004-02-17			T.HANNA		1994-08-22		sheet 1 of 3	
P	V05-0254	HTB	2005-03-18	0' ±2'	M.CLOUSER	1994-08-22		size			
R	V06-0583	HTB	2006-06-27	dr	T.HANNA	1994-08-22		47791			
S	V08-0114	HTB	2008-04-01	engr	T.HANNA	1994-08-22		A			
				chr	T.HANNA	1994-08-22		type			
				appd	T.HANNA	1994-08-22		CUSTOMER Drawing			
sheet index		revision sheet		S	S						
		1	2	3							



PRODUCT NUMBER		AWG	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
REELED FOR APPLICATION MACHINES FEEDING								
LEFT – RIGHT	RIGHT – LEFT							
47791–003	47791–000	O B S O L E T E						
47791–003LF	47791–000LF	28–32	.054 [1.37]	.058 [1.47]	.011 [0.28]	.115 [2.92]	.105 [2.67]	.040 [1.02]
47792–003	47792–000	O B S O L E T E						
47792–003LF	47792–000LF	22–26	.070 [1.78]	.065 [1.65]	.017 [0.43]	.139 [3.53]	.120 [3.05]	.050 [1.27]
47793–003	47793–000	O B S O L E T E						
47793–003LF	47793–000LF	18–20	.104 [2.64]	.104 [2.64]	.021 [0.53]	.139 [3.53]	.120 [3.05]	.050 [1.27]



NOTES:

- ① MATERIAL: C2600 CARTRIDGE BRASS, 3/4 HD.
- ② PLATING: ELECTRODEPOSITED GOLD- 50u"/1.27u AVG. THICKNESS IN CONTACT AREA. REMAINDER GOLD FLASH. UNDERPLATE 50u"/1.27u NICKEL
- ③ FOR MANUFACTURING PURPOSES ONLY.
4. TERMINAL MAY BE USED WITH MINI LATCH HOUSING.
5. APPLICABLE SPECIFICATION:
A. BUS-12-098 PRODUCT SPECIFICATION.
B. TA-211 CRIMP SPECIFICATION.
- ⑥ PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.

mat'l. code SEE NOTE 1				surface ☒	tolerance	projection	product family PV TERMINAL
ltr	ecn no	dr	date	tolerances unless otherwise specified			title C.T.W. MALE PIN
s				angles	$\frac{XX}{100} \pm 0.01/X \pm 3$ $\frac{XXX}{1000} \pm 0.005/XX \pm 13$	INCH/MM	
				0° $\pm 2'$	$\frac{XXXX}{10000} \pm 0.0020/XXX \pm 0.051$	scale 10:1	
				dr	M.CLOUSER 1994-08-22		dwg no
				engr	T.HANNA 1994-08-22		sheet 2 of 3
				chr	T.HANNA 1994-08-22		size
				appd	T.HANNA 1994-08-22		A4
sheet index	revision sheet						type CUSTOMER Drawing

PRODUCT NUMBER
 SEE SHEET 2

 Unreeling Direction
 Left to Right Into
 Applicator

 Unreeling Direction
 Right to Left Into
 Applicator

mat'l. code SEE NOTE 1				surface ☒		tolerance		projection 		product family PV TERMINAL									
ltr	ecr no	dr	date	tolerances unless otherwise specified					title C.T.W. MALE PIN										
s				angles		length XX*.01/ X*.3 XXX*.005/ XX*.13			dwg no sheet 3 of 3 size										
				0° ±2'		width .XXXX*.0020/ XXX*.051													
				dr	H. SUNDY	2004-02-17			47791 A										
				enrg	H. SUNDY	2004-02-17			type CUSTOMER Drawing										
				chr	H. SUNDY	2004-02-17													
				appd	H. SUNDY	2004-02-17													
sheet index		revision sheet																	