

TB62801F

Linear CCD Clock Driver


TB62801F is a clock distribution driver for CCD linear image sensors.

The IC can functionally drive the CCD input capacitance. It also supports inverted outputs, eliminating the need for crosspoint control.

The IC contains a 1 to 4 clock distribution driver for the main clock and 4-bit buffers for control signals.


Features

- High drivability: Guaranteed driving 450 [pF] load capacitance @f_{clock} = 20 [MHz]
- Operating temperature range: T_a = -25°C to 60°C




Weight: 0.5 g (typ.)

Pin Connection (top view)



Logic Diagram



Pin Description

Pin No.	Pin Name	Functions	Remarks
1	$\overline{2B_out}$	Light load drive output (inverted)	Driver output for CCD last-stage clock
2	2B_in	Light load drive input	Driver input for CCD last-stage clock
3	CP_in	Light load drive input	CCD clamp gate driver input
4	V _{CC}	Power supply	—
	GND	Ground	—
5	V _{CC}	Power supply	—
6	CK_in	Heavy load drive input	Driver input for CCD transfer clock
7	SH_in	Light load drive input	CCD shift gate driver input
8	RS_in	Light load drive input	CCD reset gate driver input
9	RS_out	Light load drive output (not inverted)	CCD reset gate driver output
10	SH_out	Light load drive output (not inverted)	CCD shift gate driver output
11	ϕ	Heavy load drive output (not inverted)	Driver output for CCD transfer clock
12	$\overline{\phi}$	Heavy load drive output (inverted)	Driver output for CCD transfer clock
	GND	Ground	—
13	$\overline{\phi}$	Heavy load drive output (inverted)	Driver output for CCD transfer clock
14	ϕ	Heavy load drive output (not inverted)	Driver output for CCD transfer clock
15	CP_out	Light load drive output (not inverted)	CCD clamp gate driver output
16	2B_out	Light load drive output (not inverted)	Driver output for CCD last-stage clock

Truth Table

Input		Output	
2B_in	L	$\overline{2B_out}$	H
	H		L
	L	2B_out	L
	H		H
CP_in	L	CP_out	L
	H		H
CK_in	L	ϕ	L
	H		H
	L	$\overline{\phi}$	H
	H		L
SH_in	L	SH_out	L
	H		H
RS_in	L	RS_out	L
	H		H

Maximum Ratings (Ta = 25°C)

Characteristics		Symbol	Rating	Unit
Power supply voltage		V _{CC}	−0.5 to 7.0	V
Input voltage		V _{IN}	−1.2 to V _{CC} +0.5	V
Output voltage		V _O	−0.5 to V _{CC}	V
Input clamp diode current (V _i < 0)		I _{IK}	−50	mA
Output clamp diode current (V _O < 0)		I _{OK}	−50	mA
Output current excluding other than ϕ , $\overline{\phi}$ outputs	High level	I _{OH} (O/ $\overline{O}$)	−16.0	mA
	Low level	I _{OL} (O/ $\overline{O}$)	16.0	mA
ϕ output current	High level	I _{OH} ($\phi/\overline{\phi}$)	−100	mA
	Low level	I _{OL} ($\phi/\overline{\phi}$)	150	mA
Operating Temperature		T _{opr}	−25 to 60	°C
Storage temperature		T _{stg}	−40 to 100	°C
Junction temperature		T _j	150	°C
Power dissipation		P _D	1.5	W

Note: Output current is specified as follows: V_{OH} = 4.0 V, V_{OL} = 0.5 V.

Recommended Operating Conditions

Characteristics		Symbol	Min	Typ.	Max	Unit
Power supply voltage		V_{CC}	4.7	5.0	5.5	V
Input voltage		V_{IN}	0	—	V_{CC}	V
Output voltage		V_O	0	—	V_{CC}	V
Output current excluding ϕ , $\bar{\phi}$ outputs	High level	$I_{OH} (O/\bar{O})$	—	—	-8.0	mA
	Low level	$I_{OL} (O/\bar{O})$	—	—	8.0	mA
ϕ output current (Note)	High level	$I_{OH} (\phi/\bar{\phi})$	—	—	-20.0	mA
	Low level	$I_{OL} (\phi/\bar{\phi})$	—	—	20.0	mA
Operating temperature		T_{opr}	-25	25	60	°C
Input rise/fall time		t_{ri}/t_{fi}	—	2.5	5.0	ns

Note: Output current is specified as follows: $V_{CC} = 4.7$ V, $V_{OH} = 4.5$ V, $V_{OL} = 0.2$ V
input rise/fall time is specified as 10 % to 90 % of waveform amplitude.

Electrical Characteristics


DC Characteristics (unless otherwise specified, $V_{CC} = 4.7$ to 5.5 V, $T_a = -25$ to 60°C)

Characteristics		Symbol	Test Circuit	Test Condition	V _{CC}	Min	Typ.	Max	Unit
Input voltage	High	V _{IH}	1, 2	—	4.7	2.0	—	V _{CC}	V
	Low	V _{IL}		—	4.7	0	—	0.8	
Input clamp voltage		V _{IK}	3	I _{IK} = −30 mA	4.7	—	—	1.0	V
ϕ output voltage		V _{OH} (ϕ/ $\bar{\phi}$)	4, 5	I _{OH} = −10 mA	4.7	4.5	—	V _{CC}	V
				I _{OH} = −50 mA	4.7	4.0	—	V _{CC}	
				I _{OH} = −300 mA	4.7	2.5	—	V _{CC}	
		V _{OL} (ϕ/ $\bar{\phi}$)	6, 7	I _{OL} = 100 μA	4.7	0	—	0.2	
				I _{OL} = 50 mA	4.7	0	—	0.5	
				I _{OL} = 300 mA	4.7	0	—	2.5	
Output voltage excluding ϕ, $\bar{\phi}$ outputs		V _{OH} (O/ $\bar{O}$)	4, 5	I _{OH} (O/ $\bar{O}$) = −4 mA	4.7	4.5	—	V _{CC}	V
				I _{OH} (O/ $\bar{O}$) = −16 mA	4.7	4.0	—	V _{CC}	
		V _{OL} (O/ $\bar{O}$)	6, 7	I _{OL} (O/ $\bar{O}$) = 4 mA	4.7	0	—	0.2	
				I _{OL} (O/ $\bar{O}$) = 16 mA	4.7	0	—	0.5	
Input voltage		I _{IN}	8	V _{IN} = V _{CC} or GND	5.5	—	—	1.0	μA
Static current consumption	Total	I _{CC}	9	ϕ outputs: High or Low $\bar{\phi}$ outputs: Low or High Other outputs are High	5.5	—	—	15.0	mA
	Each bit	ΔI _{CC}	10	One input: V _{IN} = 0.5 V Other inputs: V _{CC} or GND	—	—	—	1.5	
Output off mode supply voltage		V _{POR}	—	See description on next page.	—	—	3.0	—	V


Output Low Level Fixed Mode at Power-On

To avoid malfunction at power on, this IC incorporates the following functions:

- Fixes all outputs to low level until V_{CC} reaches more than 3 V.
- When V_{CC} reaches 3 V (typ.), internal logic depends on input signals.
- V_{CC} must be more than 4.7 V for the normal operation.



Additional circuit (P.O.R) test circuit



AC Characteristics (input transition rise or fall time: $t_r/t_f = 2.5$ ns)

Characteristics	Symbol	Test Condition	Normal Temperature/ $V_{CC} = 5.0$ V			All Temperatures/ $V_{CC} = 4.7$ to 5.5 V		Unit	Reference Measurement Diagram
			Min	Typ.	Max	Min	Max		
Propagation delay time	$t_{pLH} (\phi/\bar{\phi})$	$C_L = 450$ pF	7.0	10.0	14.0	7.0	16.0	ns	Measurement diagram 1
		$C_L = 350$ pF	6.0	9.0	13.0	6.0	15.0		
	$t_{pHL} (\phi/\bar{\phi})$	$C_L = 450$ pF	7.0	10.0	14.0	7.0	16.0		
		$C_L = 350$ pF	6.0	9.0	13.0	6.0	15.0		
	$t_{pLH} (O/\bar{O})$	$C_L = 30$ pF	3.0	5.0	7.0	2.5	8.0	ns	Measurement diagram 2
		$C_L = 15$ pF	2.0	4.0	6.0	1.5	7.0		
Output skew excluding $\phi, \bar{\phi}$ outputs	t_o (skw)	$C_L = 30$ pF	0	—	2.0	—	2.0	ns	Measurement diagram 3
		$C_L = 15$ pF	2.0	4.0	6.0	1.5	7.0		
Output crosspoints ($\phi1/\phi2$)	V_T (crs)	$C_L = 300$ to 450 pF	—	—	—	1.5	—	V	Measurement diagram 4

Waveform Measuring Point

Propagation Delay Time Setting

Input signal

- 2B_in
- CK_in
- SH_in
- RS_in
- CP_in

Measurement Diagram 1

Output signal

- ϕ

Output signal

- $\bar{\phi}$

Measurement Diagram 2

Output signal

- 2B_out
- CP_out
- SH_out
- RS_out


Output signal

- 2B_out

Measurement Diagram 3

Output signal

- 2B_out
- 2B_out
- CP_out
- SH_out
- RS_out




Output Waveform Crosspoint/Level Setting

Measurement Diagram 4


- ϕ

- $\bar{\phi}$




Reference Data (typ. value)


$t_{PLH}(\phi)$, $t_{PHL}(\phi) - C_L$
(characteristics of 1-output,
other outputs: No load)




Load capacitance versus maximum
operating frequency (all bits in operations)
 $V_{CC} = 5.0\text{ V}$, $T_a = 25^\circ\text{C}$, $t_{r1}/t_{f1} = 2.5\text{ ns}$




Frequency versus power dissipation,
temperature
(@all outputs: maximum load capacitance)




$P_D - T_a$



$\phi/\bar{\phi}$ output
 $I_{OL} - V_{OL}$



$\phi/\bar{\phi}$ output
 $I_{OH} - V_{OH}$




Test Circuit

DC Parameters


Pins marked with an asterisk (*) are test pins. Ground input pins which are not used as test pins so that logic is determined. Unless otherwise specified, bits of the same type are measured the same way.

- V_{IH}/V_{IL}


(1) Light load drive bit



(2) Heavy load drive bit




- V_{IK}




Note 1: When measuring input pins, connect the input pins which are not measured to GND.


- $V_{OH} (O/\phi)$




- $V_{OH} (\bar{O}/\bar{\phi})$




- $V_{OL} (O/\phi)$



- $V_{OL} (\bar{O}/\bar{\phi})$




- I_{IN}




Note: When measuring input pins, connect the input pins which are not measured to GND.

- I_{CC}



Note 1: Input logic of heavy load drive clock input pin (pin 6) is the same for high or low.

- ΔI_{CC}




Note 2: When measuring input pins, connect the input pins which are not measured to GND or power.

AC Parameters


Pins marked with an asterisk (*) are test pins. Ground the input pins which are not used as test pins so that logic is determined. Unless otherwise specified, bits of the same type are measured the same way.

- Propagation Delay Time**


(1) Light load drive bit




(2) Heavy load drive bit



- Light Load Drive Output Skew




- Heavy Load Drive Output Crosspoints



Example of Application Circuit

(1) Connection to TCD1503C




Note: Driving the CCD requires a lot of power. Toshiba recommends using a bypass capacitor connected to the 5 V power supply to stabilize voltage.

Precautions for Using

This IC does not include built-in protection circuits for excess current or over voltage. If this IC is subjected to excess current or over voltage, it may be destroyed. Hence, the utmost care must be taken when systems which incorporate this IC are designed.

Utmost care is necessary in the design of the output line, VCC and GND line since IC may be destroyed due to short-circuit between outputs, air contamination fault, or fault by improper grounding.

(2) Connection to TCD1703C





Note: Driving CCD requires a lot of power. Toshiba recommends using a bypass capacitor connected to the 5 V power supply to stabilize voltage.

Two TB62801FS are used in this application. The one is used to drive all the control bits and four transfer clock bits, the other to drive the remaining four transfer clock bits.

Package Dimensions

HSOP16-P-300-1.00

Unit : mm



Weight: 0.5 g (typ.)

RESTRICTIONS ON PRODUCT USE

030619EBA

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.