



EVERLIGHT ELECTRONICS CO.,LTD.

DATA SHEET

PART NO. : 383-2UBC/C470

DATE : 2002/9/9

DEPARTMENT : CHR&D1

REVISION : 2

RECEIVED			
☒ MASS PRODUCTION			
☐ PRELIMINARY			
☐ CUSTOMER DESIGN			
DEVICE NUMBER : CDLE-038-106			
PAGE : 4			
CUSTOMER	DESIGNER	CHECKER	APPROVER

2	Revision Update	2002/9/9
REV.	DESCRIPTION	RELEASE DATE

Office : 7C Building, Lian Hua Port Industrial District, Lian Hua Shan
Bonded Pricessing Zone Pan Yu, Guang Zhou, China
TEL. : (020)84860913,84860914
FAX : (020)84860600
[http : //www.everlight.com](http://www.everlight.com)



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDLE-038-106 REV.: 2

5.0mm Round Type LED Lamps

PART NO. : 383-2UBC/C470 ECN: Page: 1/4

■ Features :

- Choice of various viewing angles
- Available on tape and reel.
- Reliable and robust


■ Descriptions :

- The series is specially designed for applications requiring higher brightness
- The led lamps are available with different colors, intensities,

■ Applications :

- TV set
- Monitor
- Telephone
- Computer

■ Package Dimensions:



■ Notes :

1. All dimensions are in millimeters.
2. An epoxy meniscus may extend about 1.5mm(0.059") down to the lead.
3. Tolerances unless Dimension $\pm 0.25\text{mm}$.

PART NO.	Chip		Lens Color
	Material	Emitted Color	
383-2UBC/C470	InGaN/SiC	Blue	Water Clear

Office : 7C Building, Lian Hua Port Industrial District, Lian Hua Shan
Bonded Pricessing Zone Pan Yu, Guang Zhou, China
TEL. : (020)84860913,84860914
FAX : (020)84860600
[http : //www.everlight.com](http://www.everlight.com)

A0004068,X0004041



5.0mm Round Type LED Lamps

PART NO. : 383-2UBC/C470 ECN: Page: 2/4

■ Absolute Maximum Ratings at Ta = 25°C

Parameter	Symbol	Rating	Unit
Forward Current	I _F	30	mA
Operating Temperature	T _{opr}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +100	°C
Soldering Temperature	T _{sol}	260 ± 5	°C
Electrostatic Discharge	ESD	1000	V
Power Dissipation	P _d	120	mW
Peak Forward Current(Duty 1/10 @ 1KHz)	I _F (Peak)	100	mA
Reverse Voltage	V _R	5	V

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	I _v	400	800	/	mcd	I _F = 20 mA
Viewing Angle	2θ 1/2	/	6	/	deg	I _F = 20 mA
Peak Wavelength	λ _p	/	468	/	nm	I _F = 20 mA
Dominant Wavelength	λ _d	/	470	/	nm	I _F = 20 mA
Spectrum Radiation Bandwidth	△λ	/	26	/	nm	I _F = 20 mA
Forward Voltage	V _F	/	3.5	4.3	V	I _F = 20 mA
Reverse Current	I _R	/	/	50	μA	V _R = 5 V



EVERLIGHT ELECTRONICS CO.,LTD.







Device Number : CDLE-038-106 REV.: 2

5.0mm Round Type LED Lamps

PART NO. : 383-2UBC/C470 ECN : Page: 3/4

■ Typical Electro-Optical Characteristic Curves:

(UB)





EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDLE-038-106 REV.: 2

5.0mm Round Type LED Lamps

PART NO. : 383-2UBC/C470 ECN : Page: 4/4

■ Reliability test items and conditions:

NO	Item	Test Conditions	Test Hours/Cycle		Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min § 5 min L : -55°C 30min	50 CYCLES	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min § 10 sec L : -10°C 5min	50 CYCLES	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	TEMP : 25°C If = 20mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C / 85% RH	1000 HRS	76 PCS	0/1