

10V Drive Nch MOSFET

R6025ANZ

●Structure

Silicon N-channel MOSFET

●Features

- 1) Low on-resistance.
- 2) Fast switching speed.
- 3) Gate-source voltage (V_{GS}) guaranteed to be $\pm 30V$.
- 4) Drive circuits can be simple.
- 5) Parallel use is easy.

●Applications

Switching

●Packaging specifications

Type	Package	Tube
	Basic ordering unit (pieces)	360
R6025ANZ		○

●Absolute maximum ratings ($T_a=25^\circ C$)

Parameter		Symbol	Limits	Unit
Drain-source voltage		V _{DSS}	600	V
Gate-source voltage		V _{GSS}	±30	V
Drain current	Continuous	I _D *3	±25	A
	Pulsed	I _{DP} *1	±100	A
Source current (Body Diode)	Continuous	I _S *3	25	A
	Pulsed	I _{SP} *1	100	A
Avalanche current		I _{AS} *2	12.5	A
Avalanche energy		E _{AS} *2	39.0	mJ
Total power dissipation (Tc=25°C)		P _D	150	W
Channel temperature		T _{ch}	150	°C
Range of storage temperature		T _{stg}	−55 to +150	°C

*1 $P_w \leq 10\mu s$, Duty cycle $\leq 1\%$


*2 $L \approx 500\mu H$, $V_{DD}=50V$, $R_G=25\Omega$, Starting, $T_{ch}=25^\circ C$

*3 Limited only by maximum temperature allowed.


●Thermal resistance

Parameter	Symbol	Limits	Unit
Channel to case	$R_{th(ch-c)}$	0.83	$^\circ C/W$

●Dimensions (Unit : mm)



●Inner circuit



●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Gate-source leakage	I_{GSS}	—	—	±100	nA	$V_{GS}=\pm 30V$, $V_{DS}=0V$
Drain-source breakdown voltage	$V_{(BR)DSS}$	600	—	—	V	$I_D=1mA$, $V_{GS}=0V$
Zero gate voltage drain current	I_{DSS}	—	—	100	μA	$V_{DS}=600V$, $V_{GS}=0V$
Gate threshold voltage	$V_{GS(th)}$	2.5	—	4.5	V	$V_{DS}=10V$, $I_D=1mA$
Static drain-source on-state resistance	$R_{DS(on)}^*$	—	0.12	0.15	Ω	$I_D=12.5A$, $V_{GS}=10V$
Forward transfer admittance	$ Y_{fs} ^*$	14	20	—	S	$V_{DS}=10V$, $I_D=12.5A$
Input capacitance	C_{iss}	—	3250	—	pF	$V_{DS}=25V$
Output capacitance	C_{oss}	—	2400	—	pF	$V_{GS}=0V$
Reverse transfer capacitance	C_{rss}	—	85	—	pF	$f=1MHz$
Turn-on delay time	$t_{d(on)}^*$	—	50	—	ns	$V_{DD} \approx 300V$, $I_D=12.5A$
Rise time	t_r^*	—	135	—	ns	$V_{GS}=10V$
Turn-off delay time	$t_{d(off)}^*$	—	185	—	ns	$R_L=24\Omega$
Fall time	t_f^*	—	110	—	ns	$R_G=10\Omega$
Total gate charge	Q_g^*	—	88	—	nC	$V_{DD} \approx 300V$
Gate-source charge	Q_{gs}^*	—	25	—	nC	$I_D=25A$
Gate-drain charge	Q_{gd}^*	—	30	—	nC	$V_{GS}=10V$ $R_L=12\Omega$ / $R_G=10\Omega$

* Pulsed

●Body diode characteristics (Source-drain) (Ta=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Forward voltage	V_{SD}^*	—	—	1.5	V	$I_S=12.5A$, $V_{GS}=0V$

* Pulsed

●Electrical characteristic curves




Fig.1 Maximum Safe Operating Area




Fig.2 Typical output characteristics (I)




Fig.3 Typical output characteristics (II)




Fig.4 Typical Transfer Characteristics




Fig.5 Gate Threshold Voltage vs. Channel Temperature




Fig.6 Static Drain-Source On-State Resistance vs. Drain Current




Fig.7 Static Drain-Source On-State Resistance vs. Gate Source Voltage




Fig.8 Static Drain-Source On-State Resistance vs. Channel Temperature




Fig.9 Forward Transfer Admittance vs. Drain Current




Fig.10 Reverse Drain Current vs. Source-Drain Voltage




Fig.11 Typical Capacitance vs. Drain-Source Voltage




Fig.12 Dynamic Input Characteristics




Fig.13 Reverse Recovery Time vs. Reverse Drain Current




Fig.14 Switching Characteristics

●Switching characteristics measurement circuit




Fig.1-1 Switching Time Measurement Circuit




Fig.1-2 Switching Waveforms




Fig.2-1 Gate Charge Measurement Circuit




Fig.2-2 Gate Charge Waveform




Fig.3-1 Avalanche Measurement circuit




Fig.3-2 Avalanche waveform

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>