




LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
AD	39				H	REV PER 0010-1061-94	12-28-96
					J	REV PER 0010-1175-95	12-28-96
					K	REV PER 0310-0398-97	9-25-97




RECOMMENDED P.C.
BOARD LAYOUT

- 1 PHOSPHOR BRONZE 0.25[.010] COML.
FINISH: TIN PLATE
- 2 SHEAR LINES DEFINE LOOSE PIECE PART.
- 3 0.00038[.000015] GOLD IN CONTACT AREA, 0.00254-0.00508[.000100-.000200]
BRIGHT TIN-LEAD IN TERMINATION AREA, ALL OVER 0.00127[.000050] NICKEL.
- 4 0.00076[.000030] GOLD IN CONTACT AREA, 0.00254-0.00508[.000100-.000200]
BRIGHT TIN-LEAD IN TERMINATION AREA, ALL OVER 0.00127[.000050] NICKEL.
- 5 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 6 "H", (RECEPTACLE CENTERS) MAY VARY DEPENDING ON REQUIREMENTS,
MINIMUM NOMINAL CENTER SPACING BETWEEN ADJACENT RECPETACLES
IS 3.81±0.08[.150±.003].



SECTION A-A



SECTION B-B

OBSOLETE	4	1	86441-3	86448-4
OBSOLETE	3	1	86441-2	86448-2
	1	1	86441-1	86448-1
FINISH		MATERIAL	LOOSE PIECE PART NO.	PART NUMBER

PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		
MATERIAL		
SEE TABLE		
FINISH		
SEE TABLE		
DR 12-28-96 E.BRANDBERG		
CHK 12-28-96 J. HERRINGTON		
APPD 12-28-96 J. HERRINGTON		
APPD 12-28-96 D. TROUT		
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT -		
NAME		
FEMALE CONTACT, VERTICAL, TYPE "B", MOD I (HIGH PRESSURE)		
SIZE	CAGE CODE	DRAWING NO
C	00779	C=86448
SCALE	8:1	SHEET
		1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.