

# NLAS3799B, NLAS3799BL

## Dual DPDT Ultra-Low $R_{ON}$ Switch

The NLAS3799B is an ultra-low  $R_{ON}$  dual DPDT and a  $0.5\ \Omega$   $R_{ON}$  analog switch. This device is designed for low operating voltage, high current switching of speaker output and earpiece for cellphone applications. It can switch a balanced stereo output. The NLAS3799B can handle a balanced microphone/speaker/ring-tone generator in a monophone mode. The device contains a break-before-make (BBM) feature.

### Features

- Single Supply Operation  
1.65 to 4.5 V  $V_{CC}$   
Function Directly from LiON Battery
- Maximum Breakdown Voltage: 5.5 V
- Low Static Power
- NLAS3799B Interfaces with 2.8 V Chipset  
NLAS3799BL Interfaces with 1.8 V Chipset
- These are Pb-Free Devices

### Typical Applications

- Cell Phone Speaker/Microphone Switching
- Ringtone-Chip/Amplifier Switching
- Four Unbalanced (Single-Ended) Switches
- Stereo Balanced (Push-Pull) Switching

### Important Information


- ESD Protection:  
Human Body Model (HBM) > 8000 V  
Machine Model (MM) > 400 V
- Continuous Current Rating Through each Switch  $\pm 300$  mA
- Conforms to: JEDEC MO-220, Issue H, Variation VEED-6
- Package:
  - ♦ 1.8 x 2.6 x 0.75 mm WQFN-16 Pb-Free
  - ♦ 1.8 x 2.6 x 0.55 mm UQFN-16 Pb-Free



**ON Semiconductor®**


<http://onsemi.com>

### MARKING DIAGRAMS



XX = Specific Device Code  
 AK = NLAS3799BMNR2G  
 AL = NLAS3799BLMNR2G  
 AX = NLAS3799BMUR2G  
 M = Date Code/Assembly Location  
 ■ = Pb-Free Package


(Note: Microdot may be in either location)



### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 10 of this data sheet.

## NLAS3799B, NLAS3799BL



### Figure 1. Input Equivalent Circuit

## PIN DESCRIPTION

| QFN PIN #                 | Symbol          | Name and Function       |
|---------------------------|-----------------|-------------------------|
| 1, 3, 5, 7, 9, 11, 13, 15 | NO A–D, NC A–D  | Independent Channels    |
| 2, 10                     | A–B IN, C–D IN  | Controls                |
| 4, 8, 12, 16              | COM A–D         | Common Channels         |
| 6                         | GND             | Ground (V)              |
| 14                        | V <sub>CC</sub> | Positive Supply Voltage |

## TRUTH TABLE

|    |      |      |
|----|------|------|
| IN | NO   | NC   |
| H  | ON   | OFF* |
| L  | OFF* | ON   |

\*High impedance.

# NLAS3799B, NLAS3799BL

## MAXIMUM RATINGS

| Symbol        | Parameter                                                            | Value                                | Unit |
|---------------|----------------------------------------------------------------------|--------------------------------------|------|
| $V_{CC}$      | Positive DC Supply Voltage                                           | -0.5 to +5.5                         | V    |
| $V_{IS}$      | Analog Input Voltage ( $V_{NO}$ , $V_{NC}$ , or $V_{COM}$ )          | $-0.5 \leq V_{IS} \leq V_{CC} + 0.5$ | V    |
| $V_{IN}$      | Digital Select Input Voltage                                         | $-0.5 \leq V_{IN} \leq +V_{CC}$      | V    |
| $I_{anI1}$    | Continuous DC Current from COM to NC/NO                              | $\pm 300$                            | mA   |
| $I_{anI-pk1}$ | Peak Current from COM to NC/NO, 10 Duty Cycle (Note 1)               | $\pm 500$                            | mA   |
| $I_{clmp}$    | Continuous DC Current into COM/NO/NC with Respect to $V_{CC}$ or GND | $\pm 100$                            | mA   |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Defined as 10% ON, 90% OFF Duty Cycle.

## RECOMMENDED OPERATING CONDITIONS

| Symbol     | Parameter                                                                                                       | Min  | Max      | Unit |
|------------|-----------------------------------------------------------------------------------------------------------------|------|----------|------|
| $V_{CC}$   | DC Supply Voltage                                                                                               | 1.65 | 4.5      | V    |
| $V_{IN}$   | Digital Select Input Voltage                                                                                    | GND  | $V_{CC}$ | V    |
| $V_{IS}$   | Analog Input Voltage (NC, NO, COM)                                                                              | GND  | $V_{CC}$ | V    |
| $T_A$      | Operating Temperature Range                                                                                     | -40  | +85      | °C   |
| $t_r, t_f$ | Input Rise or Fall Time, IN<br>$V_{CC} = 1.6\text{ V} - 2.7\text{ V}$<br>$V_{CC} = 3.0\text{ V} - 4.5\text{ V}$ |      | 20<br>10 | ns/V |

# NLAS3799B, NLAS3799BL

## NLAS3799B DC CHARACTERISTICS – DIGITAL SECTION (Voltages Referenced to GND)

| Symbol           | Parameter                                       | Condition                                           | V <sub>CC</sub> | Guaranteed Limit |                | Unit |
|------------------|-------------------------------------------------|-----------------------------------------------------|-----------------|------------------|----------------|------|
|                  |                                                 |                                                     |                 | 25°C             | –40°C to +85°C |      |
| V <sub>IH</sub>  | Minimum High–Level Input Voltage, Select Inputs |                                                     | 3.0<br>4.3      | 1.4<br>2.0       | 1.4<br>2.0     | V    |
| V <sub>IL</sub>  | Maximum Low–Level Input Voltage, Select Inputs  |                                                     | 3.0<br>4.3      | 0.5<br>0.8       | 0.5<br>0.8     | V    |
| I <sub>IN</sub>  | Maximum Input Leakage Current, Select Inputs    | V <sub>IN</sub> = V <sub>CC</sub> or GND            | 4.3             | ±0.1             | ±1.0           | μA   |
| I <sub>OFF</sub> | Power Off Leakage Current                       | V <sub>IN</sub> = 4.5 V or GND                      | 0               | ±0.5             | ±2.0           | μA   |
| I <sub>CC</sub>  | Maximum Quiescent Supply Current (Note 2)       | Select and V <sub>IS</sub> = V <sub>CC</sub> or GND | 1.65 to 4.5     | ±1.0             | ±2.0           | μA   |

2. Guaranteed by design. Resistance measurements do not include test circuit or package resistance.

## NLAS3799B DC ELECTRICAL CHARACTERISTICS – ANALOG SECTION

| Symbol                                       | Parameter                                               | Condition                                                                                                                                                                                                                          | V <sub>CC</sub> | Guaranteed Maximum Limit |              |                |              | Unit |
|----------------------------------------------|---------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------|--------------|----------------|--------------|------|
|                                              |                                                         |                                                                                                                                                                                                                                    |                 | 25°C                     |              | –40°C to +85°C |              |      |
|                                              |                                                         |                                                                                                                                                                                                                                    |                 | Min                      | Max          | Min            | Max          |      |
| R <sub>ON</sub>                              | NC/NO On–Resistance<br>(Note 3)                         | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IN</sub> = V <sub>IH</sub><br>V <sub>IS</sub> = GND to V <sub>CC</sub><br>I <sub>IN</sub> = 100 mA                                                                                     | 3.0<br>4.3      |                          | 0.5<br>0.4   |                | 0.6<br>0.5   | Ω    |
| R <sub>FLAT</sub>                            | NC/NO On–Resistance Flatness<br>(Notes 3 and 4)         | I <sub>COM</sub> = 100 mA<br>V <sub>IS</sub> = 0 to V <sub>CC</sub>                                                                                                                                                                | 3.0<br>4.3      |                          | 0.15<br>0.15 |                | 0.15<br>0.15 | Ω    |
| ΔR <sub>ON</sub>                             | On–Resistance Match Between Channels<br>(Notes 3 and 5) | V <sub>IS</sub> = 1.5 V;<br>I <sub>COM</sub> = 100 mA<br>V <sub>IS</sub> = 2.2 V;<br>I <sub>COM</sub> = 100 mA                                                                                                                     | 3.0<br>4.3      |                          | 0.05<br>0.05 |                | 0.05<br>0.05 | Ω    |
| I <sub>NC(OFF)</sub><br>I <sub>NO(OFF)</sub> | NC or NO Off Leakage Current (Note 3)                   | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>V <sub>NO</sub> or V <sub>NC</sub> = 0.3 V<br>V <sub>COM</sub> = 4.0 V                                                                                                     | 4.3             | –10                      | 10           | –100           | 100          | nA   |
| I <sub>COM(ON)</sub>                         | COM ON Leakage Current<br>(Note 3)                      | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>V <sub>NO</sub> 0.3 V or 4.0 V with<br>V <sub>NC</sub> floating or<br>V <sub>NC</sub> 0.3 V or 4.0 V with<br>V <sub>NO</sub> floating<br>V <sub>COM</sub> = 0.3 V or 4.0 V | 4.3             | –10                      | 10           | –100           | 100          | nA   |

3. Guaranteed by design. Resistance measurements do not include test circuit or package resistance.

4. Flatness is defined as the difference between the maximum and minimum value of On–resistance as measured over the specified analog signal ranges.

5. ΔR<sub>ON</sub> = R<sub>ON(MAX)</sub> – R<sub>ON(MIN)</sub> between NCn or NOn.

# NLAS3799B, NLAS3799BL

## NLAS3799BL DC CHARACTERISTICS – DIGITAL SECTION (Voltages Referenced to GND)

| Symbol           | Parameter                                       | Condition                                           | V <sub>CC</sub> | Guaranteed Limit |              | Unit |
|------------------|-------------------------------------------------|-----------------------------------------------------|-----------------|------------------|--------------|------|
|                  |                                                 |                                                     |                 | 25°C             | –40 to +85°C |      |
| V <sub>IH</sub>  | Minimum High-Level Input Voltage, Select Inputs |                                                     | 3.0<br>4.3      | 1.3<br>1.6       | 1.3<br>1.6   | V    |
| V <sub>IL</sub>  | Maximum Low-Level Input Voltage, Select Inputs  |                                                     | 3.0<br>4.3      | 0.5<br>0.6       | 0.5<br>0.6   | V    |
| I <sub>IN</sub>  | Maximum Input Leakage Current, Select Inputs    | V <sub>IN</sub> = V <sub>CC</sub> or GND            | 4.3             | ±0.1             | ±1.0         | μA   |
| I <sub>OFF</sub> | Power Off Leakage Current                       | V <sub>IN</sub> = 4.5 V or GND                      | 0               | ±0.5             | ±2.0         | μA   |
| I <sub>CC</sub>  | Maximum Quiescent Supply Current (Note 6)       | Select and V <sub>IS</sub> = V <sub>CC</sub> or GND | 1.65 to 4.3     | ±40              | ±45          | μA   |

6. Guaranteed by design. Resistance measurements do not include test circuit or package resistance.

## NLAS3799BL DC ELECTRICAL CHARACTERISTICS – ANALOG SECTION

| Symbol                                       | Parameter                                               | Condition                                                                                                                                                                                                                          | V <sub>CC</sub> | Guaranteed Maximum Limit |              |                |              | Unit |
|----------------------------------------------|---------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------|--------------|----------------|--------------|------|
|                                              |                                                         |                                                                                                                                                                                                                                    |                 | 25°C                     |              | –40°C to +85°C |              |      |
|                                              |                                                         |                                                                                                                                                                                                                                    |                 | Min                      | Max          | Min            | Max          |      |
| R <sub>ON</sub>                              | NC/NO On–Resistance<br>(Note 7)                         | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IN</sub> = V <sub>IH</sub><br>V <sub>IS</sub> = GND to V <sub>CC</sub><br>I <sub>IN</sub> = 100 mA                                                                                     | 3.0<br>4.3      |                          | 0.5<br>0.4   |                | 0.6<br>0.5   | Ω    |
| R <sub>FLAT</sub>                            | NC/NO On–Resistance Flatness<br>(Notes 7 and 8)         | I <sub>COM</sub> = 100 mA<br>V <sub>IS</sub> = 0 to V <sub>CC</sub>                                                                                                                                                                | 3.0<br>4.3      |                          | 0.15<br>0.15 |                | 0.15<br>0.15 | Ω    |
| ΔR <sub>ON</sub>                             | On–Resistance Match Between Channels<br>(Notes 7 and 9) | V <sub>IS</sub> = 1.5 V;<br>I <sub>COM</sub> = 100 mA<br>V <sub>IS</sub> = 2.2 V;<br>I <sub>COM</sub> = 100 mA                                                                                                                     | 3.0<br>4.3      |                          | 0.05<br>0.05 |                | 0.05<br>0.05 | Ω    |
| I <sub>NC(OFF)</sub><br>I <sub>NO(OFF)</sub> | NC or NO Off Leakage Current (Note 7)                   | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>V <sub>NO</sub> or V <sub>NC</sub> = 0.3 V<br>V <sub>COM</sub> = 4.0 V                                                                                                     | 4.3             | –10                      | 10           | –100           | 100          | nA   |
| I <sub>COM(ON)</sub>                         | COM ON<br>Leakage Current<br>(Note 7)                   | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>V <sub>NO</sub> 0.3 V or 4.0 V with<br>V <sub>NC</sub> floating or<br>V <sub>NC</sub> 0.3 V or 4.0 V with<br>V <sub>NO</sub> floating<br>V <sub>COM</sub> = 0.3 V or 4.0 V | 4.3             | –10                      | 10           | –100           | 100          | nA   |

7. Guaranteed by design. Resistance measurements do not include test circuit or package resistance.

8. Flatness is defined as the difference between the maximum and minimum value of On-resistance as measured over the specified analog signal ranges.

9. ΔR<sub>ON</sub> = R<sub>ON(MAX)</sub> – R<sub>ON(MIN)</sub> between NC1 and NC2 or between NO1 and NO2.

# NLAS3799B, NLAS3799BL

## NLAS3799B/NLAS3799BL AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 3.0$ ns)

| Symbol           | Parameter                      | Test Conditions                                                                      | V <sub>CC</sub><br>(V) | V <sub>IS</sub><br>(V) | Guaranteed Maximum Limit |      |     |                   |     | Unit |
|------------------|--------------------------------|--------------------------------------------------------------------------------------|------------------------|------------------------|--------------------------|------|-----|-------------------|-----|------|
|                  |                                |                                                                                      |                        |                        | 25°C                     |      |     | −40°C to<br>+85°C |     |      |
|                  |                                |                                                                                      |                        |                        | Min                      | Typ* | Max | Min               | Max |      |
| t <sub>ON</sub>  | Turn-On Time                   | R <sub>L</sub> = 50 Ω, C <sub>L</sub> = 35 pF<br>(Figures 3 and 4)                   | 2.3 – 4.3              | 1.5                    |                          |      | 50  |                   | 60  | ns   |
| t <sub>OFF</sub> | Turn-Off Time                  | R <sub>L</sub> = 50 Ω, C <sub>L</sub> = 35 pF<br>(Figures 3 and 4)                   | 2.3 – 4.3              | 1.5                    |                          |      | 30  |                   | 40  | ns   |
| t <sub>BBM</sub> | Minimum Break-Before-Make Time | V <sub>IS</sub> = 3.0<br>R <sub>L</sub> = 50 Ω, C <sub>L</sub> = 35 pF<br>(Figure 2) | 3.0                    | 1.5                    | 2                        | 15   |     |                   |     | ns   |

|          |                                           | Typical @ 25, $V_{CC} = 3.6$ V |    |
|----------|-------------------------------------------|--------------------------------|----|
| $C_{IN}$ | Control Pin Input Capacitance             | 3.0                            | pF |
| $C_{SN}$ | SN Port Capacitance                       | 72                             | pF |
| $C_D$    | D Port Capacitance When Switch is Enabled | 220                            | pF |

\*Typical Characteristics are at 25°C.

## ADDITIONAL APPLICATION CHARACTERISTICS (Voltages Referenced to GND Unless Noted)

| Symbol    | Parameter                                                                   | Condition                                                                                                                       | $V_{CC}$<br>(V) | 25°C    | Unit |
|-----------|-----------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|-----------------|---------|------|
|           |                                                                             |                                                                                                                                 |                 | Typical |      |
| BW        | Maximum On-Channel -3 dB Bandwidth or Minimum Frequency Response (Figure 9) | $V_{IN}$ centered between $V_{CC}$ and GND (Figure 5)                                                                           | 1.65 – 4.5      | 19      | MHz  |
| $V_{ONL}$ | Maximum Feed-through On Loss                                                | $V_{IN} = 0$ dBm @ 100 kHz to 50 MHz<br>$V_{IN}$ centered between $V_{CC}$ and GND (Figure 5)                                   | 1.65 – 4.5      | -0.06   | dB   |
| $V_{ISO}$ | Off-Channel Isolation                                                       | $f = 100$ kHz; $V_{IS} = 1$ V RMS; $C_L = 5.0$ pF<br>$V_{IN}$ centered between $V_{CC}$ and GND (Figure 5)                      | 1.65 – 4.5      | -69     | dB   |
| Q         | Charge Injection Select Input to Common I/O (Figure 8)                      | $V_{IN} = V_{CC}$ to GND, $R_{IS} = 0 \Omega$ , $C_L = 1.0$ nF<br>$Q = C_L \times \Delta V_{OUT}$ (Figure 6)                    | 1.65 – 4.5      | 51      | pC   |
| THD       | Total Harmonic Distortion THD + Noise (Figure 7)                            | $F_{IS} = 20$ Hz to 20 kHz, $R_L = R_{gen} = 600 \Omega$ , $C_L = 50$ pF<br>$V_{IS} = 2$ V <sub>PP</sub>                        | 4.3             | 0.042   | %    |
| VCT       | Channel-to-Channel Crosstalk (Figure 10)                                    | $f = 100$ kHz; $V_{IS} = 1.0$ V RMS, $C_L = 5.0$ pF, $R_L = 50 \Omega$<br>$V_{IN}$ centered between $V_{CC}$ and GND (Figure 5) | 1.65 – 4.5      | -90     | dB   |

10. Off-Channel Isolation =  $20 \log_{10} (V_{COM}/V_{NO})$ ,  $V_{COM}$  = output,  $V_{NO}$  = input to off switch.

# NLAS3799B, NLAS3799BL





Figure 2.  $t_{BMM}$  (Time Break-Before-Make)





Figure 3.  $t_{ON}/t_{OFF}$






Figure 4.  $t_{ON}/t_{OFF}$

## NLAS3799B, NLAS3799BL



Channel switch control/s test socket is normalized. Off isolation is measured across an off channel. On loss is the bandwidth of an On switch.  $V_{ISO}$ , Bandwidth and  $V_{ONL}$  are independent of the input signal direction.


$$V_{ISO} = \text{Off Channel Isolation} = 20 \text{ Log } \left( \frac{V_{OUT}}{V_{IN}} \right) \text{ for } V_{IN} \text{ at } 100 \text{ kHz}$$

$$V_{ONL} = \text{On Channel Loss} = 20 \text{ Log } \left( \frac{V_{OUT}}{V_{IN}} \right) \text{ for } V_{IN} \text{ at } 100 \text{ kHz to } 50 \text{ MHz}$$

Bandwidth (BW) = the frequency 3 dB below  $V_{ONL}$


$V_{CT}$  = Use  $V_{ISO}$  setup and test to all other switch analog input/outputs terminated with 50 Ω

**Figure 5. Off Channel Isolation/On Channel Loss (BW)/Crosstalk (On Channel to Off Channel)/ $V_{ONL}$**




**Figure 6. Charge Injection: (Q)**


# NLAS3799B, NLAS3799BL




**Figure 7. Total Harmonic Distortion vs. Frequency**




**Figure 8. Charge Injection @ 0 V <  $V_{CC}$  < 4.5 V**




**Figure 9. Bandwidth vs. Frequency**



**Figure 10. Cross-Talk vs. Frequency**



**Figure 11.  $R_{ON}$  vs.  $V_{IN}$  vs. Temperature @  $V_{CC} = 3.0$  V**




**Figure 12.  $R_{ON}$  vs.  $V_{IN}$  vs. Temperature @  $V_{CC} = 4.3$  V**

## NLAS3799B, NLAS3799BL

### DEVICE ORDERING INFORMATION

| Device Order Number | Package Type         | Tape & Reel Size†  |
|---------------------|----------------------|--------------------|
| NLAS3799BMNR2G      | WQFN-16<br>(Pb-Free) | 3000 / Tape & Reel |
| NLAS3799BLMNR2G     | WQFN-16<br>(Pb-Free) | 3000 / Tape & Reel |
| NLAS3799BMUR2G      | UQFN-16<br>(Pb-Free) | 3000 / Tape & Reel |


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.



SCALE 5:1

**WQFN16, 1.8x2.6, 0.4P**  
**CASE 488AP**  
**ISSUE B**


DATE 25 JUN 2008



## NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.25 AND 0.30 MM FROM TERMINAL.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
5. EXPOSED PADS CONNECTED TO DIE FLAG. USED AS TEST CONTACTS.

| MILLIMETERS |      |       |  |
|-------------|------|-------|--|
| DIM         | MIN  | MAX   |  |
| A           | 0.70 | 0.80  |  |
| A1          | 0.00 | 0.050 |  |
| A3          | 0.20 | REF   |  |
| b           | 0.15 | 0.25  |  |
| D           | 1.80 | BSC   |  |
| E           | 2.60 | BSC   |  |
| e           | 0.40 | BSC   |  |
| L           | 0.30 | 0.50  |  |
| L1          | 0.00 | 0.15  |  |
| L2          | 0.40 | 0.60  |  |

**MOUNTING FOOTPRINT**


|                         |                                |                                                                                                                                                                                     |
|-------------------------|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON20790D</b>             | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>WQFN16, 1.8 X 2.6, 0.4P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |


onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.



SCALE 5:1

### UQFN16 1.8x2.6, 0.4P CASE 488AU ISSUE A

DATE 01 AUG 2007




#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.25 AND 0.30 MM FROM TERMINAL.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

| DIM | MILLIMETERS |      |
|-----|-------------|------|
|     | MIN         | MAX  |
| A   | 0.45        | 0.60 |
| A1  | 0.00        | 0.05 |
| A3  | 0.127 REF   |      |
| b   | 0.15        | 0.25 |
| D   | 1.80 BSC    |      |
| E   | 2.60 BSC    |      |
| e   | 0.40 BSC    |      |
| L   | 0.30        | 0.50 |
| L1  | 0.00        | 0.15 |
| L3  | 0.40        | 0.60 |


#### GENERIC MARKING DIAGRAM\*



- XX = Specific Device Code  
M = Date Code/Assembly Location  
▪ = Pb-Free Package  
(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G", may or not be present.

#### MOUNTING FOOTPRINT



|                         |                                     |                                                                                                                                                                                  |
|-------------------------|-------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON22494D</b>                  | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>16 PIN UQFN, 1.8 X 2.6, 0.4P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)