


SOT23 NPN SILICON PLANAR GENERAL PURPOSE TRANSISTORS

ISSUE 6 - JANUARY 1997

BC846	BC847
BC848	BC849
BC850	

PARTMARKING DETAILS		COMPLEMENTARY TYPES	
BC846A-Z1A	BC848B-1K	BC846	BC856
BC846B-1B	BC848C-Z1L	BC847	BC857
BC847A-Z1E	BC849B-2B	BC848	BC858
BC847B-1F	BC849C-2C	BC849	BC859
BC847C-1GZ	BC850B-2FZ	BC850	BC860
BC848A-1JZ	BC850C-Z2G		



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	BC846	BC847	BC848	BC849	BC850	UNIT
Collector-Base Voltage	V _{CBO}	80	50	30	30	50	V
Collector-Emitter Voltage	V _{CES}	80	50	30	30	50	V
Collector-Emitter Voltage	V _{CEO}	65	45	30	30	45	V
Emitter-Base Voltage	V _{EBO}	6		5			V
Continuous Collector Current	I _C	100					mA
Peak Collector Current	I _{CM}	200					mA
Peak Base Current	I _{BM}	200					mA
Peak Emitter Current	I _{EM}	200					mA
Power Dissipation at T _{amb} =25°C	P _{tot}	330					mW
Operating and Storage Temperature Range	T _j :T _{stg}	-55 to +150					°C

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER	SYMBOL		BC846	BC847	BC848	BC849	BC850	UNIT	CONDITIONS.
Collector Cut-Off Current	I_{CBO}	Max	15					nA	$V_{CB} = 30V$
		Max	5					μA	$V_{CB} = 30V$ $T_{amb}=150^{\circ}C$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	Typ	90					mV	$I_C=10mA$,
		Max.	250					mV	$I_B=0.5mA$
		Typ	200					mV	$I_C=100mA$,
		Max.	600					mV	$I_B=5mA$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	Typ	300					mV	$I_C=10mA^*$
		Max.	600					mV	
		Typ	700					mV	$I_C=10mA$,
Base-Emitter Voltage	V_{BE}	Typ	900					mV	$I_B=0.5mA$
		Max.	900					mV	$I_C=100mA$,
		Min	580					mV	$I_C=2mA$
		Typ	660					mV	$V_{CE}=5V$
Base-Emitter Voltage	V_{BE}	Max	700					mV	$V_{CE}=5V$
		Max	770					mV	$I_C=10mA$

* Collector-Emitter Saturation Voltage at $I_C = 10mA$ for the characteristics going through the operating point $I_C = 11mA$, $V_{CE} = 1V$ at constant base current.

BC846	BC847
BC848	BC849
BC850	

ELECTRICAL CHARACTERISTICS (Continued)

PARAMETER	SYMBOL		BC846	BC847	BC848	BC849	BC850	UNIT	CONDITIONS.
Static Forward Current Ratio	Group VI	h_{FE}	Min	75	75	75	—	—	$I_C=2\text{mA}$, $V_{CE}=5\text{V}$
			Typ	110	110	110	—	—	
			Max	150	150	150	—	—	
	Group A	h_{FE}	Typ	90	90	90	—	—	$I_C=0.01\text{mA}$, $V_{CE}=5\text{V}$
			Min	110	110	110	—	—	$I_C=2\text{mA}$, $V_{CE}=5\text{V}$
			Typ	180	180	180	—	—	
			Max	220	220	220	—	—	$I_C=100\text{mA}$, $V_{CE}=5\text{V}$
	Group B	h_{FE}	Typ	120	120	120	—	—	
			Min	150					$I_C=0.01\text{mA}$, $V_{CE}=5\text{V}$
			Typ	200					$I_C=2\text{mA}$, $V_{CE}=5\text{V}$
			Max	290					$I_C=100\text{mA}$, $V_{CE}=5\text{V}$
			Typ	450					
Group C	h_{FE}	Typ.	—	270	270	270	270		$I_C=0.01\text{mA}$, $V_{CE}=5\text{V}$
			Min	—	420	420	420		$I_C=2\text{mA}$, $V_{CE}=5\text{V}$
			Typ	—	500	500	500		
			Max	—	800	800	800		$I_C=100\text{mA}$, $V_{CE}=5\text{V}$
			Typ	—	—	400	—	—	
Transition Frequency	f_T	Typ	300					MHz	$I_C=10\text{mA}$, $V_{CE}=5\text{V}$ $f=100\text{MHz}$
Collector-Base Capacitance	C_{obo}	Typ Max	2.5 4.5					pF pF	$V_{CB}=10\text{V}$ $f=1\text{MHz}$
Emitter-Base Capacitance	C_{ib0}	Typ	9					pF	$V_{EB}=0.5\text{V}$ $f=1\text{MHz}$
Noise Figure	N	Typ Max	2 10	2 10	2 10	1.2 4	1 4	dB dB	$V_{CE}=5\text{V}$, $I_C=200\mu\text{A}$, $R_C=2\text{k}\Omega$, $f=1\text{kHz}$, $\Delta f=200\text{Hz}$
		Typ Max	— —	— —	— —	1.2 4	1 3	dB dB	$V_{CE}=5\text{V}$, $I_C=200\mu\text{A}$, $R_C=2\text{k}\Omega$, $f=30\text{Hz}$ to 15kHz at -3dB points
Equivalent Noise Voltage	e_n	Max.	—	—	—	110	110	nV	$V_{CE}=5\text{V}$, $I_C=200\mu\text{A}$, $R_C=2\text{k}\Omega$, $f=10\text{Hz}$ to 50Hz at -3dB points

Spice parameter data is available upon request for this device

BC846	BC847
BC848	BC849
BC850	

ELECTRICAL CHARACTERISTICS (Continued)

PARAMETER		SYMBOL		BC846	BC847	BC848	BC849	BC850	UNIT	CONDITIONS.	
Dynamic Characteristics	Group VI Group A Group B Group C	h _{ie}	Min	0.4	0.4	0.4	–	–	kΩ	V _{CE} =5V I _C =2mA	
			Typ	1.2	1.2	1.2	–	–	kΩ		
			Max	2.2	2.2	2.2	–	–	kΩ		
			Min	1.6	1.6	1.6	–	–	kΩ		
			Typ	2.7	2.7	2.7	–	–	kΩ		
			Max	4.5	4.5	4.5	–	–	kΩ		
			Min	3.2							kΩ
			Typ	4.5							kΩ
			Max	8.5							kΩ
			Min	–	–	6	6	6	kΩ		
Typ	–	–	8.7	8.7	8.7	kΩ					
Max	–	–	15	15	15	kΩ					
Group VI Group A Group B Group C	h _{re}	Typ	2.5	2.5	2.5	–	–	x10 ⁻⁴			
		Typ	1.5	1.5	1.5	–	–	x10 ⁻⁴			
		Typ	2	2	2	2	2	x10 ⁻⁴			
		Typ	–	–	3	3	3	x10 ⁻⁴			
Group VI Group A Group B Group C	h _{fe}	Min	75	75	75	–	–				
		Typ	110	110	110	–	–				
		Max	150	150	150	–	–				
		Min	125	125	125	–	–				
		Typ	220	220	220	–	–				
		Max	260	260	260	–	–				
		Min	240								
		Typ	330								
		Max	500								
		Min	–	450	450	450	450				
Typ	–	600	600	600	600						
Max	–	900	900	900	900						
Group VI Group A Group B Group C	h _{oe}	Typ	20	20	20	–	–	μs			
		Max	40	40	40	–	–	μs			
		Typ	18	18	18	–	–	μs			
		Max	30	30	30	–	–	μs			
		Typ	30						μs		
		Max	60						μs		
		Typ	–	–	60	60	60	μs			
		Max	–	–	110	110	110	μs			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

[BC846ARTA](#) [BC846ARTC](#) [BC846ATA](#) [BC846ATC](#) [BC846BRTA](#) [BC846BRTC](#) [BC846BTA](#) [BC846BTC](#)
[BC846CTA](#) [BC846CTC](#) [BC847ATA](#) [BC847ATC](#) [BC847BRTA](#) [BC847BRTC](#) [BC847BTA](#) [BC847BTC](#) [BC847CTA](#)
[BC847CTC](#) [BC848ATA](#) [BC848ATC](#) [BC848BRTA](#) [BC848BRTC](#) [BC848BTA](#) [BC848BTC](#) [BC848CRTA](#) [BC848CRTC](#)
[BC848CTA](#) [BC848CTC](#) [BC849BTA](#) [BC849BTC](#) [BC849CTA](#) [BC849CTC](#) [BC850ATA](#) [BC850ATC](#) [BC850BTA](#)
[BC850BTC](#) [BC850CTA](#) [BC850CTC](#)