

PNP General Purpose Transistors by Ascending V_{ce0} (Continued)

Part Type	V_{ce0} (V) Min	V_{cbo} (V) Min	f_{re}		I_c/V_{ce} (mA/V)	f_t (MHz) Min	Package
			Min	Max			
BCF29	32	32	120	260	2/5.0		TO-236
BCF30	32	32	215	500	2/5.0		TO-236
BCW61A	32	32	120	220	2/5.0		TO-236
2N1132A	40	60	30	90	150/10	60	TO-39
2N2904	40	60	40	120	150/10	200	TO-39
2N2905	40	60	100	300	150/10	200	TO-39
2N2906	40	60	40	120	150/10	200	TO-18
2N2907	40	60	100	300	150/10	200	TO-18
2N3905	40	40	50	150	10/1.0	200	TO-92
2N3906	40	40	100	300	10/1.0	250	TO-92
2N4037	40	60	50	250	150/10	60	TO-39
2N4402	40	40	50	150	500/2	100	TO-92
2N4403	40	40	100	300	150/2	200	TO-92
2N5365	40	40	40	120	50/1.0		TO-92
2N5366	40	40	100	300	50/1.0		TO-92
2N5817	40	50	100	200	2/2.0	100	TO-92
BCW80C	40		100	300	150/10	210	TO-236
BSR15	40	60	100	300	150/10	200	TO-236
BSS80B	40	75	40	120	150/10	250	TO-236
BSS80C	40	60	100	300	150/10	210	TO-236
MMBT2904	40	60	40	120	150/10	200	TO-236
MMBT2905	40	60	100	300	150/10	200	TO-236
MMBT2906	40	60	40	120	150/10	200	TO-236
MMBT2907	40	60	100	300	150/10	200	TO-236
MMBT3251	40	50	100	300	10/1.0	300	TO-236
MMBT3905	40	40	50	150	10/1.0	200	TO-236
MMBT3906	40	40	100	300	10/1.0	250	TO-236
MMBT4121	40	40	70	200	10/1.0	400	TO-236
MMBT4122	40	40	150	300	10/1.0	450	TO-236
MMBT4248	40	40	50		0.1/5.0		TO-236
MMBT4250	40	40	250	700	0.1/5.0		TO-236
MMBT4402	40	40	50	150	150/2.0	150	TO-236
MMBT4403	40	40	100	300	150/2.0	200	TO-236
MMBT6518	40	40	150	300	2/10		TO-236
MMBTA70	40		40	400	5/10	125	TO-236
MPS3905	40	40	50	150	10/1.0	200	TO-92
MPS3906	40	40	100	300	10/1.0	250	TO-92
MPS6516	40	40	50	100	2/10		TO-92
MPS6517	40	40	90	180	2/10		TO-92
MPS6518	40		150	300	2/10		TO-92
MPS6533	40	40	40	120	100/1.0		TO-92
MPS6534	40	40	90	270	100/1.0		TO-92
PN2904	40	60	40	120	150/10	200	TO-92
PN2905	40	60	100	300	150/10	200	TO-92
PN2906	40	60	40	120	150/10	200	TO-92
PN2907	40	60	100	300	150/10	200	TO-92
PN3251	40	50	100	300	10/1.0	300	TO-92
PN4121	40	40	70	200	10/1.0	400	TO-92
PN4122	40	40	150	300	10/1.0	450	TO-92
PN4142	40	60	40	120	150/10	200	TO-92
PN4143	40	60	100	300	150/10	200	TO-92