



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION  
ALL RIGHTS RESERVED.


© COPYRIGHT — TE Connectivity Ltd.

| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | P1  | REVISED PER ECR-18-000509 | 17JAN2018 | BDA | KR   |



1 .000030 MIN GOLD AT POINT OF MEASUREMENT IN GOLD PLATE AREA; .000030 MIN TIN IN TIN PLATE AREA; .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT

2 INSULATION RANGE: .060-.130 DIA



|                   |         |            |             |
|-------------------|---------|------------|-------------|
| —                 | 1       | .012 BRASS | 350654-7    |
| 350669-1          | PRE-TIN | .012 BRASS | 350654-1    |
| LOOSE PIECE (REF) | FINISH  | MATERIAL   | PART NUMBER |

|                                                                                                                       |                                                                                                  |                                                                                                                                          |                                                                                                                       |                                                                  |      |           |              |                 |           |
|-----------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------|------|-----------|--------------|-----------------|-----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                | DWN 17JAN2018<br>BASAVARAJA D A                                                                  |                                                                                                                                          | <div></div> TE Connectivity Ltd. |                                                                  |      |           |              |                 |           |
|                                                                                                                       | CHK 17JAN2018<br>RANDOLPH, KURT                                                                  |                                                                                                                                          |                                                                                                                       |                                                                  |      |           |              |                 |           |
| DIMENSIONS:<br>INCHES                                                                                                 | <div></div> | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br><div>0 PLC ± -<br/>1 PLC ± -<br/>2 PLC ± -<br/>3 PLC ± .015<br/>4 PLC ± -<br/>ANGLES ± -</div> |                                                                                                                       | APVD 17JAN2018<br>RANDOLPH, KURT                                 |      |           |              |                 |           |
|                                                                                                                       |                                                                                                  | PRODUCT SPEC<br>—                                                                                                                        |                                                                                                                       | NAME<br><div>PIN, GROUNDING<br/>UNIVERSAL MATE-N-LOK<br/>—</div> |      |           |              |                 |           |
| INSULATION RANGE:<br><div></div> |                                                                                                  |                                                                                                                                          | APPLICATION SPEC<br>—                                                                                                 |                                                                  | SIZE | CAGE CODE | DRAWING NO   | RESTRICTED TO   |           |
|                                                                                                                       |                                                                                                  |                                                                                                                                          | WEIGHT                                                                                                                |                                                                  | A3   | 00779     | C=350654     | —               |           |
| WIRE RANGE:<br>20-14 AWG                                                                                              | MATERIAL<br>—                                                                                    | FINISH<br>—                                                                                                                              | CUSTOMER DRAWING                                                                                                      |                                                                  |      |           | SCALE<br>5:1 | SHEET<br>1 OF 1 | REV<br>P1 |