







Copyright FCI.

PRODUCT NO.
SEE TABLE




mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY	FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.1		projection	title DUAL POLARIZED QUICKIE II ASSEMBLY	
R	ADDNOTE11	JM	1991-09-16		.XX ± 0.05				
S	V22169	MSC	1992-05-21	angles	0° ± 2°		INCH/MM	product family QUICKIE code NT	
T	N05-0368	GUL	2005-12-27						
U	N08-0251	R.B	2008-11-17	dr	GuLing	12/27/05	scale 1:1	size A4 66902	
V	N09-0400	A.Z	2010-01-18	engr	TaoDeniel	12/27/05			
				chr	TaoDeniel	12/27/05		sheet 1 of 2	
				appd	Jason Zhou	12/27/05			
sheet index	revision sheet	V	1-2						

PRODUCT NO.	SIZE	DIM L	DIM S	DIM C
66902-X10/X10LF	2X5	17.27	13.21	10.16
-X14/X14LF	2X7	22.35	18.29	15.24
-X16/X16LF	2X8	24.89	20.83	17.78
-X20/X20LF	2X10	29.97	25.91	22.86
-X24/X24LF	2X12	35.05	30.99	27.94
-X26/X26LF	2X13	37.59	33.53	30.48
-X30/X30LF	2X15	42.67	38.61	35.56
-X34/X34LF	2X17	47.75	43.69	40.64
-X40/X40LF	2X20	55.37	51.31	48.26
-X44/X44LF	2X22	60.45	56.39	53.34
-X50/X50LF	2X25	68.07	64.01	60.96
66902-X60/X60LF	2X30	80.77	76.71	73.66

DASH NO	STYLE	COVER ORIENTATION	POLARIZATION	STRAIN RELIEF
-0XX	THRU	DUAL ENTRY	DUAL POL.	YES
-1XX	THRU	DUAL ENTRY	DUAL POL.	NO
-2XX	THRU	DUAL ENTRY	CENTER KEY & DUAL POL.	YES
-3XX	THRU	DUAL ENTRY	CENTER KEY & DUAL POL.	NO
-4XX	BLIND	RIGHT	DUAL POL.	YES
-5XX	BLIND	RIGHT	DUAL POL.	NO
-6XX	BLIND	LEFT	DUAL POL.	YES
-7XX	BLIND	LEFT	DUAL POL.	NO
-8XX	BLIND	RIGHT	CENTER KEY & DUAL POL.	YES
-9XX	BLIND	LEFT	CENTER KEY & DUAL POL.	YES

COVER ORIENTATION



NOTES:

1. TERMINAL MATERIAL: FULL HARD PHOS. BRONZE ALLOY. UNS-C51000.
2. TERMINAL PLATING: 50u"/1.27um MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 30u"/0.76um MIN Au OR GXT ON CONTACT AREA ONLY.
3. MOLDING MATERIAL: BASE & COVER-GLASS FILLED POLYESTER. FLAME RETARDANT PER UL94V-0. COLOR-BLUE.
4. CONNECTOR ASSEMBL ES PACKAGED IN TUBES.
5. THE FIST TWO CAVITY POSITIONS AND THE LAST TWO. ARE IDENTIFIED BY NUMBER.
6. POLARIZING FEATURES ARE DESCRIBED IN TABLE.
7. MOLDING MATERIAL: STRAIN RELIEF-NYLON, FLAME RETARDANT PER UL 94V-0,COLOR-BLUE.
8. STRAIN RELIEF DIM APPLIES WHEN DATUM -Z- IS HELD IN A RESTRAINED CONDITION.
9. THE POLARIZING FEATURE ON THIS END IS NON-EXISTANT ON 2X5 AND 2X7 POSITION CONNECTORS.
10. 2X5 POSITION NOT AVAILABLE WITH POLARIZATION SLOT ON CENTER KEY STYLE.
11. TO ORDER PARTS THAT DO NOT HAVE MARKED INFORMATION.(DATE. P/N ETC). ADD "u" AFTER THE PART NUMBER. EXAMPLE-66902-010u.
11. PRODUCT NUMBER 66902-XXX LF
 LEAD FREE OPTION
12. WITH "LF" MARK, TERMINAL PLATING: 50u"/1.27um MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 30u"/0.76um MIN Au OR GXT IN CONTACT AREA ONLY.
13. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. FOR LEAD FREE P/N, THE PLASTIC PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TERMERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
15. PRODUCT SPEC. BUS-12-082
16. PLATING OPTIONS: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

tolerances unless otherwise specified		CUSTOMER COPY	 www.fcjconnect.com
linear	.X ± 0.1 .XX ± 0.05	projection	
angles	0° ± 2°		product family QUICKIE code NT
dr	GuLing 12/27/05	INCH/MM	size dwg no
enr	TaoDeniel 12/27/05	scale 1:1	A4 66902
chr	TaoDeniel 12/27/05		sheet 2 of 2
appd	Jason Zhou 12/27/05		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[66902-240LF](#) [66902-234LF](#) [66902-250LF](#) [66902-010](#) [66902-014](#) [66902-020](#) [66902-024](#) [66902-026](#) [66902-030](#)
[66902-040](#) [66902-044](#) [66902-050](#) [66902-110](#) [66902-116](#) [66902-120](#) [66902-124](#) [66902-126](#) [66902-130](#) [66902-134](#)
[66902-140](#) [66902-144](#) [66902-150](#) [66902-160](#) [66902-210](#) [66902-214](#) [66902-216](#) [66902-226](#) [66902-244](#) [66902-](#)
[260](#) [66902-310](#) [66902-314](#) [66902-324](#) [66902-330](#) [66902-344](#) [66902-350](#) [66902-360](#) [66902-250](#) [66902-240](#)
[66902-220](#) [66902-326LF](#) [66902-010LF](#) [66902-014LF](#) [66902-016LF](#) [66902-020LF](#) [66902-024LF](#) [66902-030LF](#)
[66902-040LF](#) [66902-044LF](#) [66902-050LF](#) [66902-060LF](#) [66902-110LF](#) [66902-114LF](#) [66902-116LF](#) [66902-120LF](#)
[66902-124LF](#) [66902-126LF](#) [66902-130LF](#) [66902-134LF](#) [66902-140LF](#) [66902-144LF](#) [66902-150LF](#) [66902-160LF](#)
[66902-210LF](#) [66902-214LF](#) [66902-216LF](#) [66902-224LF](#) [66902-226LF](#) [66902-230LF](#) [66902-244LF](#) [66902-260LF](#)
[66902-310LF](#) [66902-314LF](#) [66902-316LF](#) [66902-320LF](#) [66902-324LF](#) [66902-330LF](#) [66902-334LF](#) [66902-340LF](#)
[66902-344LF](#) [66902-350LF](#) [66902-360LF](#) [66902-220LF](#) [66902-034LF](#) [66902-234](#)