

1	NDK Part Number	NT2520SA-26M-DJA3001A
2	NDK Specification Number	DJA3001A
3	Type	NT2520SA
4	Rating	
4.1	Nominal Frequency (f_{nom})	26 MHz (2 digits marking)
4.2	Supply Voltage	+2.4 V $\pm$ 0.1 V DC (-Earth)
4.3	Current Consumption	Max. 1.1 mA (Typ. 0.9 mA)
4.4	Output Voltage	Min. 0.8 V _{p-p} Clipped sine wave (DC-Coupling)
4.5	Operable Temperature Range	-30 to +75 °C
4.6	Storage Temperature Range	-40 to +85 °C
4.7	Load impedance	10 k Ω // 10 pF
4.8	DC-cut Capacitor	DC-cut capacitor of output is not put in TCXO. Please add DC-cut capacitor (1000 pF) in output line.

5 Electrical specification

5.1 Frequency Stability

5.1.1	Frequency / Temperature Characteristics	Max. $\pm$ 2.5 ppm / -30 to +75 °C (Based on frequency at +25 $\pm$ 2 °C)
5.1.2	Frequency / Voltage Coefficient	Max. $\pm$ 0.2 ppm / +2.4 V $\pm$ 0.1 V
5.1.3	Frequency / Load Coefficient	Max. $\pm$ 0.2 ppm / (10 k Ω // 10 pF) $\pm$ 10%
5.1.4	Frequency Tolerance at Control Voltage (V_{cont} = +1.2 V DC)	Max. $\pm$ 2.5 ppm (at +25 $\pm$ 2 °C, after two reflows, based on nominal frequency)
5.1.5	Long-term Frequency Stability	Max. $\pm$ 2.0 ppm / 5 years

5.2 External Adjustment

5.2.1	Control Voltage (V_{cont})	+1.2 V $\pm$ 1.0 V DC
5.2.2	Frequency control range based on frequency at V_{cont} = +1.2 V DC	$\pm$ 9.0 to $\pm$ 15.0 ppm
5.2.3	Frequency Change Polarity	Positive
5.3	Stabilization Time	Max. 4.0 ms ($\pm$ 0.1 ppm of final frequency final frequency is the frequency after 10 s from the point when supply voltage is reached at +2.4 V. Measurement is done while the control voltage is kept at its typical value at +25 $\pm$ 2 °C)

5.4	Symmetry	40 to 60 % (Based on GND. The output signal after DC cut capacitor passage)
5.5	Harmonic Distortion	Max. -5 dBc
5.6	Phase Noise	Max. -130 dBc/Hz (@1 kHz offset)

6 Dimension

(Unit: mm)

