



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MIN. BUNDLE DIA.	MAX. BUNDLE DIA.	LENGTH L $\pm .2$ [5]
MLT2.7WH-LP	50	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-LP	50	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-LP	50	2.0" [50]	6" [152]	20.5" [521]
MLT8WH-LP	50	2.0" [50]	8" [203]	26.8" [679]
MLT10WH-LP	50	2.0" [50]	10" [254]	33.0" [838]
⑥ MLT2.7WH-TL	250	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-TL	250	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-TL	250	2.0" [50]	6" [152]	20.5" [521]



NOTES:

- 1.) APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, ^①HTMT
- 2.) MINIMUM LOOP TENSILE STRENGTH - 450 LBS (2000 NEWTONS)
ALL PARTS WHEN TESTED ON A 3" MANDREL EXCEPT
PART NO. MLT2.7WH-LP WHEN TESTED ON A 1 1/2" MANDREL.
- 3.) [] DENOTES DIMENSION IN MILLIMETERS
- 4.) TOLERANCES:
.XXX = $\pm .010$ [.25]
.XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8]
ANGLES = $\pm 2^\circ$
- 5.) MATERIAL: 304 STAINLESS STEEL



S41122_03

03	11/06	JAMB	DPN	⑥ ADDED PANDUIT PART NO'S MLT2.7WH-TL, MLT4WH-TL & MLT6WH-TL PACKAGE QTY. 250	SS00281	---	---	PANDUIT CORP. TINLEY PARK, ILLINOIS WAVE-TY HEAVY SERIES - 304 STAINLESS STEEL
02	8/04	JAMB	DPN	③④⑤ ADDED "REF" TO DIM'S. ⑤ REMOVED "AISI NO. 1 FULL RADIUSED" AND REPLACED WITH "FULLY ROUNDED"	11909	CCH	JJB	
01	10/03	BRH	DPN	① ADDED ST3MT TO APPLICATION TOOLS NOTE	11162	CCH	JJB	
00	4/03	JAMB	DPN	RELEASED	10060	CCH	JJB	
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY JAMB CHK'D DPN SCALE 2X DRAWING NO. S41122