


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED PER ECO-16-005106	05APR2016	NK	MZ
	N	REVISED PER ECO-18-000435	17JAN2018	RS	MZ



- 1 FINISH— SILVER PLATE 500 μINCHES THICK MINIMUM.
- 2 FINISH— SILVER PLATE 200 μINCHES THICK MINIMUM.
- 3 FINISH— NICKEL PLATE 40 μINCHES THICK MINIMUM.
- 4 FINISH— GOLD PLATE 50 μIN MIN THICK MINIMUM.
- 5 FINISH—
- 6 PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS: 1—2 AS 1 OVER 2.
- 7 PRODUCT IS SOLD BY THE FOOT.
- 8 PRELIMINARY PART NUMBER.
- 9 FINISH— GOLD PLATE 40 μIN THICK MINIMUM.
- 10 FINISH— NICKEL PLATE 100 μIN THICK MINIMUM.
- 11 OBSOLETE
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 13 10 LOUVERS, NOT TO EXCEED 1.000 INCHES.

OBSOLETE	$\triangle_8$	2.79 [.110]	1.90[48.3]/2.00[50.8]	1-3	20 MIN	0.25 [.010]	-	2-192002-0
OBSOLETE	.100	2.75 [.110]		4-3	$\triangle_7$	0.25 [.010]	-	1-192002-9
OBSOLETE	.100 $\triangle_8$	2.75 [.110]	1.00 $^{+.01}_{-.00}$	1-3	10-11	0.25 [.010]	-	1-192002-8
$\triangle_{12}$	.090	2.79 [.110]		9-10	$\triangle_7$	0.25 [.010]		1-192002-7
OBSOLETE	.100	2.67 [.105]		4-3	$\triangle_7$	0.15 [.006]		1-192002-6
OBSOLETE	$\triangle_8$	2.67 [.105]	-	4-3	3	0.15 [.006]	-	1-192002-5
	.090 $\triangle_8$	2.67 [.105]		4-3	$\triangle_7$	0.15 [.006]	-	1-192002-4
	$\triangle_8$	2.67 [.105]	-	1-3	3	0.15 [.006]	-	1-192002-3
	$\triangle_8$	2.67 [.105]		1-3	$\triangle_7$	0.15 [.006]	-	1-192002-2
	$\triangle_8$	2.67 [.105]		4-3	$\triangle_7$	0.15 [.006]	-	1-192002-1
	$\triangle_8$	2.79 [.110]	-	UNPL	6	0.25 [.010]	-	1-192002-0
$\triangle_{12}$		2.79 [.110]	203.2 [8.00]	1-3	--	0.25 [.010]	00517	192002-9
OBSOLETE		2.79 [.110]	--	1-3	4	0.25 [.010]	00513	192002-8
	.100 $\triangle_{11}$	2.79 [.110]	--	1-3	9	0.25 [.010]	00515	192002-7
$\triangle_{12}$		2.79 [.110]	--	1-3	5	0.25 [.010]	00514	192002-6
OBSOLETE		2.79 [.110]	152.4 [6.00]	1-3	--	0.25 [.010]	00516	192002-5
OBSOLETE		2.79 [.110]	$\triangle_{13}$	1-3	$\triangle_7$	0.25 [.010]	00502	192002-4
		2.79 [.110]		UNPL	$\triangle_7$	0.25 [.010]	00503	192002-3
OBSOLETE		2.67 [.105]		1-3	$\triangle_7$	0.15 [.006]	00501	192002-2
OBSOLETE		2.67 [.105]		UNPL	$\triangle_7$	0.15 [.006]	00500	192002-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		 TE Connectivity											
		CHK S.SIEGRIST 12-16-92													
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT BAND, STRIP											
		APVD —													
		PRODUCT SPEC —													
		APPLICATION SPEC —													
0 PLC ± — 1 PLC ± — 2 PLC ± 0.5 [.02] 3 PLC ± 0.25 [.10] 4 PLC ± — ANGLES ± —		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL BeCu		SEE TABLE		WEIGHT —		A2		00779		C=192002		—			
CUSTOMER DRAWING						SCALE		1:1		SHEET		1 OF 1		REV N	