

Technical drawing of a probe with dimensions A through K and reference dimensions F, G, and J. The drawing includes a side view and a cross-sectional view of the probe tip.

Dimensions and Reference Dimensions:

- A: $\pm .01 (.25)$
- B: $\pm .01 (.25)$
- C: REF.
- D
- E
- F: REF.
- G: REF.
- H: REF. NOMINAL HOLE DIAMETER $\pm .016 (.41)$
- J: REF.
- K: REF.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	K in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)														
PLWP30SC	.12 (3)	1.18 (30)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	5.8 (147.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.32 (145)
PLWP40SC	.12 (3)	1.58 (40)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	7.0 (178)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.37 (168)
PLWP50SC	.12 (3)	1.97 (50)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	8.2 (208.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.42 (191)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

										CAD FILENAME/LAYERS		DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS				
										PANDUIT CORP. TINLEY PARK, ILLINOIS						
										WINGED PUSH MOUNT CABLE TIE PLWP30, 40, 50SC						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.1(2.5) (.XXX) ±.020(.51) (.XX) ±.02(.5) ANGLES ±----			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY	SO	MAT'L:		SCALE NONE		
10	10/28/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS			26267	10			DATE	12/14/90	HEAT STABILIZED NYLON 6.6 BLACK (-30)		DRAWING NO.	DWG
REV	DATE	BY	CHK	DESCRIPTION			ECN	- R	CUST	SUP		CHK'D HVP			SS-26267	A SIZE