




©1968 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	R	REV: EPN DE-057	7-88	
	S	REV: ECN DE-1069	10-88	SPM
	T			ABM

- 203874-1 1. AS SHOWN
2. STRIP PART
3. BODY-BRASS, .000030 GOLD/NI. .000050.
SLEEVE, STAINLESS STEEL.
- 203874-2 1. SAME AS -1, EXCEPT:
2. BODY, SELECTIVE .000030 GOLD/NI. .000050.
- 203874-3 1. SAME AS -1, EXCEPT:
2. LOOSE PIECE PART
- 203874-4 1. SAME AS -2, EXCEPT:
2. LOOSE PIECE PART
- 203874-5 1. SAME AS -1, EXCEPT:
2. BODY SELECTIVELY PLATED .000015 GOLD/NI. .000050.
- 203874-6 1. SAME AS -1 EXCEPT:
2. BODY SELECTIVELY PLATED .000015 GOLD/NI. .000050.
- 203874-7 1. SAME AS -1 EXCEPT:
2. LOOSE PIECE PART.
- 203874-8 1. SAME AS -2 EXCEPT:
2. REVERSE FEELED FOR STANDARD APPLICATOR

WIRE RANGE: 24, 26, 28 & 30 AWG
INSULATION RANGE: .048 MAX.
HAND TOOL: AMP #90223-5
EXTRACTION TOOL: AMP #91038-3
INSERTION TOOL: AMP #91042-1

CAUTION: USE OF TIN PLATED TERMINALS IN CERTAIN ENVIRONMENTS MAY CAUSE NON-CONFORMANCE TO AMP PRODUCT SPECIFICATION 108-10015.

1. SAME AS -1 EXCEPT:
2. BODY PLATED .000050 GOLD OVER NICKEL .000030

1. SAME AS -1 EXCEPT:
2. LOOSE PIECE PART.

1. SAME AS -3 EXCEPT:
2. CUSTOMER PART NO. TO BE MARKED ON INNER-MOST PACKAGE.

1. SAME AS -1 EXCEPT:
2. CUSTOMER PART NO. TO BE MARKED ON INNER-MOST PACKAGE.

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± .5°		CONTRACT NO.		AMP	
MATERIAL		DR		NAME	
SEE DASH NO.		WYCHECK 1-26-68		CONTACT ASSY - PIN	
HEAT TREAT		CHK		SIZE	
SEE DASH NO.		M. Leazer 2-5-68		B	
FINISH		APPD		CODE IDENT NO.	
SEE DASH NO.		M. Leazer 2-5-68		00779	
LOC		DSGN APPD		NUMBER	
PRIN		OTHER APPD		203874	
DEF		A. Miller 4-6-68		SCALE	
CO				10-1	
S				WT CALC ACTUAL	
				SHEET 1 OF 1	