






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECO-17-011927	23AUG2017	RS	KR

- 1
- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
- 2
- RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
- 3
- PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
- 4
- OPTIONAL FOR KEYING HOUSING IN PANEL.
- 5
- CIRCUIT NUMBER 1 LOCATION.
- 6
- DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED CONDITION ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 7
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 8
- UNDERWRITERS RECOGNIZED COMPONENT LOGO 8 AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- 9
- 150° C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION. MAX OPERATING TEMPERATURE REMAINS 125° C.
- 10
- PHOSPHOR BRONZE CONTACTS SHOULD ALWAYS BE USED WITH THIS HOUSING.




DETAIL A
OPTIONAL CONSTRUCTIONS



RECOMMENDED PANEL CUT OUT

4.45	.175	27.43	1.080
2.79	.110	20.70	.815
2.54	.100	20.32	.800
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 16-MAY-2001	TE Connectivity	
DIMENSIONS: INCHES		CHK S. RIDGILL 16-MAY-2001		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. RIDGILL 16-MAY-2001	NAME	
	0. PLC ± -	PRODUCT SPEC	CAP, 3 CIRCUIT, UNIVERSAL MATE-N-LOK™	
	1. PLC ± -	APPLICATION SPEC	-	
MATERIAL NYLON,UL 94V-2, HIGH TEMP		WEIGHT 0.000000	SIZE A1	CAGE CODE 00779
FINISH -		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1
		RESTRICTED TO -	REV A2	