









20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

M
L
K
J
I
H
G
F
E
D
C
B
A




- NOTES:
- 1) MATERIAL :
 - CARRIER TAPE : VOLUME CONDUCTIVE POLYCARBONATE, (0.37) .014 REF THICK, BLACK
 - COVER TAPE : COLD SEAL POLYESTER, (0.06) .002 REF THICK, TRANSPARENT
 - 2) PITCH TOLERANCE OVER ANY 10 PITCHES ± (0.2) .008
 - 3) PEEL FORCE OF THE COVER TAPE IS 0.1N TO 1.0N
 - 4) AT A MAXIMUM PEEL SPEED OF (300) 181mm/min ± 10%
 - 5) REFERENCE TO IEC 286-3 EXCEPT WHERE SPECIFIED

COMPONENT	DESCRIPTION
90811-2001	MOBILE PHONE I/O CONNECTOR


UPDATED SHEET 3 ECN: E2007-0458 2007/05/10 DPMVNDUGGAN 2007/05/15 CHKD: APPRLEQAN 2007/05/16	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		 THIRD ANGLE PROJECTION
		mm	INCH	MM/IN		5:1		METRIC		
		4 PLACES ± --- ± ---		DRAWN BY		DATE		TITLE BLISTER PACKAGING FOR MOBILE PHONE HANDSET		
		3 PLACES ± --- ± ---		CHECKED BY		DATE				
		2 PLACES ± 0.10 ± ---		MW		1996/05/10				
REV	DESCRIPTION	1 PLACE ± 0.2 ± ---		APPROVED BY		DATE		 MOLEX INCORPORATED		
		ANGULAR ± .5 °		MW		1996/05/10				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				SEE CHART		SDA-90811-9001		1 OF 3		
				SIZE A1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

COMPONENT DETAIL (W/UNSWITCHED RF)



SCALE 2:1

REFERENCE ONLY



REEL DIMENSIONS

DO NOT SCALE

(400) PIECES / REEL (SUBJECT TO CHANGE)

(THREE) REELS / CARDBOARD BOX (96707-0007)

(1200) PIECES / CARDBOARD BOX (SUBJECT TO CHANGE)



99044-1066

CENTRE LINE FOR
VACUUM PICK UP

99044-5006

20.0 REF.

2.00 ±0.35
NOTE 5

Ø 1.50 ±0.10
0.00

4.00 PITCH
NOTE 2


L75

20.20


44.00 ±0.30

8.80 MAX.

DIRECTION OF UNREELING



B - B



SCALE 10:1

NOTES:

- 1) MATERIAL :
CARRIER TAPE : VOLUME CONDUCTIVE POLYSTYRENE ,0.4 REF THICK ,BLACK
COVER TAPE : COLD SEAL POLYESTER ,0.06 REF THICK, TRANSPARENT
- 2) PITCH TOLERANCE OVER ANY 10 PITCHES ±0.2
- 3) PEEL FORCE OF THE COVER TAPE IS 0.1N TO 1.0N
AT A MAXIMUM PEEL SPEED OF 300mm/min ±10%
- 4) REFERENCE TO IEC 286-3 EXCEPT WHERE NOTED



MOLEX REEL

COMPONENT	DESCRIPTION
90811-2129	MOBILE PHONE I/O CONNECTOR
90811-2130	1mm Pitch I/O Rpt 16Ckt W/RF
90811-2131	1mm Pitch I/O Rpt 16Ckt W/O RF

ADDED PART NO ECN NO: E2007-0458 2007/05/01 DRN# DUGGAN 2007/05/15 CHKD: 2007/05/16 APPR# EDUAN	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION															
	▽=0 ▽=0	<table><thead><tr><th></th><th>mm</th><th>INCH</th></tr></thead><tbody><tr><td>4 PLACES ±</td><td>---</td><td>---</td></tr><tr><td>3 PLACES ±</td><td>---</td><td>---</td></tr><tr><td>2 PLACES ±</td><td>0.10</td><td>---</td></tr><tr><td>1 PLACE ±</td><td>0.2</td><td>---</td></tr></tbody></table>		mm	INCH	4 PLACES ±	---	---	3 PLACES ±	---	---	2 PLACES ±	0.10	---	1 PLACE ±	0.2	---	DRAWN BY T. MAHON	DATE 1998/06/16	TITLE BLISTER PACKAGING FOR MOBILE PHONE HANDSET		
		mm	INCH																			
	4 PLACES ±	---	---																			
3 PLACES ±	---	---																				
2 PLACES ±	0.10	---																				
1 PLACE ±	0.2	---																				
			CHECKED BY DBRENNAN	DATE 1998/06/16																		
			APPROVED BY MWILHITE	DATE 1998/06/16	MOLEX INCORPORATED																	
			MATERIAL NO. SEE CHART	DOCUMENT NO. SDA-90811-9001	SHEET NO. 3 OF 3																	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A1 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			