

MN1871274

Type			MN1871274
ROM (x8-bit)			12K
RAM (x8-bit)			256
Minimum Instruction Execution Time			2/3 dividing 0.5μs (at 4.5 to 5.5V, 12MHz)
Interrupts			• RESET • External 0 • External 1 • Timer 0 • Timer 1 • Timer 2 • Remote Control • MOSD
Timer Counter			Timer Counter 0 : 8-bit x 1 Clock Source1/1, 1/4, 1/16, 1/64 of System Clock Interrupt SourceOverflow of Timer Counter 0 Timer Counter 1 : 8-bit x 1 Clock Source1/2, 1/16, 1/64, 1/256, 1/512 of System Clock Interrupt SourceOverflow of Timer Counter 1 Time Base Counter Clock Source1/4096 of System Clock Interrupt Source1/1, 1/2, 1/4, 1/8, Timer Counter 2 Watchdog Timer
I/O Pins	I/O	20	• Common use : 10 • General use : 10
	Input	1	• Common use : 1
A/D Inputs			5-bit x 10ch (without S/H)
PWM			14-bit x 1ch, 8-bit x 5ch
Special Ports			Hsync detection, Remote Control Reception
CRTC			Single OSD built-in (Menu OSD : 12 x 18, 128 letters)
Notes			Remote Control Data Detection Circuit built-in
Package			SDIP042-P-0600
Electrical Characteristics			


A/D Converter Characteristics

Parameter	Symbol	Condition	Limit			Unit
			min	typ	max	
A/D Conversion Absolute Error	TAD	fosc=12MHz	9			μs
Analog Input Voltage	VAD		VSS		VDD	V

(Ta= -20 to +70°C, VDD=5.0V, VSS=0V)

Support Tool

■ In-Circuit Emulator	PX-ICE1870/80+PX-PRB1876476
■ EPROM built-in Type	Use MN18P76476 with converting P-board from SDIP064-P-0750 to SDIP042-P-0600. Use MN18P73284 (under development).
■ Pin Assignment	



SDIP042-P-0600