

2		1				
LOC	DIST	REVISIONS				
G	02	P	LTR	DESCRIPTION	DATE	APVD
			D1	REDRAWN PER ECR 09-13445	11JUN09	JR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

- 1

STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
- 2

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - CU PER ASTM B152
INSULATION - NYLON
- 3


FINISH: BODY: TIN PER ASTM B-545
SLEEVE: TIN PER ASTM B-545
INSULATION - COLOR: RED
- 4

WIRE INSUL DIA .105-.140
- 5

APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE

--	LOOSE PIECE	322426
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5° FINISH
MATERIAL	

DWN jr ruth 11JUN09	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
CHK TOM MICHIELUTTI 11JUN09		
APVD TOM MICHIELUTTI 11JUN09	NAME TERMINAL, P.I.D.G., FLANGED SPADE, WIRE SIZE: 22-16	
PRODUCT SPEC UL 486A	-	
APPLICATION SPEC -	SIZE A3	CAGE CODE 00779
WEIGHT -	DRAWING NO C-322426	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 6:1
		SHEET 1 OF 1
		REV D1