

DO NOT SCALE
DIMENSIONS IN

METRIC

3rd ANGLE PROJECTION

NOTES

- 1 MATERIAL: HOUSING: TERMOPLASTICO S/ FIBRA DE VIDRO V-0 COR: PRETO
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITHOUT GLASS FIBER V-0 COLOR: BLACK
CONTACT: PHOSPHOROUS BRONZE
- 2 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO NR. COR: NATURAL
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER NR. COLOR: NATURAL
CONTACT: PHOSPHOROUS BRONZE
- 3 0,38 μ m. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 μ m NIQUEL
0,38 μ m. MIN. GOLD ON CONTACT AREA, 0,76 μ m NIQUEL UNDERPLATING
- 4 0,76 μ m. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 μ m NIQUEL
0,76 μ m. MIN. GOLD ON CONTACT AREA, 0,76 μ m NIQUEL UNDERPLATING
- 5 1,27 μ m. MIN. OURO NA AREA DE CONTATO, SOBRE BANHO 0,76 μ m NIQUEL
1,27 μ m. MIN. GOLD ON CONTACT AREA, 0,76 μ m NIQUEL UNDERPLATING
- 6 ESTANHO SOBRE NIQUEL
TIN UNDER NICKEL
- 7 PONTO DE CONTATO E/ MEDIÇÃO DA CAMADA DE OURO
CONTACT POINT FOR GOLD PLATING MEASUREMENT
- 8 ACETA PINO QUADRADO 0,64 x 0,64 OU REDONDO $\varnothing$ 0,64
ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND $\varnothing$ 0,64
- 9 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO COR VERMELHO, V-2
CONTACT: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER COLOR RED; V-2
CONTACT: PHOSPHOROUS BRONZE

	3	10	L	2 - 880584	- 1
11 OBSOLETE	6	9			9
11 OBSOLETE	6				8
	5				- 7
11 OBSOLETE	4				6
	3	2			- 5
	6				- 4
11 OBSOLETE	5				- 3
	4				- 2
	3	1	K7	880584	- 1

OTHER TREATMENT			FINISH			MATERIAL			PART REV.	PART NUMBER				
CUSTOMER DWG for REFERENCE ONLY						TOLERANCES UNLESS OTHERWISE STATED DEC. $\pm$ 0,3 ANGLES $\pm$ 1°			INS. DIA. RANGE ——//——		WIRE RANGE ——//——		SCALE ——//——	
									 TE Connectivity					
						DR. <i>Paulo</i> 01/01/84			DESCRIPTION .. AMP SHUNT CONNECTOR ASS'Y					
						CHK. <i>H</i> JUN 10 1984								
L4 REV. ECO 11-023509		HC	WLS	02DEC11		DE.			A3 DWG NO C 880584					
L3 REVISED PER ECO-11-005139		RK	HMR	28MAR11										
153 REVISION RECORD		DR	CHK	DATE		APP. <i>[Signature]</i> JUN 10 1984			SHEET 1072					

C 880584


C

B


A

DO NOT SCALE
DIMENSIONS IN mm

METRIC


3rd ANGLE PROJECTION

- 10 MATERIAL: HOUSING: TERMOPLASTICO C/ FIBRA DE VIDRO V-2 COR: VERDE
CONTATO: BRONZE FOSFOROSO
- MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-2 COLOR: GREEN
CONTACT: PHOSPHOROUS BRONZE
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



11 OBSOLETE	6			1	8
	5			1	7
	4			1	6
	3		2	1	5
	6			1	4
	5			1	3
11 OBSOLETE	4			1	2
	3		1	K1	1 - 880584 - 1

OTHER TREATMENT	FINISH	MATERIAL	PART REV.	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY				
TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0.5 ANGLES $\pm 1^\circ$		INS. DIA. RANGE	WIRE RANGE	SCALE
DR. <i>Isidor</i> CHK. <i>N. W. S.</i> DE. <i>[Signature]</i>		TE Connectivity		
DESCRIPTION AMP SHUNT CONNECTOR ASS'Y		SHEET 2 of 2		
DWG NO A3 C 880584				
REVISION	RECORD	DR	CHK	DATE