

## PRODUCT NUMBER

5 2 6 0 1 - X X X

PLATING

S=15 $\mu$ "[0.38 $\mu$ m]GOLD ON  
CONTACT AREA (NOTE 13)  
100 $\mu$ "[2.54 $\mu$ m]TIN ON TAIL  
G=30 $\mu$ "[0.76 $\mu$ m]GOLD ON  
CONTACT AREA (NOTE 13)  
100 $\mu$ "[2.54 $\mu$ m]TIN ON TAIL

- X X X

X X

X X

LF

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

A

A

B




B

C

C

D

D





RECOMMENDED BOARD LAYOUT

www.fciconnect.com			surface ISO 1302	tolerance ISO 406 ISO 1101	projection	MM
Dr	D.INGRAM	07/07/99	ANGULAR	0.X	± 0.30	size A4
Eng	L.GREEN	07/12/99	LINEAR	0.XX	± 0.13	Scale 1:1
Chr	L.GREEN	07/12/99		0.XXX	± 0.05	ECN N10-0327
Appr	L.GREEN	07/21/99	Product family	QUICKIE	Spec ref	
FCI			0.100/2.54MM LOW PROFILE SHROUDED VERTICAL HEADER			
catalog no			no	52601	Rev.	X
			dwg		CUSTOMER	sheet 2 of 3

PRODUCT No. NOTE 10	NO. OF POSITIONS	HSG. STYLE	POLARIZED POSITION	PACKAGING	POCKET PITCH	DIM M	DIM N
52601-S10-801T	2 X 5	B	01	TAPE-ON-REEL	0.787/20.00	1.260/32.00	0.790/20.07
52601-S10-805T	2 X 5	B	05	TAPE-ON-REEL	0.787/20.00	1.260/32.00	0.790/20.07
52601-S10-807T	2 X 5	B	07	TAPE-ON-REEL	0.787/20.00	1.260/32.00	0.790/20.07
52601-S14-807T	2 X 7	C	07	TAPE-ON-REEL	0.787/20.00	1.732/44.00	1.090/27.69
52601-S14-80714T	2 X 7	C	07,14	TAPE-ON-REEL	0.787/20.00	1.732/44.00	1.090/27.69
52601-X16-8T	2 X 8	D	-	TAPE-ON-REEL	0.787/20.00	1.732/44.00	1.090/27.69
52601-X20-8T	2 X 10	D	-	TAPE-ON-REEL	0.787/20.00	2.204/56.00	1.290/32.77
52601-X30-8T	2 X 15	D	-	TAPE-ON-REEL	0.787/20.00	2.834/72.00	1.786/45.37
52601-X40-8T	2 X 20	D	-	TAPE-ON-REEL	0.787/20.00	3.465/88.00	2.293/58.25

\* SPECIAL CUSTOMER



www.fciconnect.com			surface ISO 1302	tolerance ISO 406 ISO 1101		projection	MM
TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	D.INGRAM	07/07/99	ANGULAR	0.X	± 0.30	size A4	Scale 1:1
Eng	L.GREEN	07/12/99		0.XX	± 0.13		
Chr	L.GREEN	07/12/99	0° ± 2.0°	0.XXX	± 0.05	ECN	N10-0327
Appr	L.GREEN	07/21/99	Product family QUICKIE		Spec ref		
FCI			0.100/2.54MM LOW PROFILE SHROUDED VERTICAL HEADER		no 52601	Rev. X	
catalog no			CUST&#233;MER		sheet 3 of 3		