



SEE CHART


SDAE-3003-N*



3003-N * - *

BASE No. VOID CODE

No. OF CCTS. VERSION



No OF CCTS.	DIMn. A	DIMn. B
2	(5.08 ± 0.05) .200 ± .002	(9.91 ± 0.15) .390 ± .006
3	(10.16 ± 0.08) .400 ± .003	(14.99 ± 0.15) .590 ± .006
4	(15.24 ± 0.08) .600 ± .003	(20.07 ± 0.18) .790 ± .007
5	(20.32 ± 0.08) .800 ± .003	(25.15 ± 0.20) .990 ± .008
6	(25.40 ± 0.10) 1.000 ± .004	(30.23 ± 0.23) 1.190 ± .009
7	(30.48 ± 0.13) 1.200 ± .005	(35.31 ± 0.25) 1.390 ± .010
8	(35.56 ± 0.20) 1.400 ± .008	(40.39 ± 0.28) 1.590 ± .011
9	(40.64 ± 0.20) 1.600 ± .008	(45.47 ± 0.30) 1.790 ± .012
10	(45.72 ± 0.20) 1.800 ± .008	(50.55 ± 0.30) 1.990 ± .012
11	(50.80 ± 0.20) 2.000 ± .008	(55.63 ± 0.33) 2.190 ± .013
12	(55.88 ± 0.25) 2.200 ± .010	(60.71 ± 0.33) 2.390 ± .013
13	(60.96 ± 0.25) 2.400 ± .010	(65.79 ± 0.36) 2.590 ± .014
14	(66.04 ± 0.25) 2.600 ± .010	(70.87 ± 0.36) 2.790 ± .014
15	(71.12 ± 0.35) 2.800 ± .014	(75.95 ± 0.42) 2.990 ± .017
16	(76.20 ± 0.35) 3.000 ± .014	(81.03 ± 0.42) 3.190 ± .017
17	(81.28 ± 0.40) 3.200 ± .016	(86.11 ± 0.51) 3.390 ± .020
18	(86.36 ± 0.40) 3.400 ± .016	(91.19 ± 0.53) 3.590 ± .021
19	(91.44 ± 0.50) 3.600 ± .020	(96.27 ± 0.53) 3.790 ± .021
20	(96.52 ± 0.50) 3.800 ± .020	(101.35 ± 0.53) 3.990 ± .021

NOTES:

1. MATERIAL: WAFER, NYLON, 94V-2, COLOUR - NATURAL PINS, BRASS (FOR PLATING SEE CHARTS)
2. FOR DIMns. 'A','B','C','D','E','F' AND VERSIONS, SEE CHARTS ON SHEET 2 & SUBSEQUENT SHEETS.
3. FOR VERSIONS WITH VOIDS SEE SHEET 8.
4. PIN PUSH OUT FORCE: (1.36Kg)/3lbs MIN.
5. PIN MUST MEET MOLEX SOLDERABILITY SPEC. ES-152.
6. MAX BOW (0.38)/.015 OVER (25.4)/1.00

ADD PART NO SHT 7
EC NO: E2009-0320
DRWN: BMAGUIRE
CHKD:
APPR: BMAGUIRE
REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---
ANGULAR	± ---°	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY DATE

CHECKED BY DATE

APPROVED BY DATE

MATERIAL NO. SEE TABLES

SIZE A3

SCALE 1:1

DESIGN UNITS METRIC

THIRD ANGLE PROJECTION

TITLE 5.08 MM KK HDR VT RPIN

MOLEX MOLEX INCORPORATED

DOCUMENT NO. SDAE-3003-N*

SHEET NO. 1 OF 00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SEE CHART

SDAE-3003-N*

INDEX: FOR FULL DIMENSIONS SEE RELEVANT SHEET.

ENG. No.	PLATING	DIM. C	DIM. D	SHT. No.
AE-3003-NA	(102)			3
AE-3003-NAG	(501)	(11.94) / .470	(19.05) / .750	6
AE-3003-NA(503)	(503)			6
AE-3003-NB	(102)	(16.69) / .657	(23.80) / .937	3
AE-3003-NC	(102)			3
AE-3003-NCG	(501)	(23.04) / .907	(30.48) / 1.200	6
AE-3003-ND	(102)			3
AE-3003-NDG	(501)	(27.81) / 1.095	(34.92) / 1.375	6
AE-3003-NF	(102)			3
AE-3003-NFG	(501)	(32.56) / 1.282	(39.68) / 1.562	6
AE-3003-NI	(102)	(13.51) / .532	(20.32) / .800	4
AE-3003-NJ	(102)	(21.46) / .845	(28.58) / 1.125	4
AE-3003-NK	(102)			4
AE-3003-NS	(501)	(18.29) / .720	(25.40) / 1.000	7
AE-3003-NM	(102)	(11.89) / .468	(23.80) / .937	4
AE-3003-NU	(102)	(11.18) / .440	(17.45) / .687	4
AE-3003-NV	(102)	(11.94) / .470	(18.29) / .720	5
AE-3003-NY	(102)	(10.90) / .430	(17.45) / .687	5

FOR VOID VERSIONS SEE SHEET 8.

DOCUMENT ERROR

EC NO: E2009-0513

DRWN:BMAGUIRE

CHKD:

APPR:BMAGUIRE

REV

BM

QUALITY SYMBOLS

DESCRIPTION

▼=0

◻=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES

3 PLACES

2 PLACES

1 PLACE

ANGULAR ±---°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY

DATE

CHECKED BY

DATE

APPROVED BY

DATE

MATERIAL NO.

SEE CHART

SIZE

A3

SCALE

1:1

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

5.08 MM KK HDR VT RPIN

molex

MOLEX INCORPORATED

DOCUMENT NO.

SDAE-3003-N*

SHEET NO.

2 OF 08

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FOR PREVIOUS
DRAWING ISSUES
SEE MRI.

BK SEE SHEET 1.		REVISIONS		THIRD ANGLE PROJECTION		REVISE ONLY ON CAD SYSTEM		SH.	REV.												
				DIMENSIONS SHOWN (METRIC) INCH		CADCAM FILENAME SA3003X3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
				UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm 2^\circ$		DCN															
				INCH (METRIC)		GCH															
LTR		<table border="1"> <tr> <td>3 PLACE</td> <td>$\pm$</td> <td>.</td> <td></td> </tr> <tr> <td>2 PLACE</td> <td>$\pm$</td> <td>.</td> <td>$\pm$</td> </tr> <tr> <td>1 PLACE</td> <td></td> <td></td> <td>$\pm$</td> </tr> </table>		3 PLACE	$\pm$	.		2 PLACE	$\pm$	.	$\pm$	1 PLACE			$\pm$	CHK'D BY		TITLE 5.08 mm KK Hdr Vt RPIn			
				3 PLACE	$\pm$	.															
				2 PLACE	$\pm$	.	$\pm$														
				1 PLACE			$\pm$														
APP'D BY																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																					
LTR		<table border="1"> <tr> <td>DESIGN DIMENSION</td> <td>☒ (MM)</td> </tr> <tr> <td>(PRIMARY)</td> <td>☐ IN.</td> </tr> </table>		DESIGN DIMENSION	☒ (MM)	(PRIMARY)	☐ IN.	SCALE		 MOLEX EUROPE		SHEET NO. 30F	DATE 29/8 /86								
				DESIGN DIMENSION	☒ (MM)																
(PRIMARY)	☐ IN.																				
<table border="1"> <tr> <td>EQUIVALENT DIMENSION</td> <td>☐ (MM)</td> </tr> <tr> <td>(SECONDARY)</td> <td>☒ IN.</td> </tr> </table>		EQUIVALENT DIMENSION	☐ (MM)	(SECONDARY)	☒ IN.	PART NO. SEE CHART		DWG NO. SDAE-3003-N*		SIZE B											
		EQUIVALENT DIMENSION	☐ (MM)																		
(SECONDARY)	☒ IN.																				