



NOTES: 1. MATERIALS AND FINISHES: BODY & COUPLING NUT - BRASS, NICKEL PLATING CONTACT - BERYLLIUM COPPER, GOLD PLATING INSULATOR - PTFE GASKET - RUBBER 2. ELECTRICAL: A. IMPEDANCE: 75 OHM B. FREQUENCY RANGE: DC - 4 GHz C. RETURN LOSS: 28 dB MIN. 3. MECHANICAL: A. DURABILITY: 500 CYCLES MIN. B. TEMPERATURE RANGE: -65° C TO +165° C 4. PACKAGING: A. QUANTITY: SINGLE PACK B. MARKING: BAG TO BE MARKED "AMPHENOLRF, APH-BNCP-HDBNCJ, AND DATE CODE"	THIRD ANGLE PROJ. 		REVISIONS			
	REV	DESCRIPTION		DATE	ECO	APPR
	A	RELEASE TO MFG.		8/3/10	48170	CL



SCALE 2.000



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN S.LI	DATE 07-Jul-10	TITLE BNC PLUG TO HD-BNC JACK, 75 OHM ADAPTER		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER CLEMENT	DATE 29-Mar-10				
	REFERENCE EAR #	APPROVED S.HSIEH	DATE 18-Oct-10				
	CONFIGURATION LEVEL: =%%Z0HXIBIGC%=	CAD FILE	DWG SIZE B		REV A		DRAWING NO. APH-BNCP-HDBNCJ
	FINISH	Root Folder/BNC/APH-BNCP-HDBNCJ					
							PART NO. APH-BNCP-HDBNCJ