








Copyright FCI.





PRODUCT NO	METAL CLIP	REMARKS
10036355-002LF	2 PCS	NOTE ⑧ & ⑨
10036355-002CLF		NOTE ④, ⑧ & ⑨
10036355-002C-TRLF		NOTE ④, ⑥, ⑧ & ⑨



NOTE:
ALL OTHER DIMENSIONS, REFER TO SHEET 1.



RECOMMENDED PCB LAYOUT



PART WITH PICK-UP CAP, SEE NOTE ④

spec ref	-	dr	GL L00	2004-04-20	projection	MM	size	A3	scale	3:1
tolerance std	ISO 406 ISO 1101	eng	GL L00	2004-04-20	chr	GL L00	2010-10-28	ecn no	S10-0228	
surface	ISO 1302	appr	JOEY NG	2010-10-28	product family	SAS	rel level	-		
linear	0.X ± - 0.XX ±0.20 0.XXX ± -	angular	0° ±2°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 2 of 3		

NOTES:

1. MATERIAL :
1) HOUSING : HIGH TEMP THERMOPLASTIC,
UL 94V-0, COLOR BLACK
2) TERMINAL : COPPER ALLOY
3) HOLD DOWN : COPPER ALLOY
2. FINISH :
1) TERMINAL : 30µ" Au PLATING (CONTACT POINT) OVER 50µ" NICKEL
2) SOLDER TAIL : 100µ" MIN Sn OVER 50µ" NICKEL
3) HOLD DOWN : 100µ" MIN Sn OVER 50µ" NICKEL
- ③. PER SFF REV 1.1
- ④. PART WITH PICK-UP CAP, P/N XXXXXXXX-XXXC LF.
- ⑤. THE STD PACKAGING IS IN TRAY
- ⑥. FOR TAPE & REEL PACKAGING, SUFFIX "-TR" ADDED
P/N: XXXXXXXX-XXXC-TR LF
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN.
- ⑧. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ⑨. PART NUMBERS ENDING IN "LF" MEANS FOR NOTE 8 LEAD FREE IDENTIFICATION
THE EQUIVALENT P/N FOR "LF" DESIGNATION.

△H

(i) XXXXXXXX-XXXLF IS SAME AS XXXXXXXX-XXX



(ii) XXXXXXXX-XXXCLF IS SAME AS XXXXXXXX-XXXC

(iii) XXXXXXXX XXXC TRLF IS SAME AS XXXXXXXX XXXC TR
- △H

10. A △H SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

spec ref		-		dr		GL L00	2004-04-20	projection 	MM 	size	A3	scale	3:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		GL L00	2004-04-20			ecn no	S10-0228			
				chr		GL L00	2010-10-28							
ISO 406 ISO 1101					appr		JOEY NG	2010-10-28	product family		SAS		rel level	-
surface - 	linear	0.X		± -			title SAS RECEPTACLE VERTICAL SMT TYPE ASSY			dwg no	10036355			rev H
		0.XX		±0.20										
		0.XXX		± -										
ISO 1302		angular	0°		±2°		www.fci.com		cat. no.	-		Product - Customer Drw		sheet 3 of 3