

HAMAMATSU

COMPACT SIDE-ON PMT PHOTOSENSOR MODULES H9305 SERIES

The H9305 series photosensor modules contain a high-voltage power supply circuit and a 13-mm (1/2") diameter side-on photomultiplier tube in a compact aluminum housing. The 13-mm (1/2") side-on photomultiplier tube has a reflection mode photocathode that delivers high quantum efficiency at wavelengths above 600 nm, an adequate gain of up to 10^7 and fast time response. A high S/N ratio can be obtained even when measuring extremely low level light at high speeds.

The H9305 series uses a Cockcroft-Walton circuit with low power consumption. Five types are available according to the required spectral response range. Flexible cables are used for easy installation in equipment.



Product Variations

Type No.	Spectral Response	Features
H9305-01	185 nm to 750 nm	High sensitivity in UV to visible range
H9305-02	185 nm to 900 nm	For general applications in UV to near IR range
H9305-03	185 nm to 900 nm	High sensitivity in UV to near IR range
H9305-04	185 nm to 830 nm	Low dark current in UV to near IR range
H9305-05	185 nm to 650 nm	For general applications in UV to visible range

Specifications

Parameter			H9305 Series					Unit
Suffix			-01	-02	-03	-04	-05	—
Input Voltage			+11.5 to +15.5					V
Max. Input Voltage			+18					V
Max. Input Current			7					mA
Max. Output Signal Current			10					μA
Max. Control Voltage			+1.2 (Input impedance: 1 MΩ)					V
Recommended Control Voltage Adjustment Range			+0.25 to +1.0					V
Effective Area			3.7 × 13.0					mm
Sensitivity Adjustment Range			1: 10 ⁴					—
Peak Sensitivity Wavelength			420	400	450	530	340	nm
Cathode	Luminous Sensitivity	Min.	80	200	350	140	20	μA/lm
		Typ.	120	300	500	200	40	
	Blue Sensitivity Index (CS 5-58)		10	—	—	—	5	—
	Red/White Ratio		—	0.3	0.4	0.15	—	—
	Radiant Sensitivity *1		90	77	105	70	48	mA/W
Anode	Luminous Sensitivity *2	Min.	100	400	1000	300	50	A/lm
		Typ.	700	2000	2000	700	300	
	Radiant Sensitivity *1 *2		5.2 × 10 ⁵	5.2 × 10 ⁵	4.2 × 10 ⁵	2.5 × 10 ⁵	3.6 × 10 ⁵	A/W
	Dark Current *2 *3	Typ.	1	1	2	0.1	0.5	nA
Max.		10	10	10	1	5		
Rise Time *2			1.4					ns
Ripple Noise *2 *4 (peak to peak)		Max.	0.5					mV
Settling Time *5			10					s
Operating Ambient Temperature			+5 to +50					°C
Storage Temperature			-20 to +50					°C
Weight			110					g

*1: Measured at the peak sensitivity wavelength *2: Control voltage = +1.0 V *3: After 30 minutes storage in darkness




*4: Cable RG-174/U, Cable length 450 mm, Load resistance = 1 MΩ, Load capacitance = 22 pF

*5: The time required for the output to reach a stable level following a change in the control voltage from +1.0 V to +0.5 V.

Subject to local technical requirements and regulations, availability of products included in this promotional material may vary. Please consult with our sales office. Information furnished by HAMAMATSU is believed to be reliable. However, no responsibility is assumed for possible inaccuracies or omissions. Specifications are subject to change without notice. No patent rights are granted to any of the circuits described herein. ©2003 Hamamatsu Photonics K.K.


COMPACT SIDE-ON PMT PHOTOSENSOR MODULES H9305 SERIES

Characteristics (Cathode radiant sensitivity, PMT gain)




Sensitivity Adjustment Method

Voltage Programming




- Adjust the control voltage to adjust the sensitivity.
- Electrically insulate the reference voltage output.

Resistance Programming




When using a potentiometer, adjust sensitivity while monitoring the control voltage.

Dimensional Outlines (Unit: mm)



TPMOA0013ED



TPMOA0018ED

HAMAMATSU

HOME PAGE URL <http://www.hamamatsu.com>

HAMAMATSU PHOTONICS K.K., Electron Tube Center

314-5, Shimokanzo, Toyooka-village, Iwata-gun, Shizuoka-ken, 438-0193, Japan, Telephone: (81)539/62-5248, Fax: (81)539/62-2205

U.S.A.: Hamamatsu Corporation: 360 Foothill Road, P. O. Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1)908-231-0960, Fax: (1)908-231-1218 E-mail: usa@hamamatsu.com

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-2658 E-mail: info@hamamatsu.de

France: Hamamatsu Photonics France S.A.R.L.: 8, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 00, Fax: (33)1 69 53 71 10 E-mail: infos@hamamatsu.fr

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road Welwyn Garden City Hertfordshire AL7 1BW, United Kingdom, Telephone: 44-(0)1707-294888, Fax: 44-(0)1707-325777 E-mail: info@hamamatsu.co.uk

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen 12, SE-171-41 SOLNA, Sweden, Telephone: (46)8-509-031-00, Fax: (46)8-509-031-01 E-mail: info@hamamatsu.se

Italy: Hamamatsu Photonics Italia: S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39)02-935 81 733, Fax: (39)02-935 81 741 E-mail: info@hamamatsu.it

TPMO1030E01
NOV. 2003 IP