



Photoelectric sensors
W12-3, Photoelectric proximity sensor,
Background suppression

WTB12-3P2431



SICK
Sensor Intelligence.

Model Name > [WTB12-3P2431](#)Part No. > [1041411](#)**At a glance**

- State of the art technology provides precise background suppression
- Withstands harsh environments
- PinPoint LED technology with highly visible light spot; variants available with IR LED for highly critical applications
- Rugged die-cast zinc housing, with optional Teflon® coating
- Versatile mounting options due to dovetail mounting - mounting holes and oblong holes
- Highly visible status LEDs
- Sensing range adjustment with potentiometer or teach-in pushbutton
- IO-Link communication available (optional)

Your benefits

State of the art technology, e.g. OES3 provides precise background suppression and reliable detection of challenging objects

High immunity to ambient light, optical reflections and crosstalk ensures fewer false readings and less downtime

PinPoint LED technology provides a highly visible light spot that enables quick and easy sensor alignment

Highly visible status LEDs simplify sensing distance adjustments and reduce installation time

A rugged metal housing withstands high-pressure cleaners and cleaning agents, reducing downtime

Complementary outputs in one housing reduce inventory and procurement costs

IO-Link enables quick remote diagnostics and maintenance (optional)

Easy installation using SICK accessories

**Features**

Dimensions (W x H x D):	15.6 mm x 48.5 mm x 42 mm ¹⁾
Sensing range max.:	20 mm ... 350 mm ¹⁾
Sensing range:	20 mm ... 350 mm
Housing design (light emission):	Rectangular ²⁾
Light source:	LED
Type of light:	Visible red light

Wave length:	640 nm
Sensitivity adjustment:	Potentiometer, 5-turn
Sensor/detection principle:	Photoelectric proximity sensor, Background suppression
Light spot (distance):	6 mm (200 mm)


¹⁾ Object with 90 % reflectance (referred to standard white DIN 5033) ²⁾ Average service life 100,000 h at Ta = +25 °C

Mechanics/electronics

Enclosure rating:	IP 66 IP 67 IP 69K
Supply voltage:	10 V DC ... 30 V DC ¹⁾
Residual ripple:	≤ 5 Vpp ²⁾
Power consumption:	≤ 45 mA ³⁾
Switching output:	PNP, light/dark-switching, Complementary
Output current Imax.:	100 mA
Response time:	≤ 330 µs ⁴⁾
Switching frequency:	1,500 Hz ⁵⁾
Connection type:	Connector M12, 4-pin
Protection class:	II
Circuit protection:::	A, C, D ^{6) 7) 8)}
Weight:	120 g
Ambient operating temperature:	-40 °C ... 60 °C
Ambient storage temperature:	-40 °C ... 75 °C
Signal voltage PNP HIGH/LOW:	> U _U - 2,5 V/ca. 0 V
Special device:	-
UL File-No.:	UL No. NRKH.E181493 & cUL No. NRKH7.E181493


¹⁾ Limit values, operation in short-circuit protected network max. 8 A ²⁾ May not exceed or fall short of V_S ³⁾ Without load ⁴⁾ Signal transit time with resistive load ⁵⁾ With light/dark ratio 1:1 ⁶⁾ A = V_S connections reverse-polarity protected ⁷⁾ C = interference suppression ⁸⁾ D = outputs overcurrent and short-circuit protected

Dimensional drawing




- [1] Standard direction of the material being scanned
- [2] Optical axis, receiver
- [3] Optical axis, sender
- [4] Status indicator LED green: supply voltage active
- [5] Status indicator LED, yellow: Status of received light beam
- [6] M4 threaded mounting hole, 4 mm deep
- [7] Mounting hole, Ø 4.2 mm
- [8] Scanning distance adjustment, double Teach button
- [9] Connection

Einstell-Möglichkeiten




- [3] Status indicator LED, yellow: Status of received light beam
- [4] Status indicator LED green: supply voltage active
- [7] Sensing distance adjustment: Poti


Connection diagram




Connection type



Characteristic curve



Sensing range diagram



1 Scanning distance on black, 6 % Remission

2 Scanning distance on grey, 18 % Remission

3 Scanning on white, 90 % Remission

Australia	Österreich
Phone +61 3 9497 4100	Phone +43 (0)22 36 62 28 8-0
1800 334 802 – tollfree	E-Mail office@sick.at
E-Mail sales@sick.com.au	
Belgium/Luxembourg	Polka
Phone +32 (0)2 466 55 66	Phone +48 22 837 40 50
E-Mail info@sick.be	E-Mail info@sick.pl
Brasil	România
Phone +55 11 3215-4900	Phone +40 356 171 120
E-Mail sac@sick.com.br	E-Mail office@sick.ro
Canada	Russia
Phone +1(952) 941-6780	Phone +7 495 775 05 30
1 800-325-7425 – tollfree	E-Mail info@sick.ru
E-Mail info@sickusa.com	
Ceská Republika	Schweiz
Phone +420 2 57 91 18 50	Phone +41 41 619 29 39
E-Mail sick@sick.cz	E-Mail contact@sick.ch
China	Singapore
Phone +852-2763 6966	Phone +65 6744 3732
E-Mail ghk@sick.com.hk	E-Mail admin@sicksgp.com.sg
Danmark	South Africa
Phone +45 45 82 64 00	Phone +27 11 472 3733
E-Mail sick@sick.dk	E-Mail info@sickautomation.co.za
Deutschland	South Korea
Phone +49 211 5301-301	Phone +82-2 786 6321/4
E-Mail kundenservice@sick.de	E-Mail info@sickkorea.net
España	Slovenija
Phone +34 93 480 31 00	Phone +386 (0)1-47 69 990
E-Mail info@sick.es	E-Mail office@sick.si
France	Suomi
Phone +33 1 64 62 35 00	Phone +358-9-25 15 800
E-Mail info@sick.fr	E-Mail sick@sick.fi
Great Britain	Sverige
Phone +44 (0)1727 831121	Phone +46 10 110 10 00
E-Mail info@sick.co.uk	E-Mail info@sick.se
India	Taiwan
Phone +91-22-4033 8333	Phone +886 2 2375-6288
E-Mail info@sick-india.com	E-Mail sales@sick.com.tw
Israel	Türkiye
Phone +972-4-999-0590	Phone +90 216 528 50 00
E-Mail info@sick-sensors.com	E-Mail info@sick.com.tr
Italia	United Arab Emirates
Phone +39 02 27 43 41	Phone +971 4 8865 878
E-Mail info@sick.it	E-Mail info@sick.ae
Japan	USA/México
Phone +81 (0)3 3358 1341	Phone +1(952) 941-6780
E-Mail support@sick.jp	1 800-325-7425 – tollfree
Magyarország	E-Mail info@sickusa.com
Phone +36 1 371 2680	
E-Mail office@sick.hu	
Nederland	
Phone +31 (0)30 229 25 44	
E-Mail info@sick.nl	
Norge	
Phone +47 67 81 50 00	
E-Mail austefjord@sick.no	

More representatives and agencies
at www.sick.com



Sensor Intelligence.