



Series 53TP

25-50Amp • 240/480 Vac • 3 PHASE

- **SCR Output**
- **LED Status Indicator**
- **Protective Cover Available**
(Part No. KS300)
- **Panel Mount**
- **Integrated Overvoltage Protection by Automatic Self Turn-On (Suffix P)**

Three-phase solid state relays switch up to 530 Vrms directly to loads such as motors, transformers, heating elements, etc. Available with either AC or DC input (coil) control in zero-voltage or random turn-on switching versions.

Manufactured in Crydom's ISO 9001 Certified facility for optimum product performance and reliability.

	MODEL NUMBERS	D53TP25D	D53TP50D	A53TP25D	A53TP50D
OUTPUT SPECIFICATIONS ①					
Operating Voltage (47-63 Hz) [Vrms]		48-530	48-530	48-530	48-530
Load Current Range③ [Arms]		.05-25	.05-50	.05-25	.05-50
Transient Overvoltage [Vpk]		1200	1200	1200	1200
Max. Surge Current, (16.6ms) [Apk]		250	625	250	625
Max. On-State Voltage Drop @ Rated Current [Vpk]		1.6	1.6	1.6	1.6
Thermal Resistance Junction to Case (R _{θJC}) [°C/W]		1.02	.63	1.02	.63
Maximum I ² t for Fusing, (8.3 msec.) [A ² sec]		260	1620	260	1620
Max. Off-State Leakage Current @ Rated Voltage [mArms]		10	10	10	10
Min. Off-State dv/dt @ Max. Rated Voltage [V/μsec]②		500	500	500	500
Max. Turn-On Time ④		1/2 Cycle	1/2 Cycle	10.0 msec	10.0 msec
Max. Turn-Off Time		1/2 Cycle	1/2 Cycle	40.0 msec	40.0 msec
Power Factor (Min.) with Max. Load		0.5	0.5	0.5	0.5

INPUT SPECIFICATIONS ①

DC CONTROL

AC CONTROL

Control Voltage Range	3-32 Vdc	90-280 Vrms (60Hz)
Max. Turn-On Voltage	3.0 Vdc	90 Vrms
Min. Turn-Off Voltage	1.0 Vdc	10 Vrms
Nominal Input Impedance	450 Ohms	54.8k Ohms
Typical Input Current	10mA @ 5 Vdc	2.2mA @ 120 Vrms, 4.4mA @ 240 Vrms

GENERAL NOTES

©2001 CRYDOM CORP, Specifications subject to change without notice.

- ① All parameters at 25°C and per section unless otherwise specified.
 ② Off-State dv/dt test method per EIA/NARM standard RS-443, paragraph 13.11.1
 ③ Heat sinking required, for derating curves see page 2.
 ④ Turn-on time for random turn-on versions is 0.02 msec (DC Control Models).

For recommended applications and more information contact:
USA: Sales Support (877) 502-5500 **Tech Support** (877) 702-7700 **FAX** (619) 710-8540
 Crydom Corp, 2320 Paseo de las Americas, Ste. 201, San Diego, CA 92154
Email: sales@crydom.com **WEB SITE:** http://www.crydom.com
UK: +44 (0)1202 365070 • **FAX** +44 (0)1202 365090 Crydom International Ltd., 7 Cobham
 Road, Ferndown Industrial Estate, Ferndown, Dorset BH21 7PE, **Email:** intsales@crydom.com.
GERMANY: +49 (0)180 3000 506



CRYDOM

Control over power

Series 53TP

25-50Amp • 240/480 Vac • 3 PHASE

GENERAL SPECIFICATIONS

Dielectric Strength 50/60Hz Input/Output/Base 4000 Vrms

Insulation Resistance (Min.) @ 500 Vdc 10^9 Ohm

Max. Capacitance Input/Output 8 pF

Ambient Operating Temperature Range -40 to 80°C

Ambient Storage Temperature Range -40 to 125°C

MECHANICAL SPECIFICATIONS

Weight: (typical) 10.3 oz. (315g)

Encapsulation: Thermally Conductive Epoxy

Terminals: Screws and Saddle Clamps Furnished


AVAILABLE OPTIONS

-10 Non-Zero Cross,
Instantaneous Turn-On
Example: D53TP50D-10


DP 2 Controlled, 1 Linked (A1-A2)
Example: D53DP50D

P Internal Overvoltage Protection.
Relay Will Self Trigger Between
900-1200 Vpk. Not Suitable For
Capacitive Loads.
Agencies Approval Pending.
Example: D53TP50DP

Crydom Heat Sinks offer excellent
thermal management and are per-
fectly matched to the load current
ratings of Crydom panel mount
relays. Request Crydom's Heat Sink
specification sheet for all the details.



CURRENT DERATING CURVES



APPROVALS

UL E116950
CSA LR81689
VDE 5941 UG



FastFax Document No.161
SERIES53TP
Rev. 011602
PAGE 2 OF 2

©2001 CRYDOM CORP, Specifications subject to change without notice.

For recommended applications and more information contact:

USA: Sales Support (877) 502-5500 Tech Support (877) 702-7700 FAX (619) 710-8540

Crydom Corp, 2320 Paseo de las Americas, Ste. 201, San Diego, CA 92154

Email: sales@crydom.com WEB SITE: <http://www.crydom.com>

UK: +44 (0)1202 365070 • FAX +44 (0)1202 365090 Crydom International Ltd., 7 Cobham

Road, Ferndown Industrial Estate, Ferndown, Dorset BH21 7PE, Email: intsales@crydom.com.

GERMANY: +49 (0)180 3000 506

