

**HDC insert
HDC HD 7 MC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The HD range features a high density of contacts. It is thus optimally suited for signal processing.

The wire connection level is designed as a crimp contact. The established crimp connection has been used as a standard for decades.

Crimp contacts are not delivered with the inserts.

Number of poles: **7 - 8**

Rated current: **10 A**

Rated voltage: **42/250 V**

Nominal voltage acc. to UL/CSA: **600 V AC/DC**

Crimp connection

General ordering data

Order No.	1650570000
Type	HDC HD 7 MC
Version	HDC insert, Male, 250 V, 10 A, No. of poles: 7, Crimp connection, Size: 1
GTIN (EAN)	4008190870942
Qty.	1 pc(s).

HDC insert HDC HD 7 MC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data

Dimensions

Length	21 mm	Width	21 mm
Height	34 mm		

Dimensions

Height of plug	34 mm	Total length base	21 mm
----------------	-------	-------------------	-------

General data

Size	1	Series	HD
Rated voltage (DIN EN 61984)	250 V	Rated voltage according to UL/CSA	600 V AC/DC
Rated impulse voltage (DIN EN 61984)	4 kV	Rated current (DIN EN 61984)	10 A
Flammability class UL 94	V-0	Insulating material group	IIIa
Insulation resistance	$10^{10} \Omega$	Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)
No. of poles	7	Plugging cycles, silver	≥ 500
Plugging cycles, gold	≥ 500	Pollution severity	3
Type	Male		

Connection data PE

Stripping length PE connection	10 mm	Wire connection cross-section, finely stranded, min.	0.5 mm ²
Wire connection cross section, finely stranded, max.	2.5 mm ²	Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	2.5 mm ²	Wire connection cross section AWG, min.	AWG 26
Wire connection cross section AWG, max.	AWG 14	Wire cross-section, solid, min.	0.5 mm ²
Wire cross-section, solid, max.	2.5 mm ²	Connection type PE	Screw connection
Tightening torque, min. PE connection	1.2 Nm	Tightening torque, max. PE connection	1.5 Nm
Rated cross-section	2.5 mm ²	Fixing screw	M 4
Blade size, crosshead	PZ1 size	Blade size, slotted (PE connection)	SD 0,6 x 3,5, SD 0,8 x 4,0

Rating data

Rated current (DIN EN 61984)	10 A	Rated impulse voltage (DIN EN 61984)	4 kV
Rated voltage (DIN EN 61984)	250 V	Rated voltage according to UL/CSA	600 V AC/DC

Version

Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Stripping length, rated connection	8 mm	Type of connection	Crimp connection
Size	1	Volume resistance	$\leq 4 \text{ m}\Omega$
Surface finish	Silver passivated, gold	Material	Copper alloy

Classifications

ETIM 2.0	EC001121	ETIM 3.0	EC001121
UNSPSC	30-21-18-01	eClass 4.1	27-14-08-05
eClass 5.1	27-14-34-19	eClass 6.0	27-26-12-04
eClass 7.0	27-44-02-05		

Data sheet...

**HDC insert
HDC HD 7 MC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Product information

Descriptive text technical data	HD 7 insert with protective earth connection only via the plug/socket contact.
Descriptive text accessories	Accessories, see chapter J - Tools, see chapter K
Description of article	For turned contacts
Product description	For turned contacts

Approvals

Approvals

