


4		3		2		1					
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		REVISIONS							
© COPYRIGHT -- By --		ALL RIGHTS RESERVED.		P	LTR	DESCRIPTION	DATE	DWN	APVD		
					N1	REVISED PER ECO-11-004917	11MAR11	RK	HMR		
					N2	REVISED PER ECO-17-006294	10OCT2017	RS	DR		
INSULATION BODY  13.081 [.515] MAX 1 USE FOR AN UNSTRIPPED (SINGLE) WIRE END ONLY. 2 WIRE INSUL, Ø1.219-1.905[Ø.048-.075]											
						1000		LOOSE PIECE		324484	
						QTY		PACKAGE TYPE		PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 14FEB95		 TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: -		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		APVD T MICHIELUTTI 14FEB95		NAME SPARE WIRE CAP, TRANSPARENT .048-.075 INSULATION	
FOR ORDER ENTRY		1-800-526-5142		CIRCULAR MIL AREA: -		MATERIAL BODY, CU PER ASTM B152 INSUL, NYLON, COLOR, TRANSPARENT		FINISH BODY, TIN PLATE PER ASTM B545		PRODUCT SPEC -	
						APPLICATION SPEC -		WEIGHT -		RESTRICTED TO -	
						CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1	
								REV N2			