










RECOMMENDED MODULE LAYOUT



TYPE "R"	3.3 VOLT.
TYPE "L"	2.5 VOLT.
TYPE "C"	1.8 VOLT.
CENTER KEY	DESCRIPTION

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.38/.015	projection		title DDR 184P .050" 1-ROW, V/T ASS'Y METAL CLIP(FOR DELL)	
A					.XX ± 0.25/.010				
					.XXX ± 0.15/.005				
				angles	0° ±2°	MM		product family DDR	
				dr	Desmond Hu 10/16/03			code DG	
				engr	Desmond Hu 10/16/03			size dwg no	
				chr	Desmond Hu 10/16/03	scale 1.5:1	A4	10035612	
				appd	Joseph Hsia 10/16/03				
sheet index	revision sheet							cage code	



DDR ASSEMBLY PART NUMBER
10035612 - ☐ ☐ ☐ ☐

RECOMMENDED CIRCUIT BOARD HOLE LAYOUT

STYLE

- 1 : FOR 3.3 VOLT.
- 2 : FOR 2.5 VOLT.
- 3 : FOR 1.8 VOLT.

METAL CLIP

1 : WITH METAL CLIP + DIM."D"=4.00/.157.

TAIL LENGTH


CODE	DIM. "B"	DIM. "C"
0	2.59 .102	2.44 .096
1	3.35 .132	3.20 .126

PLATING

CODE	CONTACT	SOLDERTAIL	UNDERPLATE	CODE	CONTACT	SOLDERTAIL	UNDERPLATE
2	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. TIN/LEAD	50μ"(1.27μm) MIN. NICKEL OVERALL	7LF	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. 100%TIN	50μ"(1.27μm) MIN. NICKEL OVERALL
3	30μ"(0.76μm) MIN. GOLD			8LF	30μ"(0.76μm) MIN. GOLD		
4	GOLD FLASH			9LF	GOLD FLASH		

COLOR OF HOUSING AND EJECTOR

- 0 : BLACK HOUSING + IVORY EJECTOR
- 3 : BLACK HOUSING + BLACK EJECTOR

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.38/.015	projection	title		
D					.XX ± 0.25/.010		DDR 184P .050" 1-ROW, V/T ASS'Y METAL CLIP(FOR DELL)		
					.XXX ± 0.15/.005				
				angles	0° ±2°				
				dr	Desmond Hu		10/16/03	product family DDR	
				engr	Desmond Hu		10/16/03	code DG	
				chr	Desmond Hu	10/16/03	size dwg no		
				appd	Joseph Hsia	10/16/03	scale 1.5:1		
sheet index	revision sheet						A4 10035612		
							sheet 3 of		