




All dimensions are in mm; tolerances acc. ISO 2768 m-H

Documents

Assembly instruction

29 E

Panel piercing

B 31

Material and plating

Connector parts

Body

Material

Brass

Crimping sleeve

Copper

Plating

Gold, 0.1 µm min.

Gold, 0.1 µm min.

Environmental data

RoHS

compliant

Tooling

Crimping tool

11W150-000

Crimp insert

11W150-102

MCX

CABLE CLAMP

29Z101-102F**Suitable cables**

RG 316 /U, RG 174 A/U, RG 188 A/U

Weight

Weight

0.61 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	07/09/04	Sa. Krautenbacher	13.03.14	c00	14-0352	T. Krojer	13.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de		Page 2 / 2