

CentralTM Semiconductor Corp.

145 Adams Avenue, Hauppauge, NY 11788 USA

Tel: (631) 435-1110 • Fax: (631) 435-1824

Manufacturers of World Class Discrete Semiconductors

PMD1600K SERIES NPN

PMD1700K SERIES PNP

COMPLEMENTARY SILICON POWER
DARLINGTON TRANSISTOR

JEDEC TO-3 CASE

DESCRIPTION

The CENTRAL SEMICONDUCTOR PMD1600K, 1700K Series types are Complementary Silicon Darlington Power Transistors manufactured by the epitaxial-base process, mounted in a hermetically sealed metal package, designed for power switching applications. These devices are designed to be electrical/mechanical equivalents Lambda part numbers.

MAXIMUM RATINGS ($T_C=25^\circ\text{C}$)

	SYMBOL	PMD1601K PMD1701K	PMD1602K PMD1702K	PMD1603K PMD1703K	UNIT
Collector-Base Voltage	V_{CB0}	60	80	100	V
Collector-Emitter Voltage	V_{CE0}	60	80	100	V
Emitter-Base Voltage	V_{EB0}	5.0	5.0	5.0	V
Collector Current	I_C	20	20	20	A
Collector Current (PEAK)	I_{CM}	40	40	40	A
Base Current	I_B	0.5	0.5	0.5	A
Power Dissipation	P_D	180	180	180	W
Operating and Storage Junction Temperature	T_J, T_{stg}	-65 TO +200			$^\circ\text{C}$
Thermal Resistance	θ_{JC}	0.97			$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_C=25^\circ\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	MAX	UNIT
I_{CER}	$V_{CE}=.67 \times \text{Rated } V_{CE0}, R_{BE}=2.2K\Omega$		7.0	mA
I_{EB0}	$V_{EB}=5.0V$		3.0	mA
BV_{CER}	$I_C=100mA, R_{BE}=2.2K\Omega$ (PMD1601K, 1701K)	60		V
BV_{CER}	$I_C=100mA, R_{BE}=2.2K\Omega$ (PMD1602K, 1702K)	80		V
BV_{CER}	$I_C=100mA, R_{BE}=2.2K\Omega$ (PMD1603K, 1703K)	100		V
BV_{CE0}	$I_C=100mA$ (PMD1601K, 1701K)	60		V
BV_{CE0}	$I_C=100mA$ (PMD1602K, 1702K)	80		V
BV_{CE0}	$I_C=100mA$ (PMD1603K, 1703K)	100		V
$V_{CE(SAT)}$	$I_C=10A, I_B=40mA$		2.0	V
$V_{BE(SAT)}$	$I_C=10A, I_B=40mA$		2.8	V
$V_{BE(ON)}$	$V_{CE}=3.0V, I_C=10A$		2.8	V
h_{FE}	$V_{CE}=3.0V, I_C=10A$	750	20,000	
h_{fe}	$V_{CE}=3.0V, I_C=7.0A, f=1.0kHz$	300	-	
f_T	$V_{CE}=3.0V, I_C=7.0A, f=1.0MHz$	4.0		MHz
C_{ob}	$V_{CB}=10V, I_E=0, f=1.0MHz$		400	pF