- **Function, Pinout, and Drive Compatible With FCT and F Logic**
- **Reduced V_{OH} (Typically = 3.3 V) Versions of Equivalent FCT Functions**
- **Edge-Rate Control Circuitry for Significantly Improved Noise Characteristics**
- **I_{off} Supports Partial-Power-Down Mode Operation**
- **ESD Protection Exceeds JESD 22**
  - **2000-V Human-Body Model (A114-A)**
  - **200-V Machine Model (A115-A)**
  - **1000-V Charged-Device Model (C101)**
- **Matched Rise and Fall Times**
- **Fully Compatible With TTL Input and Output Logic Levels**
- **CY54FCT540T**
  - **48-mA Output Sink Current**
  - **12-mA Output Source Current**
- **CY74FCT540T**
  - **64-mA Output Sink Current**
  - **32-mA Output Source Current**
- **3-State Outputs**

CY54FCT540T . . . D PACKAGE
CY74FCT540T . . . Q PACKAGE
(TOP VIEW)



CY54FCT540T . . . L PACKAGE
(TOP VIEW)



description

The ’FCT540T inverting buffers/line drivers can be employed as memory address drivers, clock drivers, and bus-oriented transmitters/receivers. These devices provide speed and drive capabilities equivalent to their fastest bipolar-logic counterparts, while reducing power dissipation. The input and output voltage levels allow direct interface with TTL, NMOS, and CMOS devices without external components.

These devices are fully specified for partial-power-down applications using I_{off}. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

ORDERING INFORMATION

T_A	PACKAGE†		SPEED (ns)	ORDERABLE PART NUMBER	TOP-SIDE MARKING
–40°C to 85°C	QSOP – Q	Tape and reel	4.1	CY74FCT540CTQCT	FCT540C
–55°C to 125°C	CDIP – D	Tube	4.7	CY54FCT540CTDMB	
	LCC – L	Tube	4.7	CY54FCT540CTLMB	

† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 2001, Texas Instruments Incorporated
On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

FUNCTION TABLE

INPUTS			OUTPUT
$\overline{OE}_A$	$\overline{OE}_B$	D	$\overline{O}$
L	L	L	H
L	L	H	L
H	H	X	Z

H = High logic level, L = Low logic level,
X = Don't care, Z = High-impedance state

logic diagram (positive logic)



absolute maximum rating over operating free-air temperature range (unless otherwise noted)†

Supply voltage range to ground potential . . . . . –0.5 V to 7 V
DC input voltage range . . . . . –0.5 V to 7 V
DC output voltage range . . . . . –0.5 V to 7 V
DC output current (maximum sink current/pin) . . . . . 120 mA
Package thermal impedance, θ_{JA} (see Note 1): Q package . . . . . 68°C/W
Ambient temperature range with power applied, T_A . . . . . –65°C to 135°C
Storage temperature range, T_{stg} . . . . . –65°C to 150°C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The package thermal impedance is calculated in accordance with JESD 51-7.

recommended operating conditions (see Note 2)

		CY54FCT540T			CY74FCT540T			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V_{CC}	Supply voltage	4.5	5	5.5	4.75	5	5.25	V
V_{IH}	High-level input voltage	2			2			V
V_{IL}	Low-level input voltage			0.8			0.8	V
I_{OH}	High-level output current			–12			–32	mA
I_{OL}	Low-level output current			48			64	mA
T_A	Operating free-air temperature	–55		125	–40		85	°C

NOTE 2: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS			CY54FCT540T			CY74FCT540T			UNIT
				MIN	TYP†	MAX	MIN	TYP†	MAX	
V_{IK}	V_{CC} = 4.5, V	I_{IN} = –18 mA			–0.7	–1.2				V
	V_{CC} = 4.75 V,	I_{IN} = –18 mA						–0.7	–1.2	
V_{OH}	V_{CC} =4.5 V,	I_{OH} = –12 mA		2.4	3.3					V
	V_{CC} = 4.75 V	I_{OH} = –32 mA					2			
		I_{OH} = –15 mA					2.4	3.3		
V_{OL}	V_{CC} = 4.5 V,	I_{OL} = 48 mA			0.3	0.55				V
	V_{CC} = 4.75 V,	I_{OL} = 64 mA						0.3	0.55	
V_{hys}	All inputs				0.2			0.2		V
I_I	V_{CC} = 5.5 V,	V_{IN} = V_{CC}				5				µA
	V_{CC} = 5.25 V,	V_{IN} = V_{CC}							5	
I_{IH}	V_{CC} = 5.5 V,	V_{IN} = 2.7 V				±1				µA
	V_{CC} = 5.25 V,	V_{IN} = 2.7 V							±1	
I_{IL}	V_{CC} = 5.5 V,	V_{IN} = 0.5 V				±1				µA
	V_{CC} = 5.25 V,	V_{IN} = 0.5 V							±1	
I_{OZH}	V_{CC} = 5.5 V,	V_{OUT} = 2.7 V				10				µA
	V_{CC} = 5.25 V,	V_{OUT} = 2.7 V							10	
I_{OZL}	V_{CC} = 5.5 V,	V_{OUT} = 0.5 V				–10				µA
	V_{CC} = 5.25 V,	V_{OUT} = 0.5 V							–10	
I_{OS}‡	V_{CC} = 5.5 V,	V_{OUT} = 0 V		–60	–120	–225				mA
	V_{CC} = 5.25 V,	V_{OUT} = 0 V					–60	–120	–225	
I_{off}	V_{CC} = 0 V,	V_{OUT} = 4.5 V				±1			±1	µA
I_{CC}	V_{CC} = 5.5 V,	V_{IN} ≤ 0.2 V,	V_{IN} ≥ V_{CC} – 0.2 V		0.1	0.2				mA
	V_{CC} = 5.25 V,	V_{IN} ≤ 0.2 V,	V_{IN} ≥ V_{CC} – 0.2 V					0.1	0.2	
ΔI_{CC}	V_{CC} = 5.5 V, V_{IN} = 3.4 V§, f_1 = 0, Outputs open				0.5	2				mA
	V_{CC} = 5.25 V, V_{IN} = 3.4 V§, f_1 = 0, Outputs open							0.5	2	
I_{CCD}¶	V_{CC} = 5.5 V, 50% duty cycle, Outputs open, One bit switching at f_1 = 10 MHz, $\overline{OE}_A$ = $\overline{OE}_B$ = GND or $\overline{OE}_A$ = GND and $\overline{OE}_B$ = V_{CC}, V_{IN} ≤ 0.2 V or V_{IN} ≥ V_{CC} – 0.2 V				0.06	0.12				mA/ MHz
	V_{CC} = 5.25 V, 50% duty cycle, Outputs open, One bit switching at f_1 = 10 MHz, $\overline{OE}_A$ = $\overline{OE}_B$ = GND or $\overline{OE}_A$ = GND and $\overline{OE}_B$ = V_{CC}, V_{IN} ≤ 0.2 V or V_{IN} ≥ V_{CC} – 0.2 V							0.06	0.12	

† Typical values are at V_{CC} = 5 V, T_A = 25°C.

‡ Not more than one output should be shorted at a time. Duration of short should not exceed one second. The use of high-speed test apparatus and/or sample-and-hold techniques are preferable to minimize internal chip heating and more accurately reflect operational values. Otherwise, prolonged shorting of a high output can raise the chip temperature well above normal and cause invalid readings in other parametric tests. In any sequence of parameter tests, I_{OS} tests should be performed last.

§ Per TTL-driven input (V_{IN} = 3.4 V); all other inputs at V_{CC} or GND

¶ This parameter is derived for use in total power-supply calculations.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted) (continued)

PARAMETER	TEST CONDITIONS			CY54FCT540T			CY74FCT540T			UNIT
				MIN	TYP†	MAX	MIN	TYP†	MAX	
I_C#	V_{CC} = 5.5 V, Outputs open, $\overline{OE}_A$ = $\overline{OE}_B$ = GND or $\overline{OE}_A$ = GND and $\overline{OE}_B$ = V_{CC}	One bit switching at f_1 = 10 MHz at 50% duty cycle	$V_{IN} \le 0.2$ V or $V_{IN} \ge V_{CC} - 0.2$ V		0.7	1.4				mA
			V_{IN} = 3.4 V or GND		1	2.4				
		Eight bits switching at f_1 = 2.5 MHz at 50% duty cycle	$V_{IN} \le 0.2$ V or $V_{IN} \ge V_{CC} - 0.2$ V		1.3	2.6‖				
			V_{IN} = 3.4 V or GND		3.3	10.6‖				
	V_{CC} = 5.25 V, Outputs open, $\overline{OE}_A$ = $\overline{OE}_B$ = GND or $\overline{OE}_A$ = GND and $\overline{OE}_B$ = V_{CC}	One bit switching at f_1 = 10 MHz at 50% duty cycle	$V_{IN} \le 0.2$ V or $V_{IN} \ge V_{CC} - 0.2$ V					0.7	1.4	
			V_{IN} = 3.4 V or GND					1	2.4	
		Eight bits switching at f_1 = 2.5 MHz at 50% duty cycle	$V_{IN} \le 0.2$ V or $V_{IN} \ge V_{CC} - 0.2$ V					1.3	2.6‖	
			V_{IN} = 3.4 V or GND					3.3	10.6‖	
C_i								5	10	pF
C_o								9	12	pF

† Typical values are at V_{CC} = 5 V, T_A = 25°C.

$I_C = I_{CC} + \Delta I_{CC} \times D_H \times N_T + I_{CCD} (f_0/2 + f_1 \times N_1)$

Where:

I_C = Total supply current
I_{CC} = Power-supply current with CMOS input levels
ΔI_{CC} = Power-supply current for a TTL high input (V_{IN} = 3.4 V)
D_H = Duty cycle for TTL inputs high
N_T = Number of TTL inputs at D_H
I_{CCD} = Dynamic current caused by an input transition pair (HLH or LHL)
f_0 = Clock frequency for registered devices, otherwise zero
f_1 = Input signal frequency
N_1 = Number of inputs changing at f_1

All currents are in milliamperes and all frequencies are in megahertz.

‖ Values for these conditions are examples of the I_{CC} formula.

switching characteristics over operating free-air temperature range (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	CY54FCT540CT		UNIT
			MIN	MAX	
t_{PLH}	D	$\overline{O}$	1.5	4.7	ns
t_{PHL}			1.5	4.7	
t_{PZH}	$\overline{OE}$	$\overline{O}$	1.5	6.5	ns
t_{PZL}			1.5	6.5	
t_{PHZ}	$\overline{OE}$	$\overline{O}$	1.5	5.7	ns
t_{PLZ}			1.5	5.7	

switching characteristics over operating free-air temperature range (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	CY74FCT540CT		UNIT
			MIN	MAX	
t_{PLH}	D	$\overline{O}$	1.5	4.1	ns
t_{PHL}			1.5	4.1	
t_{PZH}	$\overline{OE}$	$\overline{O}$	1.5	5.8	ns
t_{PZL}			1.5	5.8	
t_{PHZ}	$\overline{OE}$	$\overline{O}$	1.5	5.2	ns
t_{PLZ}			1.5	5.2	

PARAMETER MEASUREMENT INFORMATION



LOAD CIRCUIT FOR
TOTEM-POLE OUTPUTS



LOAD CIRCUIT FOR
3-STATE OUTPUTS

TEST	S1
t_{PLH}/t_{PHL}	Open
t_{PLZ}/t_{PZL}	7 V
t_{PHZ}/t_{PZH}	Open



VOLTAGE WAVEFORMS
PULSE DURATION



VOLTAGE WAVEFORMS
SETUP AND HOLD TIMES



VOLTAGE WAVEFORMS
PROPAGATION DELAY TIMES
INVERTING AND NONINVERTING OUTPUTS



VOLTAGE WAVEFORMS
ENABLE AND DISABLE TIMES
LOW- AND HIGH-LEVEL ENABLING

NOTES: A. C_L includes probe and jig capacitance.
B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
C. The outputs are measured one at a time with one input transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
5962-9222006MRA	Active	Production	CDIP (J) | 20	20 | TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-9222006MR A
CY74FCT540CTQCT	Active	Production	SSOP (DBQ) | 20	2500 | LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT540C
CY74FCT540CTQCT.B	Active	Production	SSOP (DBQ) | 20	2500 | LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	FCT540C

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

REEL DIMENSIONS



TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CY74FCT540CTQCT	SSOP	DBQ	20	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CY74FCT540CTQCT	SSOP	DBQ	20	2500	353.0	353.0	32.0

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI’s products are provided subject to TI’s Terms of Sale, TI’s General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI’s provision of these resources does not expand or otherwise alter TI’s applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025