


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.


PRODUCT NO.
SEE TABLE



$\phi .040 \pm .003$
 1.02 ± 0.08 TYP


$.100 \pm .003$
 2.54 ± 0.08 TYP
NON-ACCUM.

RECOMMENDED HOLE PATTERN



NOTE 3

NOTE 4



mat'l. code NOTE 1 & TAB				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date		$.XX \pm .01 / X \pm .3$			title BERGSTIK® I HEADER	
D	V41868	GAH	1/27/95	linear	$.XXX \pm .005 / .XX \pm .13$	projection			
E	S00136	JPEH	05OCT'00		$.XXXX \pm .0020 / .XXX \pm .051$			product family BERGSTIK	
				angles	$0^\circ \pm 2^\circ$			size dwg no	
				dr	G. HULL 1/27/95	INCH/MM		A 67191	
				enrg	A. LIN 1/27/95				
				chr	T. BREWBAKER 1/27/95	scale		sheet 1 of 2	
				appd	A. LIN 1/27/95	5:1			
sheet index	revision sheet	E	D					cage code	
		1	2					22526	

PRODUCT NUMBER	DIM A TOTAL PIN LENGTH	DIM B ± 0.10 ± 0.25 TAIL LENGTH	DIM C ± 0.08 ± 0.20 MATING LENGTH
67191-XXX	.425/10.80	.095/2.41	.230/5.84
67192-XXX	.450/11.43	.120/3.05	.230/5.84
67193-XXX	.755/19.18	.425/10.80	.230/5.84
67194-XXX	.555/14.10	.225/5.72	.230/5.84
67467-XXX	.568/14.43	.150/3.81	.318/8.08

PLATING VARIATION

DASH NO.	OVERPLATING	UNDER PLATING	PLASTIC COLOR	TERMINAL MATERIAL
-9YY30u"/.76u Au		50u"/1.27u Ni	BLACK	3/4 HD. PHOS. BRNZ.

PART NO INFORMATION

XXXXX-YYY (NOTE 5)

SEE TABLE FOR PREFIX OF PART NO. — NO. OF POSITIONS — TERMINAL PLATING

EXAMPLE:

67191-908 DENOTES AN 8 POSITION HEADER WITH 30u"/.76u GOLD OVER 50u"/1.27u NICKEL PLATED TERMINALS. THE OVERALL PLASTIC LENGTH MAY BE .855/21.72 MAX (NOTE 6). THE PLASTIC COLOR IS BLACK.

NOTES;

- ① MOLDING MAT'L: 20% MIN GLASS-FILLED NYLON, RATED PER UL 94V-0.
- ② MEASURED AT DATUM -D-. WITH PART IN A RESTRAINED CONDITION.
- ③ 5 POUNDS/2.3 KILOGRAMS MINIMUM TERMINAL PUSH OUT FORCE IN EITHER DIRECTION.
- ④ BERG LOGO MAY APPEAR ON THIS SURFACE.
- ⑤ MIN NO. OF POSITIONS - 1, MAX NO. OF POSITIONS - 36.
- ⑥ .050/1.27 MAX AS MOLDED (MOLDED AS 36 POS. ONLY) .075/1.91 MAX WHEN BROKEN TO SPECIFIED LENGTHS.
- ⑦ TWO SIDES OF LEAD-IN PIN NOT PLATED, TYP BOTH ENDS.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3	projection	title		
D					.XXX±.005/.XX±.13		BERGSTIK® I HEADER		
				angles	.XXX±.0020/.XXX±.051		.100/2.54 C.C. SR STRAIGHT		
				dr	G. HULL 1/27/95	INCH/MM	product family BERGSTIK		code
				engr	A. LIN 1/27/95		size dwg no		sheet
				chr	T. BREWBAKER 1/27/95		A 67191		2 of
				appd	A. LIN 1/27/95	scale			
sheet index	revision sheet					5:1			