



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

2SB772

Features

- Capable of 1.25Watts of Power Dissipation.
- Collector-current 3.0A
- Collector-base Voltage 40V
- Operating and storage junction temperature range: -55°C to +150°C

PNP Silicon Plastic-Encapsulate Transistor

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
OFF CHARACTERISTICS				
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage ($I_C=10\text{mAdc}$, $I_B=0$)	30	---	Vdc
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage ($I_C=100\text{uAdc}$, $I_E=0$)	40	---	Vdc
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage ($I_E=100\text{uAdc}$, $I_C=0$)	5.0	---	Vdc
I_{CBO}	Collector Cutoff Current ($V_{CB}=40\text{Vdc}$, $I_E=0$)	---	1.0	uAdc
I_{CEO}	Collector Cutoff Current ($V_{CE}=30\text{Vdc}$, $I_B=0$)	---	1.0	uAdc
I_{EBO}	Emitter Cutoff Current ($V_{EB}=6.0\text{Vdc}$, $I_C=0$)	---	1.0	uAdc

ON CHARACTERISTICS

$h_{FE(1)}$	DC Current Gain ($I_C=1.0\text{Adc}$, $V_{CE}=2.0\text{Vdc}$)	60	400	---
$h_{FE(2)}$	DC Current Gain ($I_C=100\text{mAdc}$, $V_{CE}=2.0\text{Vdc}$)	32	---	---
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ($I_C=2.0\text{Adc}$, $I_B=0.2\text{Adc}$)	---	0.5	Vdc
$V_{BE(sat)}$	Base-Emitter Saturation Voltage ($I_C=2.0\text{Adc}$, $I_B=0.2\text{Adc}$)	---	2.0	Vdc


SMALL-SIGNAL CHARACTERISTICS

f_T	Transistor Frequency ($I_C=0.1\text{Adc}$, $V_{CE}=5.0\text{Vdc}$, $f=10\text{MHz}$)	50	---	MHz
-------	---	----	-----	-----

CLASSIFICATION OF $h_{FE(1)}$

Rank	R	O	Y	GR
Range	60-120	100-200	160-320	200-400

TO-126



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.30	0.33	7.70	8.30	
B		0.56		14.20	
C	0.50	0.53	12.76	13.36	
D	0.15	0.16	3.80	4.0	
E	0.12	0.13	3.10	3.30	
F	0.025	0.033	0.65	0.85	
G	0.06	0.07	1.50	1.70	
H	0.025	0.033	0.65	0.85	
J	0.08	0.10	2.08	2.48	
K	0.12	0.14	3.05	3.45	
L	0.63	0.64	15.90	16.30	
M		0.04		1.0	
N		0.02		0.5	
P	0.06	0.08	1.55	1.95	
Q	0.018	0.023	0.45	0.60	
R	0.43	0.44	10.80	11.20	