



P	LTR	DESCRIPTION	DATE	DWN	APVD
	AJ3	REVISED PER ECO-17-013752	20DEC2017	J.Z	D.Z

- 1

0.00076 MIN GOLD PLATING IN THIS AREA WITH 0.00381 MIN MATTE TIN LEAD ON THE REMAINDER, BOTH OVER 0.00127 MIN NICKEL UNDERPLATE.
2. FITS 1.17 – 1.27 DIAMETER HOLE IN A 1.57 OR 2.36 PRINTED CIRCUIT BOARD.
3. PARTS TO COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 4


0.05 – 0.25 DIAMETER OPENING REQUIRED IN TIP OF PIN.
5. APPLICATOR FEED: 8.00 – 8.26
- 6

0.00076 MIN GOLD PLATING IN THIS AREA WITH 0.00381 MIN MATTE TIN ON THE REMAINDER, BOTH OVER 0.00127 MIN NICKEL UNDERPLATE.



6	3-60803-1
PRE TIN	60803-2
6	60803-1
FINISH	PART NUMBER

0.13	.005	1.27	.050	2.36	.093	-	-
0.05	.002	1.17	.046	2.29	.090	9.91	.390
0.00381	.000150	1.12	.044	1.57	.062	8.26	.325
0.00127	.000050	0.38	.015	1.52	.060	8.00	.315
0.00076	.000030	0.25	.010	1.47	.058	4.06	.160
MM	IN	MM	IN	MM	IN	MM	IN
CONVERSION TABLE							



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 7-28-97	TE TE Connectivity			
DIMENSIONS: mm		CHK R. SWING 7-28-97				
		APVD A. BEDDICK 9-10-97	NAME			
		PRODUCT SPEC	PIN, .058 DIAMETER, PHOSPHER BRONZE, PRESS FIT, LOOSE PIECE, P.C. CONTACT			
MATERIAL 0.25 PH BRZ		FINISH SEE TABLE	SIZE A2	CAGE CODE 00779	DRAWING NO C-60803	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 15:1	SHEET 1 OF 1	REV AJ3	