


Type	Pole	A
DBS 1102	2	6.02
DBS 1103	3	8.56
DBS 1104	4	11.10
DBS 1105	5	13.64
DBS 1106	6	16.18
DBS 1107	7	18.72
DBS 1108	8	21.26
DBS 1109	9	23.80
DBS 1110	10	26.34
DBS 1112	12	31.42

P.C.B. LAYOUT



Specifications:

- Contact rating: 25mA, 24V DC; 100mA, 6V DC
min.: 0.1mA, 3V DC
- Contact resistance: 50mOhm max.
- Insulation resistance: 100MOhm min. at 500V DC
- Dielectric strength: 500V, 50Hz for the duration of 1 minute
- Operating temperature: -40°C to +85°C
- Mechanical life: min. 2 000 cycles
- Material: PPS meets UL94V-0
- Contacts: gold plated over nickel
- Mounting: on pc-board
- Slide position: off
- Soldering conditions: auto-soldering: max. 260°C, 5sec.
- Vibration: MIL-STD 202F, method 201A
- Shock: MIL-STD 202F, method 213B, condition A



Tolerances:			Date	Name	<h1>DBS 1100</h1>
			02/07	dr	
			knitter-switch		<h2>30 10 62</h2>
Vibration / shock	06/10	dr			
Modifications	Date	Name			
					Page
					1/1