





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			F	REVISED PER ECO-14-016920	03NOV2014	SY	FY



SECTION W-W



- 1 MATERIAL: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.

2 GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): $1.27\mu\text{m}$ MIN NICKEL AND ACTION
PIN: $0.5\mu\text{m}$ MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.

5 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIRONMENT APPLICATIONS.

6 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.


7 PLATED-THROUGH HOLES AT $2 \times 1.5\text{mm}$ GRID
88 TOTAL HOLES.

8 ROW "I" 6 PLATED THROUGH HOLES FOR UPPERSHIELD.

9 CONNECTOR & SHIELD LUBRICATED WITH BELCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

10 SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE
OR ADHESIVE.

11 $0.76\mu\text{m}$ MIN GOLD PLATING ON MATING SURFACE



		3-5646492-0
OBSOLETE		1-5646492-9
OBSOLETE		5646492-9
		5646492-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: B CARBO OR: G SKIPPER APVD: G SKIPPER PRODUCT SPEC APPLICATION SPEC —	28JUL05 28JUL05 28JUL05	 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLG ± 1-PLG ±0.1 2-PLG ± 3-PLG ± 4-PLG ± ANGLES ± FINISH: SEE TABLE		NAME: R/A RECEPTACLE ASSY, 88 POSN, TTR 8 ROW, TYPE F, Z-PACK 2mm HM	
MATERIAL: 		WEIGHT: —		SIZE: A1 CAGE CODE: 00779 DRAWING NO: C5646492	RESTRICTED TO:
		CUSTOMER DRAWING		SCALE: 5:1 SHEET: 1 of 1 REV: F	