


FEATURES


- Standard 3.2mm x 2.5mm 4-Pad Surface Mount Package
- HCMOS Output
- Fundamental and 3rd Overtone Crystal Designs
- Frequency Range 1 – 125 MHz
- Frequency Stability ± 50 ppm Standard, ± 25 ppm and ± 20 ppm Available
- Operating Voltages +1.8Vdc, +2.5Vdc, +2.8Vdc, +3.3Vdc or +5.0Vdc
- Operating Temperature to -40°C to +85°C
- Output Enable Standard
- Tape & Reel Packaging Standard, EIA-418
- **RoHS/Green Compliant [6/6]**



APPLICATIONS

Model 632 is ideal for applications; such as broadband access, Ethernet/Gigabit Ethernet, microprocessors/DSP/FPGA, networking equipment computers and peripherals, digital video, cameras and other portable devices.

ORDERING INFORMATION



¹ Consult factory for 6I Stability/Temperature availability.


² Frequency is recorded with three leading significant digits before the 'M' and 5 significant digits after the 'M' [including zeros].

[Ex. 3.579545 MHz, code as 003M57954; 14.31818 MHz, code as 014M31818; 125 MHz, code as 125M00000]

**Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.**

PACKAGING INFORMATION [reference]

Device quantity is 1k pcs. minimum and 3k pcs. maximum per 180mm reel. **8mm tape width.**




ELECTRICAL CHARACTERISTICS

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Maximum Supply Voltage	V_{CC}	-	-0.5	-	4.0	V
Storage Temperature	T_{STG}	-	-40	-	+100	°C
Frequency Range	f_O	-	1.0	-	125	MHz
Frequency Stability [See Note 1 and Ordering Information]	$\Delta f/f_O$	-	-	-	20, 25, 50	± ppm
Aging	$\Delta f/f_O$	-	-	-	3	± ppm/yr
Operating Temperature	T_A	-	-20 -40	+25	+70 +85	°C
Supply Voltage	V_{CC}	$\pm 10\%$	1.62 2.25 2.52 2.97 4.50	1.8 2.5 2.8 3.3 5.0	1.98 2.75 3.08 3.63 5.50	V
Supply Current	I_{CC}	$C_L = 15\text{pF}$ 1.0 MHz to 100 MHz 100.1 MHz to 125 MHz	- - -	- - -	7 12	mA
Model 632M [+18V]						
Model 632N, 632T [+2.5V, +2.8V]					10 20	
Model 632L, 632S [+3.3V, +5.0V]					15 25	
Output Load	C_L		-	-	15	pF
Output Voltage Levels						
Logic '1' Level	V_{OH}	CMOS Load	90% V_{CC}	-	-	V
Logic '0' Level	V_{OL}	CMOS Load	-	-	10% V_{CC}	
Output Current						
Logic '1' Level [M,N,T,L,S]	I_{OH}	$V_{OH} = 90\%V_{CC}$ [1.8V, 2.5/2.8V, 3.3V, 5.0V]	-	-	-2, -4, -8, -16	mA
Logic '0' Level [M,N,T,L,S]	I_{OL}	$V_{OL} = 10\%V_{CC}$ [1.8V, 2.5/2.8V, 3.3V, 5.0V]	-	-	+2, +4, +8, +16	
Output Duty Cycle	SYM	@ 50% Level	45	-	55	%
Rise and Fall Time						
Model 632M [+18V]	T_R, T_F	@ 10% - 90% Levels, $C_L = 15\text{pF}$ 1.0 MHz to 20 MHz 20.1 MHz to 125 MHz	- - -	- - -	5 4	ns
Model 632N, 632T [+2.5V, +2.8V]					4 3	
Model 632L, 632S [+3.3V, +5.0V]					3 2	
Start Up Time	T_S	Application of V_{CC}	-	-	2	ms
Enable Function						
Enable Input Voltage	V_{IH}	Pin 1 Logic '1', Output Enabled	0.7* V_{CC}	-	-	V
Disable Input Voltage	V_{IL}	Pin 1 Logic '0', Output Disabled	-	-	0.3* V_{CC}	
Enable Time [M,N,T,L,S]	T_{PLZ}	Pin 1 Logic '1'	-	-	2	ms
Standby Current	I_{ST}	Pin 1 Logic '0', Output Disabled	-	-	15	µA
Period Jitter, pk-pk	pjpk-pk	-	-	-	40	ps
Phase Jitter, RMS	tjrms	Bandwidth 12 kHz - 20 MHz	-	-	1	


Notes:

- Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and aging.

LVC MOS OUTPUT WAVEFORM



TEST CIRCUIT, CMOS LOAD




ENABLE TRUTH TABLE

PIN 1	PIN 3
Logic '1'	Output
Open	Output
Logic '0'	High Imp.

MECHANICAL SPECIFICATIONS

PACKAGE DRAWING



MARKING INFORMATION

1. XX.XX – Frequency in MHz.
2. C – CTS and Pin 1 identifier.
3. ** – Manufacturing Site Code.
4. D – Manufacturing Date Code.
[See Table 1 for codes.]
5. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.

NOTES


1. Termination pads (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
2. Reflow conditions per JEDEC J-STD-020; 260°C maximum, 20 seconds.
3. MSL = 1.

TABLE I

YEAR MONTH					JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
2001	2005	2009	2013	2017	A	B	C	D	E	F	G	H	J	K	L	M
2002	2006	2010	2014	2018	N	P	Q	R	S	T	U	V	W	X	Y	Z
2003	2007	2011	2015	2019	a	b	c	d	e	f	g	h	j	k	l	m
2004	2008	2012	2016	2020	n	p	q	r	s	t	u	v	w	x	y	z

SUGGESTED SOLDER PAD GEOMETRY

C_{BYPASS} should be ≥ 0.01 uF.



D.U.T. PIN ASSIGNMENTS

PIN	SYMBOL	DESCRIPTION
1	EOH	Enable
2	GND	Circuit & Package Ground
3	Output	RF Output
4	V_{CC}	Supply Voltage

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

<u>632L3I038M40000</u>	<u>632L3I025M00000</u>	<u>632L3I020M00000</u>	<u>632L3C066M66666</u>	<u>632L3I024M00000</u>	
<u>632L3I026M00000</u>	<u>632L3I048M00000</u>	<u>632L3C048M00000</u>	<u>632L3I040M00000</u>	<u>632L3I050M00000</u>	
<u>632L3C050M00000</u>	<u>632L3I002M04800</u>	<u>632L3I044M23680</u>	<u>632L3I012M00000</u>	<u>632L3I024M57600</u>	<u>632L3I016M00000</u>
<u>632L3I030M00000</u>	<u>632L3I010M00000</u>	<u>632L3I008M00000</u>	<u>632L3C033M00000</u>	<u>632L3I001M84320</u>	
<u>632L3I003M57954</u>	<u>632L3I003M68640</u>	<u>632L3I004M00000</u>	<u>632L3I007M37200</u>	<u>632L3I011M05920</u>	<u>632L3I013M00000</u>
<u>632L3I014M31818</u>	<u>632L3I014M74560</u>	<u>632L3I018M43200</u>	<u>632L3I027M00000</u>	<u>632L3I029M49120</u>	
<u>632L3I032M00000</u>	<u>632L3I033M00000</u>	<u>632L3I033M33300</u>	<u>632L3I044M00000</u>	<u>632L3I060M00000</u>	<u>632M3I003M57954</u>
<u>632M3I003M68640</u>	<u>632M3I004M00000</u>	<u>632M3I007M37200</u>	<u>632M3I008M00000</u>	<u>632M3I010M00000</u>	
<u>632M3I012M00000</u>	<u>632M3I013M00000</u>	<u>632M3I014M31818</u>	<u>632M3I014M74560</u>	<u>632M3I016M00000</u>	
<u>632M3I020M00000</u>	<u>632M3I024M00000</u>	<u>632M3I025M00000</u>	<u>632M3I027M00000</u>	<u>632M3I030M00000</u>	
<u>632M3I032M00000</u>	<u>632M3I033M33300</u>	<u>632M3I040M00000</u>	<u>632M3I048M00000</u>	<u>632M3I050M00000</u>	
<u>632M3I060M00000</u>	<u>632M3I066M66600</u>	<u>632N3I004M00000</u>	<u>632N3I008M00000</u>	<u>632N3I010M00000</u>	
<u>632N3I012M00000</u>	<u>632N3I012M50000</u>	<u>632N3I013M50000</u>	<u>632N3I014M31818</u>	<u>632N3I014M74560</u>	
<u>632N3I020M00000</u>	<u>632N3I024M00000</u>	<u>632N3I024M57600</u>	<u>632N3I025M00000</u>	<u>632N3I027M00000</u>	
<u>632N3I030M00000</u>	<u>632N3I032M00000</u>	<u>632N3I033M00000</u>	<u>632N3I033M33300</u>	<u>632N3I040M00000</u>	
<u>632N3I044M00000</u>	<u>632N3I048M00000</u>	<u>632N3I050M00000</u>	<u>632N3I060M00000</u>	<u>632N3I066M66600</u>	
<u>632L3C025M00000</u>	<u>632L3I036M86400</u>	<u>632L3C040M00000</u>	<u>632L3C020M00000</u>	<u>632L3I066M66660</u>	
<u>632L3C024M00000</u>	<u>632L3I007M37280</u>	<u>632L3C008M00000</u>			