MULTI-LAYER HIGH-Q CAPACITORS



These lines of multilayer capacitors have been developed for High-Q and microwave applications.

• The **S-Series** (R07S, R14S, R15S) capacitors give an ultra-high Q performance, and exhibit NP0 temperature characteristics.

• The **L-Series** (R05L) capacitors give mid-high Q performance, and exhibit NP0 temperature characteristics.

• The **E-Series** (S42E, S48E, S58E) capacitors give excellent high-Q performance from HF to Microwave frequencies. Typical uses are high voltage, high current applications. They are offered in chip (Ni barrier or Non-Magnetic Pt.-Ag) or in Non-Magnetic leaded form.

• RoHS compliance is standard for all unleaded parts (see termination options box).

HOW TO ORDER

252	S48	E	470	K	V	4	E

WVDC[2]
250 = 25 V
201 = 200 V
251 = 250 V
501 = 500 V
102 = 1000 V
152 = 1500 V
252 = 2500 V
362 = 3600 V
722 = 7200 V

CASE SIZE
R05 (0201)
R07 (0402)
R14 (0603)
R15 (0805)
S42 (1111)
S48 (2525)
S58 (3838)

DIELECTRIC
S = Ultra High Q NPO
L = High Q NPO
E = Ultra High Q NPO, High Voltage, High Power,
T[1] = High Temp (175C) Ultra High Q NPO

CAPACITANCE (pF)
1st two digits are significant; third digit denotes number of zeros, R = decimal.
100 = 10 pF
101 = 100 pF

TOLERANCE
A = ± 0.05 pF
B = ± 0.10 pF
C = ± 0.25 pF
D = ± 0.50 pF
F = ±1 %
G = ±2%
J = ±5%
K = ± 10%

For tolerance availability, see chart.

TERMINATION
Nickel Barrier
V = Ni/Sn (Green)
T = Ni/SnPb
G = Ni/Au (Green)
Non-Mag[1]
U = Cu/Sn (Green)
C = Cu/SnPb
Leaded (All Non-Mag)[1]
1 = Microstrip
2 = Axial Ribbon
3 = Axial Wire
4 = Radial Ribbon
5 = Radial Wire

Part Number written: **252S48E470KV4E**

MARKING
3 = Cap Code & Tolerance
4 = No Marking
6 = EIA Code
(Marking option is only available on 0805 and larger case sizes)

PACKAGING
S = Bulk
W = Waffle Pack
0201 - 0603
Y = Paper 5" Reel
T = Paper 7" Reel
R[1] = Paper 13" Reel
J[1] = Paper 5" Reel - Horizontally Oriented Electrodes
N[1] = Paper 5" Reel - Vertically Oriented Electrodes
L[1] = Paper 7" Reel - Horizontally Oriented Electrodes
V[1] = Paper 7" Reel - Vertically Oriented Electrodes
0805 - 3838
Z = Embossed 5" Reel
E = Embossed 7" Reel
U[1] = Embossed 13" Reel
M[1] = Embossed 5" Reel - Horizontally Oriented Electrodes
Q[1] = Embossed 5" Reel - Vertically Oriented Electrodes
G[1] = Embossed 7" Reel - Horizontally Oriented Electrodes
P[1] = Embossed 7" Reel - Vertically Oriented Electrodes
Tape specifications conform to EIA RS481



[1] - Not available for all MLCC - Call factory for info.
[2] - WVDC - Working Voltage DC.

Low ESR / High-Q Capacitor Selection Chart

Cap. Value \ EIA Size			RF Power Applications									
			0201 (R05)		0402	0603	0805	0805	1111		2525	3838	
			NPO (R05L)	NPO (R05G)	(R07S)	(R14S)	(R15S)	(R15G)	(S42E)		(S48E)	(S58E)	
Capacitance pF	Code												
0.1	0R1												
0.2	0R2		25 V	25 V	200 V	250 V			500V	1500V			
0.3	0R3		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V			
0.4	0R4		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V			
0.5	0R5		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V		
0.6	0R6		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
0.7	0R7		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
0.8	0R8		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
0.9	0R9		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.0	1R0		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.1	1R1		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.2	1R2	A	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.3	1R3		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.4	1R4	B	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.5	1R5		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.6	1R6	C	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.7	1R7		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.8	1R8		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
1.9	1R9	D	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
2.0	2R0		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
2.1	2R1		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
2.2	2R2		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
2.4	2R4		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
2.7	2R7		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
3.0	3R0		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
3.3	3R3		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
3.6	3R6		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
3.9	3R9		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
4.3	4R3		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
4.7	4R7		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
5.1	5R1		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
5.6	5R6	A**	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
6.2	6R2	B	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
6.8	6R8		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
7.5	7R5	C	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
8.2	8R2		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
9.1	9R1	D	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
10	100		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
11	110		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
12	120		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
13	130	F	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
15	150		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
16	160	G	25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
18	180		25 V	25 V	200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
20	200	J	25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
22	220		25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
24	240	K	25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
27	270		25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
30	300		25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
33	330		25 V		200 V	250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V

Consult factory for Non-Standard values.
****A tolerance only available for R07S (0402) and R14S(0603) caps**

Low ESR / High-Q Capacitor Selection Chart

Cap. Value \ EIA Size			0201 (R05)		0402	RF Power Applications							
			NPO (R05L)	NP0 (R05G)	(R07S)	0603 (R14S)	0805 (R15S)	0805 (R15G)	1111 (S42E)		2525 (S48E)	3838 (S58E)	
Capacitance pF	Code	Tolerance											
36	360	F G J K	25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
39	390		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
43	430		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
47	470		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
51	510		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
56	560		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
62	620		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
68	680		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
75	750		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
82	820		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
91	910		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
100	101		25 V			250 V	250 V	1000V	500V	1500V	2500V	3600V	7200V
110	111						250 V		300V	1500V	2500V	3600V	7200V
120	121						250 V		300V	1000V	2500V	3600V	7200V
130	131						250 V		300V	1000V	2500V	3600V	7200V
150	151						250 V		300V	1000V	2500V	3600V	7200V
160	161						250 V		300V	1000V	2500V	3600V	7200V
180	181						250 V		300V	1000V	2500V	3600V	7200V
200	201						250 V		300V	1000V	2500V	3600V	
220	221						250 V		200V	1000V	2500V	3600V	
240	241								200V	1000V	2500V	3600V	
270	271								200V	1000V	2500V	3600V	
300	301								200V	1000V	1500V	3600V	
330	331								200V	1000V	1500V	3600V	
360	361								200V	1000V	1500V	3600V	
390	391								200V	500V	1500V	3600V	
430	431	G J K							200V	500V	1500V	2500V	
470	471								200V	500V	1500V	2500V	
510	511								100V	500V	1000V	2500V	
560	561								100V	500V	1000V	2500V	
620	621								100V	500V	1000V	2500V	
680	681								50V		1000V	2500V	
750	751								50V		1000V	2500V	
820	821								50V		1000V	2500V	
910	911								50V		1000V	1000V	
1000	102								50V		1000V	1000V	
1200	122										1000V	1000V	
1500	152										500V	1000V	
1800	182										500V	1000V	
2200	222										300V	1000V	
2700	272										300V	500V	
3300	332											500V	
3900	392											500V	
4700	472											500V	
5100	512											500V	
10000	103												

Consult factory for Non-Standard values.

Dielectric Characteristics — *NPO*

TEMPERATURE COEFFICIENT:	0 ± 30ppm /°C, -55 to 125°C
QUALITY FACTOR / DF:	Q >1,000 @ 1KHz (C>1,000pF), Typical 10,000 (C<1,000 pF)
INSULATION RESISTANCE:	>100 GΩ @ 25°C,WVDC[1]; 125°C IR is 10% of 25°C rating
DIELECTRIC STRENGTH:	500 V ≤ 2.5 X WVDC[1] Min., 25°C, 50 mA max 1000 V ≤ 1.5 X WVDC[1] Min., 25°C, 50 mA max > 1500 = 1 X WVDC[1] Min., 25°C, 50 mA max
TEST PARAMETERS::	1MHz ±50kHz, 1.0±0.2 VRMS, 25°C

AVAILABLE CAPACITANCE:

Size 0201:	0.2 - 100 pF	Size 1111:	0.2 - 1000 pF
Size 0402:	0.2 - 33 pF	Size 2525:	1.0 - 2700 pF
Size 0603:	0.2 - 100 pF	Size 3838:	1.0 - 5100 pF
Size 0805:	0.3 - 220 pF		

Mechanical & Environmental Characteristics

	SPECIFICATION	TEST PARAMETERS
SOLDERABILITY:	Solder coverage ≥ 90% of metalized areas No termination degradation	Preheat chip to 120°-150°C for 60 sec., dip terminals in rosin flux then dip in Sn62 solder @ 240°±5°C for 5±1 sec
RESISTANCE TO SOLDERING HEAT:	No mechanical damage Capacitance change: ±2.5% or 0.25pF Q>500 I.R. >10 G Ohms DWV[2]: 2.5 x WVDC[1]	Preheat device to 80°-100°C for 60 sec. followed by 150°-180°C for 60 sec. Dip in 260°±5°C solder for 10±1 sec. Measure after 24±2 hour cooling period
TERMINAL ADHESION:	Termination should not pull off. Ceramic should remain undamaged.	Linear pull force[3] exerted on axial leads soldered to each terminal.
PCB DEFLECTION:	No mechanical damage. Capacitance change: 2% or 0.5pF Max	Glass epoxy PCB: 0.5 mm deflection
LIFE TEST:	MIL-STD-202, Method 108I No mechanical damage Capacitance change: ±3.0% or 0.3 pF Q>500 I.R. >1 G Ohms DWV[2]: 2.5 x WVDC[1]	Applied voltage: 200% of WVDC[1] for capacitors rated at 500 volts DC or less. 100% of WVDC[1] for capacitors rated at 1250 volts DC or less. Temperature: 125°±3°C Test time: 1000+48-0 hours
THERMAL CYCLE:	No mechanical damage. Capacitance change: ±2.5% or 0.25pF Q>2000 I.R. >10 G Ohms DWV[2]: 2.5 x WVDC[1]	5 cycles of: 30±3 minutes @ -55°+0/-3°C, 2-3 min. @ 25°C, 30±3 min. @ +125°+3/-0°C, 2-3 min. @ 25°C Measure after 24±2 hour cooling period
HUMIDITY, STEADY STATE:	No mechanical damage. Capacitance change: ±5.0% or 0.50pF max. Q>300 I.R. ≥ 1 G-Ohm DWV[2]: 2.5 x WVDC[1]	Relative humidity: 90-95% Temperature: 40°±2°C Test time: 500 +12/-0 Hours Measure after 24±2 hour cooling period
HUMIDITY, LOW VOLTAGE:	No mechanical damage. Capacitance change: ±5.0% or 0.50pF max. Q>300 I.R. = 1 G-Ohm min. DWV[2]: 2.5 x WVDC[1]	Applied voltage: 1.5 VDC, 50 mA max. Relative humidity: 85±2% Temperature: 40°±2°C Test time: 240 +12/-0 Hours Measure after 24±2 hour cooling period
VIBRATION:	No mechanical damage. Capacitance change: ±2.5% or 0.25pF Q>1000 I.R. ≥ 10 G-Ohm DWV[2]: 2.5 x WVDC[1]	Cycle performed for 2 hours in each of three perpendicular directions Frequency range 10Hz to 55 Hz to 10 Hz traversed in 1 minute. Harmonic motion amplitude: 1.5mm

[1] - WVDC - Working Voltage DC.
[2] - DWV - Dielectric Withstanding Voltage.
[3] - 0402 ≥ 2.0lbs, 0603 ≥ 4.0lbs (min).
[4] - Whichever is less.

Mechanical Characteristics

Size	Units	Length	Width	Thickness	End Band
EIA 0201	In	.024 ±.001	.012 ±.001	.012 ±.001	.008 Max.
Metric (0603)	mm	(0.60 ±0.03)	(0.30 ±0.03)	(0.30 ±0.03)	(0.20 Max.)
EIA 0402	In	.040 ±.004	.020 ±.004	.020 ±.004	.010 ±.006
Metric (1005)	mm	(1.02 ±0.1)	(0.51 ±0.1)	(0.51 ±0.1)	(0.25 ±.15)
EIA 0603	In	.062 ±.006	.032 ±.006	.030 +.005/-.003	.014 ±.006
Metric (1608)	mm	(1.57 ±0.15)	(0.81 ±0.15)	(0.76 +.13-.08)	(0.35 ±.15)
EIA 0805	In	.080 ±.008	.050 ±.008	.040 ±.006	.020 ±.010
Metric (2012)	mm	(2.03 ±0.20)	(1.27 ±0.20)	(1.02 ±.15)	(0.50 ±.25)

Horizontal and Verticle Oriented Capacitors

Horizontal Electrode Orientation



Vertical Electrode Orientation



Applications & Features

Size:	EIA 0201, 0402
Performance:	SRF's up to 20 GHz, Ultra High Q, Tight tolerance, Ultralow ESR
Termination:	Ni/Au, Ni/Sn, Ni/SnPb
Applications:	High Frequency Wireless Communications, Portable Wireless Products, Battery Powered Products

RoHS Compliant

Benifits of using Oriented Capacitors

- Consistent Orientation - Improved repeatability of production circuits.
- Consistent Orientation - More consistent filter performance.
- Vertical Orientation - The elimination of parallel frequencies.
- Vertical Orinetation - Lower inductance for a given capacitor.
- Horizontal Orientation - Lower coupling between adjacent capacitors.

E-Series Terminations and Leads

CHIP DIMENSIONS

Termination	Size	Units	L	Tol	W	Tol	T	E / B	Tol
V,T U,C	S42E	In	0.110	+.020 -.010	0.110	+/- .015	0.102 Max.	0.015 Typ.	+/- 0.008
		mm	2.79	+0.51 -0.25	2.79	+/- 0.38	2.59 Max.	0.38 Typ.	+/- 0.20
	S48E	In	0.230	+.025 -.010	0.250	+/- .015	0.150 Max.	0.025 Typ.	
		mm	5.84	+0.63 -0.25	6.35	+/- 0.38	3.81 Max.	0.63 Typ.	
	S58E	In	0.380	+.015 -.010	0.380	+/- .010	0.170 Max.	0.025 Typ.	
		mm	9.65	+0.38 -0.25	9.65	+/- 0.25	4.32 Max.	0.63 Typ.	

For all E-Series Models:

OPERATING TEMP. :	-55 to +125°C
INSULATION RESISTANCE:	>10G Ω @ 25°C
TEMPERATURE COEFFICIENT:	0 ± 30ppm /°C, -55 to 125°C
DISSIPATION FACTOR (TYP.):	< 0.05% @ 1 MHz

Drawings not to scale

Unleaded Termination Codes “V” (Ni/Sn), “T” (Ni/SnPb), “U” (Cu/Sn non-mag), “C” (Cu/SnPb non-mag)



Microstrip Ribbon Leads (Non-Magnetic), Termination Code “1”



Axial Ribbon Leads (Non-Magnetic), Termination Code “2”



Axial Wire Leads (Non-Magnetic), Termination Code “3”



Radial Ribbon Leads (Non-Magnetic), Termination Code “4”



Radial Wire Leads (Non-Magnetic), Termination Code “5”



Lead	Size	LL(min)	X	Tol	e	e-Tol
1	S42E	0.25	0.093	+/-0.005	0.004	+/- 0.002
		6.40	2.36	+/- 0.13	0.102	+/- 0.051
	S48E	0.394	0.217	+/- 0.02	0.009	- 0.0019/+ 0.0031
		10.0	5.5	+/- 0.50	0.220	- 0.050/+ 0.080
	S58E	0.748	0.35	+/- 0.02	0.010	- 0.0019/+ 0.0039
		19.00	8.90	+/- 0.50	0.250	- 0.050/+ 0.100
2	S42E	0.25	0.093	+/-0.005	0.004	+/- 0.002
		6.40	2.36	+/- 0.13	0.102	+/- 0.051
	S48E	0.394	0.217	+/- 0.02	0.009	- 0.0019/+ 0.0031
		10.00	5.50	+/- 0.50	0.220	- 0.050/+ 0.080
	S58E	0.748	0.35	+/- 0.02	0.010	- 0.0019/+ 0.0039
		19.00	8.90	+/- 0.50	0.25	- 0.050/+ 0.100
3	S42E	0.25	0.020in (0.511) diameter wire			
		6.40				
	S48E	0.394				
		10.00				
	S58E	0.748				
		19.00				

Lead	Size	LL(min)	X	Tol	e	e-Tol
4	S42E	0.352	0.093	+/-0.005	0.004	+/- 0.002
		8.90	2.36	+/- 0.13	0.102	+/- 0.051
	S48E	0.501	0.217	+/- 0.02	0.009	- 0.0019/+ 0.0031
		12.70	5.50	+/- 0.50	0.220	- 0.050/+ 0.080
	S58E	0.886	0.35	+/- 0.02	0.010	- 0.0019/+ 0.0039
		22.50	8.90	+/- 0.50	0.25	- 0.050/+ 0.100
5	S42E	0.25	0.020in (0.511) diameter wire			
		6.40				
	S48E	0.394				
		10.00				
	S58E	0.748				
		19.00				

SERIES RESONANCE CHART

Typical Series Resonant Frequency (Series Mounted)



RF CHARACTERISTICS - L-SERIES

ESR vs Frequency: 0201/R05L



Q vs Frequency: 0201/R05L



ESR vs Capacitance: 0201/R05L



Q vs Capacitance: 0201/R05L



S-Series RF Characteristics versus Frequency

Equivalent Series Resistance: 0402/R07S



Q Factor: 0402/R07S



Equivalent Series Resistance: 0603/R14S



Q Factor: 0603/R14S



Equivalent Series Resistance: 0805/R15S



Q Factor: 0805/R15S



Measurements performed on a Boonton 34A Resonant Coaxial Line and represent typical capacitor performance.

S-Series RF Characterisitcs versus Capacitance

Equivalent Series Resistance: 0402/R07S



Q Factor: 0402/R07S



Equivalent Series Resistance: 0603/R14S



Q Factor: 0603/R14S



Equivalent Series Resistance: 0805/R15S



Q Factor: 0805/R15S



Measurements performed on a Boonton 34A Resonant Coaxial Line and represent typical capacitor performance.

S42E Series RF Characteristics versus Frequency

Equivalent Series Resistance: 1111/S42E



Q Factor: 1111/S42E



S42E Series RF Characteristics versus Capacitance

S42E Equivalent Series Resistance vs Capacitance, Typical



S42E Q vs. Capacitance, Typical



S42E SRF (Series Mount), Typical



JTI S48E GRAPHICAL DATA

SRF (Shunt Mount), S48E, Typical (Preliminary)



As measured on a 8720C VNA, using a Shunt-Through fixture, and using the S11 magnitude dip to determine the SRF

Current Rating vs. Capacitance, S48E, Typical (Preliminary)



Solid traces show voltage limited current (Vrms)

Dotted traces show power dissipation limited current (Based on 4 Watts Power Dissipation, and 125 degrees C case temp.)

S48E Q vs. Capacitance, Typical (Preliminary)



As measured on a 4287A LCR meter, using a 16092A fixture

S48E ESR vs. Capacitance, Typical (Preliminary)



As measured on a 4287A LCR meter, using a 16092A fixture

JTI S48E Graphical Data



*Actual data from Boonton 34A resonant line.

JTI S58E Graphical Data



*Actual data from Boonton 34A resonant line.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Johanson:

250R05L1R8BV4T 500R07S100FV4T 500R07S2R0BV4T 251R14S2R2BV4T 251R14S0R6BV4T 500R07S0R4AV4T 500R07S0R3BV4T 500R07S150FV4T 251R14S1R8BV4T 250R05L1R0BV4T 251R14S1R2BV4T 251R14S2R0BV4T 251R14S1R0BV4T 250R05L1R5BV4T 500R07S1R2BV4T 500R07S3R0BV4T 500R07S4R7BV4T 251R14S3R0BV4T 500R07S100GV4T 500R07S270JV4T 500R07S0R9BV4T 251R14S3R9BV4T 500R07S2R2BV4T 250R05L3R6CV4T 500R07S5R6BV4T 251R14S0R5BV4T 500R07S2R7BV4T 500R07S1R3BV4T 500R07S100JV4T 500R07S2R4BV4T 251R14S120GV4T 500R07S5R6CV4T 500R07S1R2AV4T 250R05L1R2BV4T 500R07S1R5BV4T 500R07S6R8CV4T 251R14S330GV4T 500R07S0R7BV4T 500R07S0R4BV4T 500R07S200GV4T 500R07S1R0BV4T 500R07S3R9BV4T 500R07S3R3BV4T 500R07S1R8BV4T 251R14S0R8BV4T 500R07S0R8BV4T 251R14S1R5BV4T 251R14S150JV4T 251R14S100GV4T 251R14S430JV4T 251R14S470JV4T 251R14S270JV4T 251R14S6R8CV4T 500R07S8R2CV4T 500R07S0R5BV4T 500R07S1R5AV4T 251R14S3R3BV4T 500R07S0R5AV4T 102S42E1R3AV4E 251R14S180JV4T 250R05L5R1DV4T 500R07S1R7BV4T 501S42E2R4BV4E 501S42E910KV4E 301S42E111JV4E 102S42E5R1CV4E 251R15S2R0DV4E 501S42E270FV4E 251R15S820KV4E 251R14S1R3CV4T 251R14S470KV4T 102S42E5R6CV4E 501S42E910FV4E 250R05L180JV4T 251R15S131JV4E 500S42E751JV4E 201S42E241FV4E 251R15S120GV4E 250R05L5R6DV4T 250R05L6R2CV4T 251R14S510GV4T 250R05L120JV4T 251R15S221GV4E 500R07S7R5BV4T 102S42E4R3DV4E 251R14S3R3DV4T 501S42E240GV4E 201R07S2R1DV4T 251R15S101FV4E 251R14S160KV4T 500R07S8R2BV4T 501S42E750GV4E 102S42E1R2AV4E 201R07S2R1AV4T 250R05L4R3CV4T 251R15S820FV4E 250R05L160KV4T 500R07S1R1AV4T 251R14S470FV4T 201S42E471KV4E