



LOC	DIST	REVISIONS					
EH	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REV; EC 0B10-0154-01	18OCT01	LH	MD
			D	REV ECN 0B10-0178-02	30DEC02	LH	MD
			E	REV ECR-05-004347	09JUN05	LH	CC
			F	REV ECO-06-27719	04JAN07	LH	CD



1. ONE CABLE PACKAGED IN A CLEAR POLYBAG.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
4. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
5. AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.



0.15	0.5	203.2 (8.00)	9-219243-8
15.24	50	15392.4 (606.00)	5-219243-0
12.20	40	12344.4 (486.00)	4-219243-0
9.15	30	9296.4 (366.00)	3-219243-0
7.62	25	7721.6 (304.00)	2-219243-5
6.10	20	6197.6 (244.00)	2-219243-0
4.88	16	4978.4 (196.00)	1-219243-6
4.57	15	4724.4 (184.00)	1-219243-5
4.27	14	4368.8 (172.00)	1-219243-4
3.66	12	3759.2 (148.00)	1-219243-2
3.35	11	3454.4 (136.00)	1-219243-1
3.05	10	3149.6 (124.00)	1-219243-0
2.74	9	2794 (110.00)	219243-9
2.44	8	2489.2 (98.00)	219243-8
2.14	7	2184.4 (86.00)	219243-7
1.83	6	1879.6 (74.00)	219243-6
1.53	5	1574.8 (62.00)	219243-5
1.22	4	1270 (50.00)	219243-4
0.92	3	965.2 (38.00)	219243-3
0.61	2	660.4 (26.00)	219243-2
0.30	1	355.6 (14.00)	219243-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM[INCHES]

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	

DWN
M. BOLES
25JUL97

CHK
B. ANTHONY
25JUL97

APVD
B. ANTHONY
25JUL97

PRODUCT SPEC
108-1163

APPLICATION SPEC
114-6053

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa., 17105-3608

CABLE ASSEMBLY, MOD PLUG, 8 POSITION
GREEN, ENHANCED CATEGORY 5

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=219243

RESTRICTED TO
NTS

SHEET
1

OF
1

REV
F

AMP 1471-9 REV 31MAR2000