


SYMBOL DEFINITION

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING

TOTAL NO. OF SYMBOLS ON DRAWING







17

LAST NO. USED

27

MISSING NUMBERS

DWS STATUS					REVISION HISTORY					AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE								
14FE01	R	J2	-	-		DIM 39 +0.3/-0.85 WAS 39 +/-0.3				206418	ESF	ESF	JH
25N002	R	10	-	-		MAT'L SPEC WAS R0067547				233874	ARA	ARA	ET



NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- MATING COMPONENTS OR EQUIVALENT: CONVENIENCE CTR 12077574
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

THE FOLLOWING APPLY UNLESS OTHERWISE SPECIFIED:

PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC.
TRUE POSITION TOLERANCES AND RELATED DATUMS, APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME.
OTHER GEOMETRIC TOLERANCES, AND RELATED DATUMS, APPLY PER SEPARATE TRUE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCE. SEE GM STANDARDS, AND APPLICABLE DIVISIONAL STANDARDS, FOR INTERPRETATION.

GEOMETRIC DRAWING SYMBOLS FOR INTERPRETATION:

FLAT	PROFILE OF A LINE	PARALLEL
STRAIGHT	PERPENDICULAR	TRUE POSITION
ROUND	PROFILE OF A SURFACE	CIRCULAR RUNOUT
CYLINDRICAL	ANGULAR	TOTAL RUNOUT
MAXIMUM MATERIAL CONDITION (MMC)		DIAMETER
LEAST MATERIAL CONDITION (LMC)		BASIC DIMENSION
REGARDLESS OF FEATURE SIZE (RFS)		
PROJECTED TOL. ZONE		



DWG TYPE: PART DRAWING

STYLE: 27,123

VOLUME (CMT): 6900

DISTR CODE: D

ROUTING: 6900

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 & 2019 DIMENSIONING AND TOLERANCING ADDENDUM 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY TO THE DATE OF PUBLICATION. THIS DOCUMENT DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE BASED SEPARATELY, REGARDLESS OF DATUM REFERENCE.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE:

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

UNIGRAPHICS

DELPHI

DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DRAWING NAME: COVER CONVENIENCE CTR

DRAWING NUMBER: 12160897

SIZE: A0

SCALE: 2:1

FRAME NO: 1

SHEET NO: 1

OF: 1

REV: R

N/P: 10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12160897](#)