

## Search Results

### Evaluate

- FAQ's

### Design a Solution

- Catalog Cut Sheet

- PDF-FQZO-12-10 P

- Part Drawings

- PDF-QuickNet SFQ ..

### How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) [Search Tips](#) 

☒ **Text Search: 'FQZ-12-10'**

Your search criteria matched only one product, shown below

## FQZ-12-10



- QuickNet™ SFQ Series MTP\* Fiber Optic Cassettes are compatible with QuickNet™ Patch Panels for up to 96 fiber connections in 1RU with QAPP48HDBL QuickNet™ 48-port Angled Patch Panel
- Low insertion loss of 0.5dB max. per cassette and .75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of <2.6dB
- Return loss: ≥26dB (10Gig™ multimode), ≥20dB (multimode), ≥55dB (singlemode)
- Connect together with high-density female MTP\* cable assemblies as interconnecting network segments for deploying a remote or data center location in minutes
- Significantly reduce installation time and labor by eliminating field connector terminations
- Factory terminated, assembled and 100% tested
- Insertion loss data provided on every fiber cassette
- Return loss data provided on all singlemode fiber cassettes
- Lifetime traceability of test data to a Q.C. number on each fiber cassette
- 10Gig™ OM3 50/125µm Fiber Cassettes are tested per IEEE 802.3ae 10 GbE to support

network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm; backward compatible with all 50/125µm (OM2) MPO or MTP\* system requirements

\*MTP is a registered trademark of US Conec Ltd.

• Part Number	FQZ-12-10
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	Six LC duplex adapters to one male MTP*; 12-fiber pre-terminated MTP* rear mount cassette provides low insertion loss of 1.0dB max. per fiber; 10Gig™ 50/125µm (OM4) fiber. Method A.
• Pricing Description	OM4 50µm LC Duplex 6 Fiber SFQ Cassette, Method A
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.